

## Bill of Materials

TI DESIGNS

TIDM-THDREADING

ltem	Qty	Reference	Value	Manufacturer	Manufacturer Part Number	Part Description	Digikey Part Number
1	1	IC1	24C02CSN	MICROCHIP TECHNOLOGY	24LC02B-I/SN	IC EEPROM 2KBIT 400KHZ 8SOIC	24LC02B-I/SN-ND
2	1	XT1	32.768 KHZ	CITIZEN FINEDEVICE CO LTD (VA)	CMR200T32768DZBT	CRYSTAL 32.768 KHZ 6PF SMD	300-8341-1-ND
3	2	C37 C40	12pF	YAGEO (VA)	CC0603JRNPO9BN120	CAP CER 12PF 50V 5% NPO 0603	311-1059-1-ND
4		C8 C10 C12 C15 C17 C19 C21	15nF	YAGEO (VA)	CC0805KRX7R9BB153	CAP CER 0.015UF 50V 10% X7R 0805	311-1143-1-ND
5		C23 C25 C27 C28 C30 C31 C33 C36 C43	100nF	YAGEO (VA)	CC0603ZRY5V9BB104	CAP CER 0.1UF 50V Y5V 0603	311-1343-1-ND
6	7	C41 C42 C52 C53 C54 C57 C59	0.1uF	YAGEO (VA)	CC0603ZRY5V9BB104	CAP CER 0.1UF 50V Y5V 0603	311-1343-1-ND
7	2	C38 C44	0.47uF	YAGEO (VA)	CC0603KRX7R7BB474	CAP CER 0.47UF 16V 10% X7R 0603	311-1428-1-ND
8	8	C22 C24 C26 C29 C32 C34 C35 C51 C49 C1 C2 C3 C4 C5 C6 C7 C9 C11 C13 C14 C16 C18	4.7uF	YAGEO (VA)	CC0603KRX5R6BB475	CAP CER 4.7UF 10V 10% X5R 0603	311-1455-1-ND
9	14	C20	47pF	YAGEO (VA)	CC0805JRNPOBBN470	CAP CER 47PF 500V 5% NPO 0805	311-1484-1-ND
10	1	C55 C56 C58	10uF	KEMET (VA)	T491A106M006AT	CAP TANT 10UF 6.3V 20% 1206	399-3685-1-ND
				, ,		CAP ALUM 4.7UF 400V 20%	
11	1	C100	4.7uF/400V	KEMET	ESH475M400AH2AA	RADIAL	399-6097-ND
12	8	ACT JP2 JP11 JP12 REACT RX_EN TX_EN HD1	2x1 0.1 Header	3M	961102-6404-AR	CONN HEADER VERT SGL 2POS GOLD	3M9447-ND
13	8	JP3 JP4 JP5 JP6 JP7 JP8 JP9 JP10 AUXVCC3	3x1 0.1 Header	3M	961103-6404-AR	CONN HEADER VERT SGL 3POS GOLD	3M9448-ND
14	8	SV2	5x1 0.1 Header	3M	961105-6404-AR	CONN HEADER VERT SGL 5POS GOLD	961105-6404-AR
15	3	DGND DVCCs	4x1 0.1 Header	3M	961104-6404-AR	CONN HEADER VERT SGL 4POS GOLD	3M9449-ND
16	1	SV1	2x2 0.1 Header	TE CONNECTIVITY AMP	825440-2	CONN HEADER VERT DUAL 4POS GOLD	A106735-ND
17	8	R/L7 R/L8 R/L9 R/L10 R/L11 R/L12 R/L13 R/L14	0Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0805ZT0R00	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZT0R00CT-ND
18	4	R1 R2 R3	S20K275	EPCOS INC	S20K275	VARISTOR 275V RMS 20MM RADIAL	495-1417-ND
19	2	LED_3 LED_4	Orange	ROHM SEMICONDUCTOR	SLR-342DC3F	LED 3.1MM 610NM ORANGE TRANSP	511-1245-ND
20	2	LED_1 LED_6	Green	ROHM SEMICONDUCTOR	SLR-342MC3F	LED 3.1MM 563NM GREEN TRANSP	511-1247-ND
21	2	LED_ACT LED_REACT	Red	ROHM SEMICONDUCTOR	SLR-342VC3F	LED 3.1MM 650NM RED TRANSPARENT	511-1249-ND

Item	Qty	Reference	Value	Manufacturer	Manufacturer Part Number	Part Description	Digikey Part Number
						LED 3.1MM 585NM YELLOW	
22	2	LED_2 LED_5	Yellow	ROHM SEMICONDUCTOR	SLR-342YC3F	TRANSP	511-1251-ND
		D1 D2 D3 D4 D5 D6 D7 D8 D9 D10					
		D11 D12 D13 D14 D15 D16					
		D28 D29 D30 D31 D32 D33 D34 D35				DIODE SW GPP 75V 200MA	
23	32	D36 D37 D38 D39 D40 D41 D42 D43 D44	PMLL4148	NXP SEMICONDUCTORS (VA)	PMLL4148L,115	SOD80C	568-1749-1-ND
						TRANSISTOR PNP 45V 100MA	
24	2	Q1 Q2	BC857BSMD	NXP SEMICONDUCTORS (VA)	BC860B,215	SOT23	568-6094-1-ND
						TXRX IRDA 115.2KBIT 1.9MM 6-	
25	1	IRDA	TFBS4711-TT1	VISHAY SEMICONDUCTOR OPTO DIVISION (VA)	TFBS4711-TT1	SMD	751-1068-1-ND
						CONN D-SUB RCPT STR 9POS	
26	1	RS1	RS-232 Connector	TE CONNECTIVITY AMP	2-5747706-0	30GOLD	A32036-ND
						DIODE SCHOTTKY 40v 350MW	
27	4	D24 D25 D26 D27	LL103A	DIODES INCORPORATED (VA)	LLSD103A-7	MINIMELF	LLSD103ADICT-ND
						CONN HEADER 14 POS STRGHT	
28	1	JTAG	JTAG	3M	N2514-6002-RB	GOLD	MHC14K-ND
						BEAD CORE 4A 100 MHZ 0805	
29	6	L1 L3 L5 L6	EXCML20A	PANASONIC ELECTRONIC COMPONENTS (VA)	EXC-ML20A390U	SMD	P10191CT-ND
				,		CAP ALUM 150UF 10V 20%	
30	1	C101	150uF	PANASONIC ELECTRONIC COMPONENTS	EEU-FR1A151	RADIAL	P14374-ND
						SWITCH TACTILE SPST-NO 0.02A	
31	4	BTN1 BTN2 BTN3 BTN4 RESET	Switch	PANASONIC ELECTRONIC COMPONENTS (VA)	EVQ-11L05R	15V	P8079SCT-ND
32	2	OPTO1 OPTO2	TIL191	CEL CALIFORNIA EASTERN LABS	PS2501-1-A	OPTOCOUPLER 1CH TRANS 4-DIP	PS2501-1A-ND
33	2	U1 U2	PS8802	CEL CALIFORNIA EASTERN LABS (VA)	PS8802-1-F3-AX		PS8802-1-F3-AXCT-ND
34	1	R65	68Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603FT68R0	RES TF 68 OHM 1% 0.1W 0603	RMCF0603FT68R0CT-ND
						RES 100 OHM 1/10W 5% 0603	
35	8	R54 R55 R56 R57 R58 R59 R60 R61	100Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT100R	SMD	RMCF0603JT100RCT-ND
36	2	R62 R68 R72 R78	1kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT1K00	RES 1K OHM 1/10W 5% 0603 SMD	
37	1	R67	1.5kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT1K50	RES 1.5K OHM 1/10W 5% 0603	RMCF0603JT1K50CT-ND
38	1	R64	220Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT220R	RES 220 OHM 1/10W 5% 0603	RMCF0603JT220RCT-ND
39	2	R69 R71	2.2kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT2K20	RES 2.2K OHM 1/10W 5% 0603	RMCF0603JT2K20CT-ND
40	1	R48	330Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT330R	RES 330 OHM 1/10W 5% 0603	RMCF0603JT330RCT-ND
41	1	R51	47ΚΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT47K0	RES 47K OHM 1/10W 5% 0603	RMCF0603JT47K0CT-ND
42	1	R47	47Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603JT47R0	RES 47 OHM 1/10W 5% 0603 SMD	RMCF0603JT47R0CT-ND
43	18	R73 R74 R75 R76 R77 R79	0Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0603ZT0R00	RES 0.0 OHM 1/10W 0603 SMD	RMCF0603ZT0R00CT-ND
44	5	R42 R43 R46	560kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0805FT560K	RES TF 560K OHM 1% 0.125W	RMCF0805FT560KCT-ND
45	4	R49 R50 R52 R53	100ΚΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0805JT100K	RES 100K OHM 1/8W 5% 0805	RMCF0805JT100KCT-ND
46	3	R40 R41 R63	10kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0805JT10K0	RES 10K OHM 1/8W 5% 0805 SMD	
47	1	R36	10Ω 1kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0805JT10R0	RES 10 OHM 1/8W 5% 0805 SMD	RMCF0805JT10R0CT-ND
48 49	14 3	R14 R16 R18 R24 R25 R26 R15 R17 R19	2.37kΩ	STACKPOLE ELECTRONICS INC (VA)  STACKPOLE ELECTRONICS INC (VA)	RMCF0805JT1K00 RMCF0805FT2K37	RES 1.0K OHM 1/8W 5% 0805 RES 2.37K OHM 1/8W 1% 0805	RMCF0805JT1K00CT-ND RMCF0805FT2K37CT-ND
50	9	R5 R6 R7 R8 R9 R10 R11 R12 R13	330kΩ	STACKPOLE ELECTRONICS INC (VA)	RMCF0805JT330K	RES 330K OHM 1/8W 5% 0805	RMCF0805JT330KCT-ND
51	4	R20 R21 R22 R23	13Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0805FT13R0	RES 13 OHM 1/8W 1% 0805 SMD	RMCF0805FT13R0CT-ND
52	1	R4 R39 R99 R100 R101 R102 R103	0Ω	STACKPOLE ELECTRONICS INC (VA)	RMCF0805ZT0R00	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZT0R00CT-ND
53	2	RF1 RF2	EM Connector	SAMTEC	TFM-110-02-S-D-WT	CONN HEADER 20POS 1.27MM	N/A
54	1	ZD3	SMAJ5.0ABCT	BOURNS INC (VA)	SMAJ5.0A	DIODE TVS 5.0V 400W UNI 5%	SMAJ5.0ABCT-ND
55	4	TVS1 TVS2 TVS3 TVS4	SMAJ5.0CA	BOURNS INC (VA)	SMAJ5.0CA	DIODE TVS 5.0V 400W BI 5% SMD	SMAJ5.0CABCT-ND
56	1	EZ-RF	SL127L6TH	DNP	DNP	Mill-Max 850-10-006-20-001000	N/A
57	1	LCD1	TI 160SEG LCD	ADKOM	fh-1152p	Custom LCDs for TI EVM	Custom

Item	Qty	Reference	Value	Manufacturer	Manufacturer Part Number	Part Description	Digikey Part Number
58		R44 R45	DNP	DNP	DNP	DNP	DNP
59		C63	DNP	DNP	DNP	DNP	DNP
60	1	R66	DNP	DNP	DNP	DNP	DNP
61	1	R70	DNP	DNP	DNP	DNP	DNP
62	1	U\$1	CUI_XR	CULINC	VSK-S3-3R3U	Isolated Power Supply, 3.3 V, 700	102-1801-ND
63	1	MSP430F67791A	MSP430F67791AIPEU	TEXAS INSTRUMENTS	MSP430F67791AIPEU	MSP430F67791A IPEU metering	N/A
64	1	C102	100uF	RUBYCON	100YXG100MEFC10X23	CAP Electrolytic 100uF 100V 20%,	1189-1020-ND
65	3	C39,C46,C50	0.22uF	EPCOS INC	B32922C3224M	CAP poly 0.22uF 305VAC/630VDC	495-2320-ND
66	1	C48	2.2uF	TDK CORPORATION (VA)	C3225X7R2A225K230AB	CAP Ceramic 2.2uF 100V X7R 1210	445-4497-2-ND
67	1	C45	0.01uF	TDK CORPORATION (VA)	C1608X7R1E103K080AA	CAP CER 10000PF 25V 10% X7R	445-5100-1-ND
68	1	C62	47uF	TAIYO YUDEN (VA)	LMK325BJ476MM-T	CAP Ceramic 47uF 10V X5R 1210	587-1383-1-ND
69	1	C47	0.1uF	KEMET (VA)	C0603C104K8RACTU	CAP Ceramic 0.1uF 10V X5R 0603	399-1095-1-ND
70	1	C60	.056uF	MURATA ELECTRONICS (VA)	GRM188R71E563KA01D	CAP Ceramic .056uF 25V X7R 10%	490-6433-1-ND
71	1	C61	100pF	KEMET (VA)	C0603C101J3GACAUTO	CAP Ceramic 100pF 25V NPO, 5%	399-6841-1-ND
72	1	D23	B160	COMCHIP TECHNOLOGY (VA)	CDBB160-G	Diode Schottky 1A 60V B160 SMB	641-1107-1-ND
73	3	D17,D19,D21	48V	DIODES INCORPORATED (VA)	1N4757A-T	Diode Zener 51V 1W 1N4757A D0-	1N4757ADICT-ND
74	3	D18,D20,22	1N4007	FAIRCHILD SEMICONDUCTOR (VA)	1N4007	DIODE GEN PURPOSE 1000V 1A	1N4007FSCT-ND
75	1	L7	1mH	COILCRAFT	MSS1038-105	Inductor, SMT, MSS1038-105	N/A
76	1	R35,R38	1ΜΩ	TE CONNECTIVITY AMP (VA)	1-1879417-9	RES 1M OHM 1/16W 1% 0603	A102234CT-ND
77	1	R37	33.2kΩ	STACKPOLE ELECTRONICS INC (VA)	RNCS0603BKE33K2	RES 33.2K OHM 1/16W .1% 0603	RNCS0603BKE33K2CT-ND
78	1	R95	22.1kΩ	TE CONNECTIVITY AMP (VA)	9-1879337-2	RES 22.1K OHM 1/16W 1% 0603	A102241CT-ND
79	1	R96	51.1Ω	TE CONNECTIVITY AMP (VA)	3-1879335-7	RES 51.1 OHM 1/16W 1% 0603	A102292TR-ND
80	1	R97	31.6kΩ	TE CONNECTIVITY AMP (VA)	1879338-8	RES 31.6K OHM 1/16W 1% 0603	A102261DKR-ND
81	1	R98	10.0kΩ	TE CONNECTIVITY AMP (VA)	1614881-2	RES 10.0K OHM 1/16W 0.1% 0603	A102331CT-ND
82	3	R92,R93,R94	100Ω	PANASONIC ELECTRONIC COMPONENTS	ERG-2SJ101	RES 100 OHM 2W 5% AXIAL	P100W-2BK-ND
83	1	U3	TPS54060ADGQ	TEXAS INSTRUMENTS	TPS54060ADGQ	IC REG BUCK ADJ 0.5A 10MSOP	296-30339-5-ND

## IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.