

NexFET™ 智能同步整流器

特性

- V_{DD} 为 4.5V 时, R_{on} 为 55m Ω (典型值)
- 集成
- 最大额定电流 80A
- 高密度 — 小外形尺寸无引线 (SON) 5mm × 6mm 封装
- 超低电感封装
- 系统已优化的印刷电路板 (PCB) 封装
- 与 TTL IN 信号兼容
- 无卤素
- 符合 RoHS 绿色环保标准-无铅端子镀层无卤素

应用范围

- 针对 DC/DC 转换器的次级同步整流

说明

CSD43301Q5M NexFET™ 智能同步整流器是一款针对高功率高密度 DC/DC 转换器内的次级同步整流而进行了高度优化的设计。这个产品集成有驱动器集成电路 (IC) 和超低功耗 R_{on} 功率金属氧化物半导体场效应晶体管 (MOSFET) 来完善同步整流功能。此外, 已经对印刷电路板 (PCB) 封装进行了优化以帮助减少设计时间并简化总体系统设计。

订购信息

器件	封装	介质	数量	出货
CSD43301Q5M	小外形尺寸无引线 (SON) 5mm × 6mm 塑料封装	13-英寸卷带	2500	卷带包装




Figure 1. Application Diagram



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

NexFET is a trademark of Texas Instruments.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 2012–2013, Texas Instruments Incorporated
English Data Sheet: [SLPS380](#)

CSD43301Q5M

ZHCSAI6B – DECEMBER 2012 – REVISED MAY 2013

www.ti.com.cn


These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

 $T_A = 25^\circ\text{C}$ (unless otherwise noted)

		VALUE		UNIT
		MIN	MAX	
DRAIN to P_{GND}		-0.3	12	V
DRAIN to P_{GND} (10ns)		-7	14	V
V_{DD} to P_{GND}		-0.3	8	V
IN, SD to P_{GND} ⁽²⁾		-0.3	$V_{DD} + 0.3$	V
ESD Rating	Human Body Model (HBM)		2000	V
	Charged Device Model (CDM)		500	V
Power Dissipation (P_D)			12	W
Operating Temperature Range, (T_J)		-40	150	$^\circ\text{C}$
Storage Temperature Range, (T_{STG})		-65	150	$^\circ\text{C}$

(1) Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to Absolute Maximum rated conditions for extended periods may affect device reliability.

(2) Must not exceed 8V

RECOMMENDED OPERATING CONDITIONS

 $T_A = 25^\circ$ (unless otherwise noted)

Parameter	Conditions	MIN	MAX	UNIT
Bias Voltage (V_{DD})		4.5	6	V
Input Supply Voltage (V_{IN})			9.6	V
Continuous Output Current (I_{OUT})			80	A
Peak Output Current, (I_{OUT-PK}) ⁽¹⁾			120	A
Switching Frequency, (f_{SW})			1500	kHz
Minimum IN Pulse Width		48		ns
Operating Temperature		-40	125	$^\circ\text{C}$

(1) Peak Output Current is applied for $t_p = 50\mu\text{s}$.

THERMAL INFORMATION

 $T_A = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER		MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case (Top of package)			20	$^\circ\text{C/W}$
$R_{\theta JB}$	Thermal Resistance, Junction-to-Board ⁽¹⁾			2	$^\circ\text{C/W}$

(1) $R_{\theta JB}$ value based on hottest board temperature within 1mm of the package.

ELECTRICAL CHARACTERISTICS

 $T_A = 25^\circ\text{C}$, $V_{DD} = 5\text{V}$ (unless otherwise noted)

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNIT
Device On Resistance					
R _{on}	I _D = 50A, , T _J = 25°C	0.55	0.70		mΩ
	I _D = 50A, T _J = 125°C	0.70	0.88		mΩ
V _{DD}					
Standby Supply Current (I _{DD})	SD = V _{DD} = 5V	153	300		μA
Operating Supply Current (I _{DD})	SD = 0V, IN = 50% Duty Cycle, f _{SW} = 300kHz	29.5			mA
POWER-ON RESET AND UNDER VOLTAGE LOCKOUT					
Power on Reset (V _{DD} Rising)	T _A = 25°C	3.9	4.2	4.5	V
	T _A = -40°C to 140°C	3.7	4.2	4.65	V
UVLO (V _{DD} Falling)		3.45	3.9	4.35	V
Hysteresis		200	300	500	mV
IN					
IN Logic Level High (V _{INH})	V _{DD} = 5V, SD = 0, I _D = 25A (See Figure 4)	2.0			V
IN Logic Level Low (V _{INL})			0.8		V
IN Input Hysteresis			0.8		V
IN to DRAIN Propagation Delay (t _{PDLH})			32		ns
IN to DRAIN Propagation Delay (t _{PDHL})			80		ns
Minimum Pulse Width Changes Output			36	48	ns
SD					
SD Logic Level High Threshold (V _{IH})		2.0			V
SD Logic Level Low Threshold (V _{IL})			0.8		V
Hysteresis			0.8		V
SD to DRAIN Propagation Delay (t _{PDLH})	V _{DD} = 5V, IN = V _{DD} , I _D = 25A (See Figure 5)	80			ns
SD to DRAIN Propagation Delay (t _{PDHL})		32			ns
Dynamic Characteristics					
Output Capacitance (C _O)	V _{DRAIN} = 6V	10	13		nF
Output Charge (Q _O)		54			nC
Body Diode					
Forward Voltage (V _F)	I _D = 40A	0.75	0.85		V
Reverse Recovery Charge (Q _{RR})	I _D = 40A, V _{DRAIN} = 6V, di/dt = 150A/μs	161			nC
Reverse Recovery Time Delay (t _{RR})		72			ns

PIN CONFIGURATION




Figure 2. Pin Configuration

PIN DESCRIPTION

PIN		DESCRIPTION
NO.	NAME	
1,2,4, 8, 10,11	NC	No connect. These should not be used for any electrical connection. These pins should not be connected to each other. Connect to dead copper only.
3	V _{DD}	Supply Voltage for IC
5,6	DRAIN	Drain terminal of internal MOSFET
7	P _{GND}	Power Ground and source terminal of the internal MOSFET. Needs to be connected to Pin 13 on PCB
9	SD	Shut Down Pin: Logic High disables the Device
12	IN	Input for Gate Driver
13	P _{GND}	Power Ground and source terminal of the internal MOSFET. Needs to be connected to Pin 7 on PCB




Figure 3. Functional Block Diagram

TYPICAL DEVICE CHARACTERISTICS




Figure 4. IN Switching Waveforms




Figure 5. SD Switching Waveform




Figure 6. Output Capacitance




Figure 7. Normalized On Resistance R_{on}

TYPICAL DEVICE CHARACTERISTICS CONTINUED




Figure 8. On Resistance vs. Supply Voltage




Figure 9. Supply Current vs. Supply Voltage




Figure 10. Supply Current vs. Switching Frequency

Application Information

V_{DD} and Under-Voltage Lockout (UVLO)

The driver IC in the CSD43301Q5M has an internal UVLO protection feature on the V_{DD} pin. Whenever the driver is in the UVLO condition (i.e. when V_{DD} voltage is less than V_{ON} during power up and when V_{DD} voltage is less than V_{OFF} during power down), this circuit holds the gate of the integrated MOSFET LOW, regardless of the status of IN and SD. The UVLO is typically 4.2V with 300-mV typical hysteresis. This hysteresis helps prevent chatter when low V_{DD} supply voltages have noise from the power supply and also when there are droops in the V_{DD} bias voltage when the system commences switching and there is a sudden increase in I_{DD} . This provides the capability to operate at low voltage levels (below 5V), along with best-in-class switching characteristics. For example, at power up, the MOSFET remains OFF until the V_{DD} voltages reaches the UVLO threshold. This prevents operating the MOSFET in the linear region and conducting a large load current at the same time, which often results in device overheating and can potentially damage the device.

Since the driver draws current from the V_{DD} pin to bias all internal circuits, for the best high-speed circuit performance, Multi-Layer Ceramic Capacitor (MLCC) bypass capacitors are recommended to prevent noise problems. A 1 μ F MLCC type capacitor should be located as close as possible to the V_{DD} to GND pins of the gate driver.

Operating Supply Current

The driver IC in the CSD43301Q5M has a low quiescent current in normal operation. I_{DDQ} is less than 0.2 mA when the device is disabled ($SD = 0$). The operating current vs. supply voltage is shown in [Figure 9](#), and the operating current vs. frequency is shown in [Figure 10](#).

Input Stage

The input pins (IN and SD) of the CSD43301Q5M are based on a TTL/CMOS compatible input threshold logic that is independent of the V_{DD} supply voltage. With a typical high threshold of 2.2 V and a typical low threshold of 1.2 V, the logic level thresholds can be conveniently driven with PWM control signals derived from 3.3-V or 5-V digital power controllers. Wider hysteresis (typical of 0.8 V) offers enhanced noise immunity compared to traditional TTL logic implementations, where the hysteresis is typically less than 0.5 V. These devices also feature tight control of the input pin threshold voltage levels which eases system design considerations and ensures stable operation across temperature. The very low input capacitance on these pins reduces loading and increases switching speed. The device features an important safety function wherein, whenever any of the input pins are in a floating condition, the output of the respective channel is held in the low state. This is achieved using a V_{DD} pull-up resistor on the SD input or a GND pull-down resistor on the IN input. This can be seen in the block diagram in [Figure 3](#).

Power Dissipation

Power Dissipation of the CSD43301Q5M used in secondary rectification is given by the following:

$$P_{LOSS} = P_{DRV} + P_{COND} + P_{SW} \quad (1)$$

where driver loss is given by

$$P_{DRV} = V_{DD} \times I_{DD} \quad (2)$$

and conduction loss is given by

$$P_{COND} = I_{D_RMS}^2 \times R_{ON} \quad (3)$$

Switching losses consist of body diode conduction losses during dead time, body diode reverse recovery losses, and output charge losses, given by the following:

$$P_{SW} = I_D \times V_F \times (DT_R + DT_F) \times F_{SW} + Q_{RR} \times V_{DRAIN} \times F_{SW} + \frac{1}{2} Q_{OSS} \times V_{DRAIN} \times F_{SW} \quad (4)$$

Recommended PCB Design Overview

The CSD43301Q5M features extremely low nominal R_{ON} . In order to maximize the performance of this device, some simple layout guidelines should be followed.

- The DRAIN pins of the CSD43301Q5M should be placed as close as possible to the inductor and connected with a short wide trace. This reduces PCB conduction losses and reduce switching noise level. ⁽¹⁾
- The GND pin (pin 7) must be connected into the thermal pad (pin 13) on the bottom of the device via a copper pour (without thermal spokes) for maximum performance.
- The CSD43301Q5M has the ability to use the GND planes as the primary thermal path. As such, the use of thermal vias is an effective way to pull away heat from the device and into the system board. Concerns of solder voids and manufacturability problems can be addressed by the use of three basic tactics to minimize the amount of solder attach that will wick down via the barrel:
 - Intentionally space out the vias from each other to avoid a cluster of holes in a given area.
 - Use the smallest drill size allowed in your design. The example in [Figure 11](#) uses vias with a 10 mil drill hole and a 16 mil capture pad.
 - Tent the opposite side of the via with a solder mask.

In the end, the number and size of the thermal vias should align with the end user's PCB design rules and manufacturing types.





Figure 11. Recommended PCB Layout (Top Down View)


(1) Keong W. Kam, David Pommerenke, "EMI Analysis Methods for Synchronous Buck Converter EMI Root Cause Analysis", University of Missouri – Rolla

MECHANICAL DATA




DIM	MILLIMETERS			INCHES		
	Min	Nom	Max	Min	Nom	Max
A	1.400	1.450	1.500	0.055	0.057	0.059
A1	0.000	0.000	0.050	0.000	0.000	0.002
b	0.200	0.250	0.350	0.008	0.010	0.013
b1	2.750 TYP			0.108 TYP		
b2	0.200	0.250	0.320	0.008	0.010	0.013
b3	0.250 TYP			0.010 TYP		
c1	0.150	0.200	0.250	0.006	0.008	0.010
c2	0.150	0.200	0.250	0.006	0.008	0.010
D2	5.300	5.400	5.500	0.209	0.213	0.217
d	0.200	0.250	0.300	0.008	0.010	0.012
d1	0.350	0.400	0.450	0.014	0.016	0.018
d2	1.900	2.000	2.100	0.075	0.079	0.083
E	5.900	6.000	6.100	0.232	0.236	0.240
E1	4.900	5.000	5.100	0.193	0.197	0.201
E2	3.200	3.300	3.400	0.126	0.130	0.134
e	0.500 TYP			0.020 TYP		
K	0.350 TYP			0.014 TYP		
L	0.400	0.500	0.600	0.016	0.020	0.024
L1	0.210	0.310	0.410	0.008	0.012	0.016
θ	0.00	—	—	0.00	—	—

Recommended PCB Pattern



NOTE: Dimensions are in mm (inches).

Recommended Stencil



NOTE: Dimensions are in mm (inches).

REVISION HISTORY

Changes from Original (December 2012) to Revision A Page

- Changed [Figure 3](#) 4

Changes from Revision A (December 2012) to Revision B Page

- Changed the MECHANICAL DATA image and corresponding table 9
- Changed the Recommended PCB Pattern - lead width From: 0.300(0.012) To: 0.350(0.014) 10
- Changed the Recommended Stencil image 10

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
CSD43301Q5M	Active	Production	LSON-CLIP (DQP) 12	2500 LARGE T&R	ROHS Exempt	NIPDAU	Level-2-260C-1 YEAR	-55 to 125	43301M
CSD43301Q5M.B	Active	Production	LSON-CLIP (DQP) 12	2500 LARGE T&R	-	Call TI	Call TI	-55 to 125	

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.


⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer:The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


TAPE AND REEL INFORMATION



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CSD43301Q5M	LSON-CLIP	DQP	12	2500	330.0	12.4	5.3	6.3	1.8	8.0	12.0	Q1

TAPE AND REEL BOX DIMENSIONS



*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CSD43301Q5M	LSON-CLIP	DQP	12	2500	346.0	346.0	33.0

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](#) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月