

CSD75208W1015 双路 20V 共源 P 通道 NexFET™ 功率金属氧化物半导体场效应晶体管 (MOSFET)

1 特性

- 双路 P 通道 MOSFET
- 共源配置
- 1.5mm x 1mm 小尺寸封装
- 栅极 - 源电压钳位
- 栅极静电放电 (ESD) 保护 - 3kV
- 无铅
- 符合 RoHS 环保标准
- 无卤素


2 应用

- 电池管理
- 负载开关
- 电池保护

3 说明

此器件设计用于在超薄且具有出色散热特性的超小外形尺寸封装内提供最低的导通电阻和栅极电荷。低导通电阻与小型低厚度封装结合在一起，使得此器件成为电池供电运行空间受限应用的理想选择。

顶视图



产品概要

$T_A = 25^\circ\text{C}$		典型值		单位
V_{DS}	漏源电压	-20		V
Q_g	栅极电荷总量 (-4.5V)	1.9		nC
Q_{gd}	栅极电荷 (栅极到漏极)	0.23		nC
$R_{DS(on)}$	漏源导通电阻	$V_{GS} = -1.8\text{V}$	100	mΩ
		$V_{GS} = -2.5\text{V}$	70	mΩ
		$V_{GS} = -4.5\text{V}$	56	mΩ
R_{D1D2} (导通)	漏极到漏极导通电阻	$V_{GS} = -1.8\text{V}$	190	mΩ
		$V_{GS} = -2.5\text{V}$	120	mΩ
		$V_{GS} = -4.5\text{V}$	90	mΩ
$V_{GS(th)}$	阈值电压	-0.8		V

订购信息⁽¹⁾

器件	数量	介质	封装	出货
CSD75208W1015	3000	7 英寸卷带	1.0mm x 1.5mm 晶圆级封装	卷带封装
CSD75208W1015T	250	7 英寸卷带		

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。



绝对最大额定值

$T_A = 25^\circ\text{C}$		值	单位
V_{DS}	漏源电压	-20	V
V_{GS}	栅源电压	-6	V
I_{D1D2}	持续漏极到漏极电流， $T_C = 25^\circ\text{C}$ 时测得	-1.6	A
	脉冲漏极到漏极电流， $T_C = 25^\circ\text{C}$ ⁽¹⁾ 时测得	-22	A
I_S	持续源引脚电流	-3	A
	⁽¹⁾ 脉冲源引脚电流 ⁽²⁾	-39	A
I_G	持续栅极钳位电流	-0.5	A
	脉冲栅极钳位电流 ⁽¹⁾	-7	A
P_D	功率耗散	0.75	W
T_J, T_{stg}	运行结温和 储存温度范围	-55 至 150	$^\circ\text{C}$

(1) 最大 $R_{\theta JA} = 165^\circ\text{C/W}$ ，脉冲持续时间 $\leq 100\mu\text{s}$ ，占空比 $\leq 1\%$

(2) 两器件并行





目录

1	特性	1	6.1	接收文档更新通知	8
2	应用	1	6.2	社区资源	8
3	说明	1	6.3	商标	8
4	修订历史记录	3	6.4	静电放电警告	8
5	Specifications	4	6.5	Glossary	8
	5.1 Electrical Characteristics	4	7	机械、封装和可订购信息	9
	5.2 Thermal Information	4	7.1	CSD75208W1015 封装尺寸	9
	5.3 Typical MOSFET Characteristics	5	7.2	建议印刷电路板 (PCB) 焊盘图案	10
6	器件和文档支持	8	7.3	卷带封装信息	10

4 修订历史记录

Changes from Original (July 2014) to Revision A	Page
• Changed Figure 1	5
• 已添加 社区资源 和 接收文档更新通知 部分添加到了 器件和文档支持 。	8

5 Specifications

5.1 Electrical Characteristics

 $T_A = 25^\circ\text{C}$ unless otherwise stated

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
STATIC CHARACTERISTICS						
BV _{DSS}	Drain-to-Source Voltage	V _{GS} = 0 V, I _{DS} = −250 μA	−20			V
BV _{GSS}	Gate-to-Source Voltage	V _{DS} = 0 V, I _G = −250 μA	−6.1		−7.2	V
I _{DSS}	Drain-to-Source Leakage Current	V _{GS} = 0 V, V _{DS} = −16 V			−1	μA
I _{GSS}	Gate-to-Source Leakage Current	V _{DS} = 0 V, V _{GS} = −6 V			−100	nA
V _{GS(th)}	Gate-to-Source Threshold Voltage	V _{DS} = V _{GS} , I _{DS} = −250 μA	−0.5	−0.8	−1.1	V
R _{DS(on)}	Drain-to-Source On-Resistance	V _{GS} = −1.8 V, I _D = −1 A		100	150	mΩ
		V _{GS} = −2.5 V, I _D = −1 A		70	88	mΩ
		V _{GS} = −4.5 V, I _D = −1 A		56	68	mΩ
R _{D1D2(on)}	Drain-to-Drain On-Resistance	V _{GS} = −1.8 V, I _{D1D2} = −1 A		190	285	mΩ
		V _{GS} = −2.5 V, I _{D1D2} = −1 A		120	150	mΩ
		V _{GS} = −4.5 V, I _{D1D2} = −1 A		90	108	mΩ
g _{fs}	Transconductance	V _{DS} = −2 V, I _D = −1 A		7.5		S
DYNAMIC CHARACTERISTICS						
C _{ISS}	Input Capacitance	V _{GS} = 0 V, V _{DS} = −10 V, f = 1 MHz		315	410	pF
C _{OSS}	Output Capacitance			132	172	pF
C _{RSS}	Reverse Transfer Capacitance			7.7	10	pF
Q _g	Gate Charge Total (−4.5 V)	V _{DS} = −10 V, I _{DS} = −1 A		1.9	2.5	nC
Q _{gd}	Gate Charge, Gate-to-Drain			0.23		nC
Q _{gs}	Gate Charge, Gate-to-Source			0.48		nC
Q _{g(th)}	Gate Charge at V _{th}			0.31		nC
Q _{OSS}	Output Charge	V _{DS} = −10 V, V _{GS} = 0 V		2.1		nC
t _{d(on)}	Turn On Delay Time	V _{DS} = −10 V, V _{GS} = −4.5 V, I _{DS} = −1 A, R _G = 0 Ω		9		ns
t _r	Rise Time			5		ns
t _{d(off)}	Turn Off Delay Time			29		ns
t _f	Fall Time			11		ns
DIODE CHARACTERISTICS						
V _{SD}	Diode Forward Voltage	I _{DS} = −1 A, V _{GS} = 0 V	−0.75		−1	V
Q _{rr}	Reverse Recovery Charge	V _{DD} = −10 V, I _F = −1 A, di/dt = 200 A/μs		4.3		nC
t _{rr}	Reverse Recovery Time			9		ns

5.2 Thermal Information


 $T_A = 25^\circ\text{C}$ unless otherwise stated

THERMAL METRIC		MIN	TYP	MAX	UNIT
$R_{\theta JA}$	Junction-to-Ambient Thermal Resistance ⁽¹⁾ ⁽²⁾		165		$^\circ\text{C}/\text{W}$
	Junction-to-Ambient Thermal Resistance ⁽²⁾ ⁽³⁾		95		


⁽¹⁾ Device mounted on FR4 material with minimum Cu mounting area

⁽²⁾ Measured with both devices biased in a parallel condition.

⁽³⁾ Device mounted on FR4 material with 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu.




Typ $R_{\theta JA} = 95^{\circ}\text{C/W}$
when mounted on
1 inch² (6.45 cm²) of
2-oz. (0.071-mm thick)
Cu.



Typ $R_{\theta JA} = 165^{\circ}\text{C/W}$
when mounted on
minimum pad area of
2-oz. (0.071-mm thick)
Cu.

5.3 Typical MOSFET Characteristics

($T_A = 25^{\circ}\text{C}$ unless otherwise stated)



Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 2. Saturation Characteristics




Figure 3. Transfer Characteristics




Figure 4. Gate Charge




Figure 5. Capacitance




Figure 6. Threshold Voltage vs Temperature




Figure 7. On-State Drain-to-Drain Resistance vs Gate-to-Source Voltage

Typical MOSFET Characteristics (continued)

($T_A = 25^\circ\text{C}$ unless otherwise stated)




Figure 8. On-State Drain-to-Source Resistance vs Gate-to-Source Voltage




Figure 9. Normalized On-State Resistance vs Temperature




Figure 10. Typical Diode Forward Voltage




Figure 11. Maximum Safe Operating Area




Figure 12. Maximum Drain Current vs Temperature

6 器件和文档支持

将

6.1 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。请单击右上角的通知我进行注册，即可收到任意产品信息更改每周摘要。有关更改的详细信息，请查看任意已修订文档中包含的修订历史记录。

6.2 社区资源

下列链接提供到 TI 社区资源的连接。链接的内容由各个分销商“按照原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的《使用条款》。

TI E2E™ 在线社区 **TI 的工程师对工程师 (E2E) 社区**。此社区的创建目的在于促进工程师之间的协作。在 e2e.ti.com 中，您可以咨询问题、分享知识、拓展思路并与同行工程师一道帮助解决问题。

设计支持 **TI 参考设计支持** 可帮助您快速查找有帮助的 E2E 论坛、设计支持工具以及技术支持的联系信息。

6.3 商标

NexFET, E2E are trademarks of Texas Instruments.
All other trademarks are the property of their respective owners.

6.4 静电放电警告



这些装置包含有限的内置 ESD 保护。存储或装卸时，应将导线一起截短或将装置放置于导电泡棉中，以防止 MOS 门极遭受静电损伤。

6.5 Glossary


SLYZ022 — *TI Glossary*.

This glossary lists and explains terms, acronyms, and definitions.

7 机械、封装和可订购信息

以下页面包括机械、封装和可订购信息。这些信息是指定器件的最新可用数据。这些数据发生变化时，我们可能不会另行通知或修订此文档。如欲获取此产品说明书的浏览器版本，请参见左侧的导航栏。

7.1 CSD75208W1015 封装尺寸




NOTE: 全部尺寸单位为 mm（除非另外注明）。

表 1. 引脚分配

位置	名称
B1, B2	源极
C1	栅极 1
C2	漏极 1
A2	栅极 2
A1	漏极 2


7.2 建议印刷电路板 (PCB) 焊盘图案



M0158-01

NOTE: 全部尺寸单位为 mm (除非另外注明)。

7.3 卷带封装信息



M0159-01

NOTE: 全部尺寸单位为 mm (除非另外注明)。

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
CSD75208W1015	Active	Production	DSBGA (YZC) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	75208
CSD75208W1015.B	Active	Production	DSBGA (YZC) 6	3000 LARGE T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	75208
CSD75208W1015T	Active	Production	DSBGA (YZC) 6	250 SMALL T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	75208
CSD75208W1015T.B	Active	Production	DSBGA (YZC) 6	250 SMALL T&R	Yes	SNAGCU	Level-1-260C-UNLIM	-55 to 150	75208

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](https://www.ti.com) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月