

PMP20249 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C2	2	0.47uF	CGA3E3X7R1H474K080AB	TDK	CAP, CERM, 0.47 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0603	0603
2	C5, C6, C9, C19	4	22uF	C4532X7R1E226M250KC	TDK	CAP, CERM, 22 µF, 25 V, +/- 20%, X7R,	
3	C8, C18, C21, C22	4	0.22uF	C1608X7R1H224K080AB	TDK	CAP, CERM, 0.22 µF, 50 V, +/- 10%, X7R, 0603	0603
4	C10, C24	2	0.1uF	C1005X7R1H104K050BB	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, 0402	0402
5	C11, C25	2	0.027uF	GRM155R61C273KA01D	MuRata	CAP, CERM, 0.027 µF, 16 V, +/- 10%, X5R, 0402	0402
6	C12, C26	2	0.1uF	GRM155R71A104KA01D	MuRata	CAP, CERM, 0.1 µF, 10 V, +/- 10%, X7R, 0402	0402
7	C13	1	220uF	EEE-FK1C221XP	Panasonic	CAP, AL, 220 µF, 16 V, +/- 20%, 0.34 ohm, SMD	SMT Radial D8
8	C14, C23, C27, C32	4	10uF	C1608X5R1A106M080AC	TDK	CAP, CERM, 10 µF, 10 V, +/- 20%, X5R, 0603	0603
9	C15, C28	2	0.1uF	CGA2B3X7R1H104K050BB	TDK	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
10	C16, C29	2	4.7uF	GCM21BR71C475KA73K	MuRata	CAP, CERM, 4.7 µF, 16 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0805	0805
11	C17	1	150uF	EEE-FK1C151XP	Panasonic	CAP, AL, 150 µF, 16 V, +/- 20%, 0.34 ohm, SMD	SMT Radial D8
12	C30	1	1000uF	EKM0250EI102MJ16S	Chemi-Con	CAP, AL, 1000 µF, 25 V, +/- 20%, TH	D10xL16mm
13	C31	1	0.1uF	GCM155R71H104KE02D	MuRata	CAP, CERM, 0.1 µF, 50 V, +/- 10%, X7R, AEC-Q200 Grade 1, 0402	0402
14	D1	1	30V	1SMB30CAT3G	ON Semiconductor	Diode, TVS, Bi, 30 V, 600 W, SMB	SMB
15	D2, D3	2	16V	SMAJ16CA	Littelfuse	Diode, TVS, Bi, 16 V, 400 W, SMA	SMA
16	J2, J5	2		5-146261-1	TE Connectivity	Header, 100mil, 2x1, Gold, TH	Header, 2x1, 100mil
17	J3	1		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
18	J4, J6	2		UB225-F04S6BY-B	Yuqiu Electronics	Receptacle, USB Type A, Gold, SMT	Receptacle, USB Type A, SMT
19	L1, L2	2	10uH	MSS1278-103MLB	Coilcraft	Inductor, Shielded Drum Core, Ferrite, 10 µH, 5.7 A, 0.02 ohm, SMD	MSS1278
20	L3	1	1uH	SRP4012-1R0M	Bourns	Inductor, Flat Wire, Powdered Iron, 1 µH, 4.8 A, 0.0336 ohm, SMD	4.7x1.2x4.0mm
21	R1, R4, R14, R17	4	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
22	R2, R15	2	49.9	CRCW040249R9FKED	Vishay-Dale	RES, 49.9, 1%, 0.063 W, 0402	0402
23	R3, R7, R8, R9, R16, R20, R21, R22	8	100k	CRCW0402100KJNED	Vishay-Dale	RES, 100 k, 5%, 0.063 W, 0402	0402
24	R5, R18	2	2.67k	CRCW04022K67FKED	Vishay-Dale	RES, 2.67 k, 1%, 0.063 W, 0402	0402
25	R10, R23	2	20k	CRCW040220K0JNED	Vishay-Dale	RES, 20 k, 5%, 0.063 W, 0402	0402
26	R11, R24	2	80.6k	CRCW040280K6FKED	Vishay-Dale	RES, 80.6 k, 1%, 0.063 W, 0402	0402
27	R12, R25	2	37.4k	CRCW040237K4FKED	Vishay-Dale	RES, 37.4 k, 1%, 0.063 W, 0402	0402
28	R13, R26	2	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
29	TP1, TP7, TP8, TP13	4		5000	Keystone	Test Point, Miniature, Red, TH	Red Miniature Testpoint
30	TP2, TP11, TP12, TP14	4		5001	Keystone	Test Point, Miniature, Black, TH	Black Miniature Testpoint
31	TP3, TP4, TP5, TP6, TP9, TP10	6		5002	Keystone	Test Point, Miniature, White, TH	White Miniature Testpoint
32	U1	1		LMS3655AQRNLRQ1	Texas Instruments	3.5/5.5A Synchronous Buck Regulator for Automotive Applications, RNL0022A	RNL0022A
33	U2, U4	2		TPS2549IRTERQ1	Texas Instruments	Automotive USB Charging Port Controller with Integrated Power Switch & Cable Compensation, RTE0016C	RTE0016C
34	U3	1		LMS3635AQRNLRQ1	Texas Instruments	3.5/5.5A Synchronous Buck Regulator for Automotive Applications, RNL0022A	RNL0022A
35	C3, C4, C7, C20	0	22uF	C4532X7R1E226M250KC	TDK	CAP, CERM, 22 µF, 25 V, +/- 20%, X7R,	
36	R6, R19	0	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated