



11/17/2016

PMP20541 REV B Bill of Materials

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
C17, C26	2	100pF	GRM1885C1H101JA01D	MuRata	CAP, CERM, 100 pF, 50 V, +/- 5%, COG/NP0, 0603	603
C15	1	3300pF	GRM188R72A332KA01D	MuRata	CAP, CERM, 3300 pF, 100 V, +/- 10%, X7R, 0603	603
C25	1	4700pF	GRM188R71H472KA01D	MuRata	CAP, CERM, 4700 pF, 50 V, +/- 10%, X7R, 0603	603
C16	1	0.022uF	GRM188R71H223KA01D	MuRata	CAP, CERM, 0.022 µF, 50 V, +/- 10%, X7R, 0603	603
C27	1	0.047uF	C1608X7R1H473K080AA	TDK	CAP, CERM, 0.047 µF, 50 V, +/- 10%, X7R, 0603	603
C22	1	0.22uF	C1608X7R1H224K080AB	TDK	CAP, CERM, 0.22 µF, 50 V, +/- 10%, X7R, 0603	603
C3, C8	2	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 0805	805
C20, C23	2	0.47uF	C2012X7R1H474K125AB	TDK	CAP, CERM, 0.47 µF, 50 V, +/- 10%, X7R, 0805	805
C9	1	100pF	GRM21A5C2E101JW01D	MuRata	CAP, CERM, 100 pF, 250 V, +/- 5%, COG/NP0, 0805	805
C14, C21, C28	3	1uF	GRM21BR71E105KA99L	MuRata	CAP, CERM, 1 µF, 25 V, +/- 10%, X7R, 0805	805
C10	1	150uF	20SVP150M	Panasonic	CAP, Aluminum Polymer, 150 µF, 20 V, +/- 20%, 0.02 ohm, 10x10.3 SMD	10x10.3
C11, C12, C13, C18, C19	5	10uF	C1210C106K3RACTU	Kemet	CAP, CERM, 10 µF, 25 V, +/- 10%, X7R, 1210	1210
C4, C5, C6, C7	4	2.2uF	GRM32ER72A225KA35L	MuRata	CAP, CERM, 2.2 µF, 100 V, +/- 10%, X7R, 1210	1210
C1, C24	2	4700pF	1812GC472KA1	AVX	CAP, CERM, 4700 pF, 2000 V, +/- 10%, X7R, 1812	1812
C2	1	47uF	EEE-FK1J470P	Panasonic	CAP, AL, 47 µF, 63 V, +/- 20%, 0.65 ohm, SMD	SMT Radial F
D1	1		ES2DA-13-F	Diodes Inc.	Diode, Superfast Rectifier, 200 V, 2 A, SMA	SMA
D2, D3	2		MMSD4148T1G	ON Semiconductor	Diode, Switching, 100 V, 0.2 A, SOT-123	SOD-123
D4, D5, D6	3		BAT54S-7-F	Diodes Inc.	Diode, Schottky, 30 V, 0.2 A, SOT-23	SOT-23
J1, J2	2		ED555/2DS	On-Shore Technology	Terminal Block, 3.5mm Pitch, 2x1, TH	7.0x8.2x6.5mm
L1	1	3.3uH	XFL4020-332MEB	Coilcraft	Inductor, Shielded, Composite, 3.3 µH, 2.9 A, 0.03 ohm, SMD	4x2x4mm
L2	1	330nH	XAL5030-331MEB	Coilcraft	Inductor, Shielded, Composite, 330 nH, 19.2 A, 0.0032 ohm, SMD	5.3x31.x5.5mm
Q1	1		FDMS86252	Fairchild Semiconductor	MOSFET, N-CH, 150 V, 4.6 A, PQFN08A	PQFN08A
Q2, Q4	2		MMBT3906-7-F	Diodes Inc.	Transistor, PNP, 40 V, 0.2 A, SOT-23	SOT-23
Q3	1		CSD18534Q5A	Texas Instruments	MOSFET, N-CH, 60 V, 50 A, SON 5x6mm	SON 5x6mm
R8, R17, R22	3	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	603
R2	1	4.7	CRCW06034R70JNEA	Vishay-Dale	RES, 4.7, 5%, 0.1 W, 0603	603
R13	1	20	CRCW060320R0JNEA	Vishay-Dale	RES, 20, 5%, 0.1 W, 0603	603
R10, R11, R24	3	1.00k	CRCW06031K00FKEA	Vishay-Dale	RES, 1.00 k, 1%, 0.1 W, 0603	603
R21	1	1.50k	CRCW06031K50FKEA	Vishay-Dale	RES, 1.50 k, 1%, 0.1 W, 0603	603
R18	1	2.00k	CRCW06032K00FKEA	Vishay-Dale	RES, 2.00 k, 1%, 0.1 W, 0603	603
R25	1	2.61k	CRCW06032K61FKEA	Vishay-Dale	RES, 2.61 k, 1%, 0.1 W, 0603	603
R6	1	4.53k	CRCW06034K53FKEA	Vishay-Dale	RES, 4.53 k, 1%, 0.1 W, 0603	603
R20	1	4.99k	CRCW06034K99FKEA	Vishay-Dale	RES, 4.99 k, 1%, 0.1 W, 0603	603
R16, R19, R23	3	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	603
R15	1	49.9k	CRCW060349K9FKEA	Vishay-Dale	RES, 49.9k, 1%, 0.1W, 0603	603
R12	1	53.6k	CRCW060353K6FKEA	Vishay-Dale	RES, 53.6 k, 1%, 0.1 W, 0603	603
R14	1	82.5k	CRCW060382K5FKEA	Vishay-Dale	RES, 82.5k, 1%, 0.1W, 0603	603
R4	1	121k	CRCW0603121KFKEA	Vishay-Dale	RES, 121 k, 1%, 0.1 W, 0603	603
R5	1	20	CRCW080520R0JNEA	Vishay-Dale	RES, 20, 5%, 0.125 W, 0805	805
R1	1	39k	CRCW120639K0JNEA	Vishay-Dale	RES, 39 k, 5%, 0.25 W, 1206	1206
R7	1	0.05	CRM2010-FZ-R050ELF	Bourns	RES, 0.05, 1%, 1 W, 2010	2010
R3	1	75	CRCW201075R0JNEF	Vishay-Dale	RES, 75, 5%, 0.75 W, AEC-Q200 Grade 0, 2010	2010
R9	1	5.1	CRCW25125R10JNEG	Vishay-Dale	RES, 5.1, 5%, 1 W, AEC-Q200 Grade 0, 2512	2512
T1	1		ATS-1410R-WNC	Atech OEM Inc	Transformer, 20.5 uH, SMT	22x22mm
T2	1		PA0184NLT	Pulse Engineering	Transformer, Gate Drive, 1.2mH, SMT	9.02x7.62x8.64mm
U1	1		UCC2897APWR	Texas Instruments	Advanced Active Clamp PWM Controller with Current-Mode Control, -40 to +125 degC, 20-pin TSSOP (PW), Green (RoHS & no Sb/Br)	PW0020A

Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
U2	1		FOD817AS	Fairchild Semiconductor	Optocoupler, 5 kV, 80-160% CTR, SMT	DIP-4L Gullwing
U3	1		TL431AIDBVR	Texas Instruments	Adjustable Precision Shunt Regulator, 34 ppm / degC, 100 mA, -40 to 85 degC, 5-pin SOT-23 (DBV), Green (RoHS & no Sb/Br)	DBV0005A

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated