

双路外设驱动器

查询样品: [SN65472-EP](#)


特性

- 特别针对高达 **300mA** 的使用
- 高压输出
- **55V** 时无输出闭锁
(在传到 **300mA** 电流后)
- 中速切换
- 针对各种应用和逻辑功能选择的电路灵活性
- **TTL** 兼容二极管钳位输入
- 标准电源电压

支持工业应用

- 受控基线
- 一个组装和测试场所
- 一个制造场所
- 支持扩展 (**-40°C** 至 **125°C**) 温度范围 ⁽¹⁾
- 延长的产品生命周期
- 延长的产品变更通知
- 产品可追溯性

D 封装
(顶视图)



(1) 可定制工作温度范围

说明/订购信息

SN56472 双路外设驱动器可与系列 **SN7452B** 和系列 **SN75462** 进行功能互换, 但是被设计用于要求更高击穿电压的系统。此系统以稍慢于系列 **75452B** 系列产品的开关速度为代价提供高于这些系列产品所能够提供的击穿电压 (与系列 **SN75462** 限值一样)。典型应用包括高速逻辑缓冲器, 电源驱动器, 中继驱动器, 灯驱动器, MOS 驱动器, 线路驱动器和存储器驱动器。

SN65472 是一个双路外设 **NAND** 驱动器 (假定为正逻辑电路), 逻辑门的输出在内部被连接至 **npn** 输出晶体管的底部。

这个器件的运行温度范围为 **-40°C** 至 **125°C**。



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

PRODUCTION DATA information is current as of publication date. Products conform to specifications per the terms of the Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

Copyright © 2013, Texas Instruments Incorporated
English Data Sheet: [SLRS061](#)



This integrated circuit can be damaged by ESD. Texas Instruments recommends that all integrated circuits be handled with appropriate precautions. Failure to observe proper handling and installation procedures can cause damage.


ESD damage can range from subtle performance degradation to complete device failure. Precision integrated circuits may be more susceptible to damage because very small parametric changes could cause the device not to meet its published specifications.

ORDERING INFORMATION⁽¹⁾

T _J	PACKAGE ⁽²⁾		ORDERABLE PART NUMBER	TOP-SIDE MARKING	VID NUMBER
-40°C to 125°C	SOIC - D	Tape of 75	SN65472DEP	65472	V62/13618-01XE-T
		Reel of 2500	SN65472DREP	65472	V62/13618-01XE


- (1) For the most current package and ordering information, see the Package Option Addendum at the end of this document, or see the TI website at www.ti.com.
(2) Package drawings, thermal data, and symbolization are available at www.ti.com/packaging.

LOGIC SYMBOL



This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

LOGIC DIAGRAM (POSITIVE LOGIC)




**Table 1. FUNCTION TABLE
(EACH DRIVER)**

INPUTS		Y ⁽¹⁾
A	B	
L	L	H (Off state)
L	H	H (Off state)
H	L	H (Off state)
H	H	L (On state)

(1) positive logic: $Y = \overline{A}\overline{B}$ or $\overline{A} + \overline{B}$

SCHEMATIC (EACH DRIVER)



Resistor values shown are nominal.

ABSOLUTE MAXIMUM RATINGS⁽¹⁾

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V _{CC}	Supply voltage range ⁽²⁾		7	V
V _I	Input voltage		5.5	V
	Inter-emitter voltage ⁽³⁾		5.5	V
V _O	Off-state output voltage		70	V
I _O	Continuous collector or output current ⁽⁴⁾		400	mA
	Peak collector or output current (t _w ≤ 10 ms, duty cycle ≤ 50%) ⁽⁴⁾		500	mA
T _J	Absolute maximum junction temperature range	–40	150	°C
T _{stg}	Storage temperature range	–65	150	°C

- (1) Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
- (2) Voltage values are with respect to the network GND, unless otherwise specified.
- (3) This is the voltage between two emitters, A and B.
- (4) Both halves of these dual circuits may conduct rated current simultaneously; however, power dissipation averaged over a short time interval must fall within the continuous dissipation rating.

THERMAL INFORMATION

THERMAL METRIC ⁽¹⁾		SN65472-EP	UNITS
		D	
		8 PINS	
θ _{JA}	Junction-to-ambient thermal resistance ⁽²⁾	115.3	°C/W
θ _{JCTop}	Junction-to-case (top) thermal resistance ⁽³⁾	59.7	
θ _{JB}	Junction-to-board thermal resistance ⁽⁴⁾	56.2	
ψ _{JT}	Junction-to-top characterization parameter ⁽⁵⁾	13.5	
ψ _{JB}	Junction-to-board characterization parameter ⁽⁶⁾	55.6	
θ _{JCbot}	Junction-to-case (bottom) thermal resistance ⁽⁷⁾	N/A	

- (1) 有关传统和全新热度的更多信息，请参阅 *IC 封装热量量* 应用报告（文献号：ZHCA543）。
- (2) 在 JESD51-2a 描述的环境中，按照 JESD51-7 的规定，在一个 JEDEC 标准高 K 电路板上进行仿真，从而获得自然对流条件下的结至环境热阻。
- (3) 通过在封装顶部模拟一个冷板测试来获得结至芯片外壳（顶部）的热阻。不存在特定的 JEDEC 标准测试，但可在 ANSI SEMI 标准 G30-88 中找到内容接近的说明。
- (4) 按照 JESD51-8 中的说明，通过在配有用于控制 PCB 温度的环形冷板夹具的环境中进行仿真，以获得结至电路板的热阻。
- (5) 结至顶部的特征参数，(ψ_{JT})，估算真实系统中器件的结温，并使用 JESD51-2a（第 6 章和第 7 章）中描述的程序从仿真数据中提取出该参数以便获得 θ_{JA}。
- (6) 结至电路板的特征参数，(ψ_{JB})，估算真实系统中器件的结温，并使用 JESD51-2a（第 6 章和第 7 章）中描述的程序从仿真数据中提取出该参数以便获得 θ_{JA}。
- (7) 通过在外露（电源）焊盘上进行冷板测试仿真来获得结至芯片外壳（底部）热阻。不存在特定的 JEDEC 标准测试，但可在 ANSI SEMI 标准 G30-88 中找到了内容接近的说明。

RECOMMENDED OPERATING CONDITIONS

		MIN	NOM	MAX	UNIT
V _{CC}	Supply voltage	4.75	5	5.25	V
V _{IH}	High-level input voltage	2.1			V
V _{IL}	Low-level input voltage			0.8	V
T _A	Operating free-air temperature range	–40		85	°C
T _J	Operating virtual junction temperature	–40		125	°C

ELECTRICAL CHARACTERISTICS

These specifications apply for $-40^{\circ}\text{C} \leq T_J \leq 125^{\circ}\text{C}$ (unless otherwise noted)


PARAMETER	TEST CONDITIONS	MIN	TYP ⁽¹⁾	MAX	UNIT
V_{IK} Input clamp voltage	$V_{CC} = 4.75\text{ V}$, $I_I = -12\text{ mA}$		-1.2	-1.5	V
I_{OH} High-level output current	$V_{CC} = 4.75\text{ V}$, $V_{IH} = 2\text{ V}$, $V_{OH} = 70\text{ V}$			270	μA
V_{OL} Low level output voltage	$V_{CC} = 4.75\text{ V}$, $V_{IL} = 0.8\text{ V}$, $I_{OL} = 100\text{ mA}$		0.25	0.4	V
	$V_{CC} = 4.75\text{ V}$, $V_{IL} = 0.8\text{ V}$, $I_{OL} = 300\text{ mA}$		0.5	0.75	
I_I Input current at maximum input voltage	$V_{CC} = 5.25\text{ V}$, $V_I = 5.5\text{ V}$			1	mA
I_{IH} High-level input current	$V_{CC} = 5.25\text{ V}$, $V_I = 2.4\text{ V}$			44	μA
I_{IL} Low-level input current	$V_{CC} = 5.25\text{ V}$, $V_I = 0.4\text{ V}$		-1	-1.6	mA
I_{CCH} Supply current, outputs high	$V_{CC} = 5.25\text{ V}$, $V_I = 5\text{ V}$		13	17	mA
I_{CCL} Supply current, outputs low	$V_{CC} = 5.25\text{ V}$, $V_I = 0$		61	76	mA

(1) All typical values are at $V_{CC} = 5\text{ V}$, $T_A = 25^{\circ}\text{C}$.

SWITCHING CHARACTERISTICS

$V_{CC} = 5\text{ V}$, $T_A = 25^{\circ}\text{C}$, over operating free-air temperature range (unless otherwise noted)


PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
t_{PLH} Propagation delay time, low-to-high-level output	$I_O \approx 200\text{ mA}$, $C_L = 15\text{ pF}$, $R_L = 50\text{ }\Omega$, see Figure 2		45	65	ns
t_{PHL} Propagation delay time, high-to-low-level output	$I_O \approx 200\text{ mA}$, $C_L = 15\text{ pF}$, $R_L = 50\text{ }\Omega$, see Figure 2		30	50	ns
t_{TLH} Transition time, low-to-high-level output	$I_O \approx 200\text{ mA}$, $C_L = 15\text{ pF}$, $R_L = 50\text{ }\Omega$, see Figure 2		13	25	ns
t_{THL} Transition time, high-to-low-level output	$I_O \approx 200\text{ mA}$, $C_L = 15\text{ pF}$, $R_L = 50\text{ }\Omega$, see Figure 2		10	20	ns
V_{OH} High level output voltage after switching	$V_S = 55\text{ V}$, $I_O \approx 300\text{ mA}$, see Figure 3	$V_S - 18$			mV



- (1) See Datasheet for Absolute Maximum and minimum Recommended Operating Conditions.
- (2) Silicon operating life design goal is 10 years at 105°C junction temperature (does not include package interconnect life).


Figure 1. SN65472-EP Wirebond Life Derating Chart

PARAMETER MEASUREMENT INFORMATION



- NOTES: A. The pulse generator has the following characteristics: $\text{PRR} \leq 1\ \text{MHz}$, $Z_O \approx 50\ \Omega$.
 B. C_L includes probe and jig capacitance.

Figure 2. Switching Times



- NOTES: A. The pulse generator has the following characteristics: $\text{PRR} \leq 12.5\ \text{kHz}$, $Z_O \approx 50\ \Omega$.
 B. C_L includes probe and jig capacitance.

Figure 3. Latch-Up Test

PACKAGING INFORMATION

Orderable part number	Status (1)	Material type (2)	Package Pins	Package qty Carrier	RoHS (3)	Lead finish/ Ball material (4)	MSL rating/ Peak reflow (5)	Op temp (°C)	Part marking (6)
SN65472DEP	Active	Production	SOIC (D) 8	75 TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472
SN65472DEP.A	Active	Production	SOIC (D) 8	75 TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472
SN65472DREP	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472
SN65472DREP.A	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472
V62/13618-01XE	Active	Production	SOIC (D) 8	2500 LARGE T&R	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472
V62/13618-01XE-T	Active	Production	SOIC (D) 8	75 TUBE	Yes	NIPDAU	Level-1-260C-UNLIM	-40 to 85	65472

⁽¹⁾ **Status:** For more details on status, see our [product life cycle](#).

⁽²⁾ **Material type:** When designated, preproduction parts are prototypes/experimental devices, and are not yet approved or released for full production. Testing and final process, including without limitation quality assurance, reliability performance testing, and/or process qualification, may not yet be complete, and this item is subject to further changes or possible discontinuation. If available for ordering, purchases will be subject to an additional waiver at checkout, and are intended for early internal evaluation purposes only. These items are sold without warranties of any kind.

⁽³⁾ **RoHS values:** Yes, No, RoHS Exempt. See the [TI RoHS Statement](#) for additional information and value definition.

⁽⁴⁾ **Lead finish/Ball material:** Parts may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.


⁽⁵⁾ **MSL rating/Peak reflow:** The moisture sensitivity level ratings and peak solder (reflow) temperatures. In the event that a part has multiple moisture sensitivity ratings, only the lowest level per JEDEC standards is shown. Refer to the shipping label for the actual reflow temperature that will be used to mount the part to the printed circuit board.

⁽⁶⁾ **Part marking:** There may be an additional marking, which relates to the logo, the lot trace code information, or the environmental category of the part.

Multiple part markings will be inside parentheses. Only one part marking contained in parentheses and separated by a "~" will appear on a part. If a line is indented then it is a continuation of the previous line and the two combined represent the entire part marking for that device.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.




D0008A

PACKAGE OUTLINE

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



4214825/C 02/2019


NOTES:

1. Linear dimensions are in inches [millimeters]. Dimensions in parenthesis are for reference only. Controlling dimensions are in inches. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed .006 [0.15] per side.
4. This dimension does not include interlead flash.
5. Reference JEDEC registration MS-012, variation AA.


D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



LAND PATTERN EXAMPLE
EXPOSED METAL SHOWN
SCALE:8X



SOLDER MASK DETAILS

4214825/C 02/2019

NOTES: (continued)

6. Publication IPC-7351 may have alternate designs.


7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.

EXAMPLE STENCIL DESIGN

D0008A

SOIC - 1.75 mm max height

SMALL OUTLINE INTEGRATED CIRCUIT



SOLDER PASTE EXAMPLE
BASED ON .005 INCH [0.125 MM] THICK STENCIL
SCALE:8X

4214825/C 02/2019

NOTES: (continued)

8. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
9. Board assembly site may have different recommendations for stencil design.

重要通知和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、与某特定用途的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他安全、安保法规或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的相关应用。严禁以其他方式对这些资源进行复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。对于因您对这些资源的使用而对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，您将全额赔偿，TI 对此概不负责。

TI 提供的产品受 [TI 销售条款](#)、[TI 通用质量指南](#) 或 [ti.com](https://www.ti.com) 上其他适用条款或 TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。除非德州仪器 (TI) 明确将某产品指定为定制产品或客户特定产品，否则其产品均为按确定价格收入目录的标准通用器件。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

版权所有 © 2025，德州仪器 (TI) 公司

最后更新日期：2025 年 10 月