

CSD19505KCS 80V N 沟道 NexFET™ 功率 MOSFET

1 特性


- 超低 Q_g 和 Q_{gd}
- 低热阻
- 雪崩级
- 无铅端子镀层
- 符合 RoHS
- 无卤素
- TO-220 塑料封装

2 应用

- 次级侧同步整流器
- 电机控制

3 说明

这款 80V、 $2.6m\Omega$ 、TO-220 NexFET™ 功率 MOSFET 旨在用于更大限度地降低功率转换应用中的损耗。



产品概要

$T_A = 25^\circ\text{C}$		典型值		单位
V_{DS}	漏源电压	80		V
Q_g	栅极电荷总量 (10V)	76		nC
Q_{gd}	栅漏栅极电荷	11		nC
$R_{DS(on)}$	漏源导通电阻	$V_{GS} = 6V$	2.9	$m\Omega$
		$V_{GS} = 10V$	2.6	$m\Omega$
$V_{GS(th)}$	阈值电压	2.6		V

订购信息⁽¹⁾


器件	封装	介质	数量	运输
CSD19505KCS	TO-220 塑料封装	管装	50	管装

(1) 如需了解所有可用封装，请参阅数据表末尾的可订购产品附录。


绝对最大额定值

$T_A = 25^\circ\text{C}$		值	单位
V_{DS}	漏源电压	80	V
V_{GS}	栅源电压	± 20	V
I_D	持续漏极电流 (受封装限制)	150	A
	持续漏极电流 (受器件限制), $T_C = 25^\circ\text{C}$ 时测得	208	
	持续漏极电流 (受器件限制), $T_C = 100^\circ\text{C}$ 时测得	147	
I_{DM}	脉冲漏极电流 ⁽¹⁾	400	A
P_D	功率耗散	300	W
T_J , T_{stg}	工作结温和贮存温度范围	-55 至 175	$^\circ\text{C}$
E_{AS}	雪崩能量, 单脉冲 $I_D = 101A$, $L = 0.1mH$, $R_G = 25\Omega$	510	mJ

(1) 最大 $R_{\theta JC} = 0.5^\circ\text{C/W}$, 脉冲持续时间 $\leq 100 \mu s$, 占空比 $\leq 1\%$



$R_{DS(on)}$ 与 V_{GS} 之间的关系



栅极电荷



Table of Contents

1 特性.....	1	5.2 Documentation Support.....	7
2 应用.....	1	5.3 接收文档更新通知.....	7
3 说明.....	1	5.4 支持资源.....	7
4 Specifications.....	3	5.5 Trademarks.....	7
4.1 Electrical Characteristics.....	3	5.6 静电放电警告.....	7
4.2 Thermal Information.....	3	5.7 术语表.....	7
4.3 Typical MOSFET Characteristics.....	4	6 Revision History.....	7
5 Device and Documentation Support.....	7	7 Mechanical, Packaging, and Orderable Information....	8
5.1 第三方产品免责声明.....	7		

4 Specifications

4.1 Electrical Characteristics

(T_A = 25°C unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT	
STATIC CHARACTERISTICS							
BV _{DSS}	Drain-to-Source Voltage	V _{GS} = 0V, I _D = 250 μ A	80			V	
I _{DSS}	Drain-to-Source Leakage Current	V _{GS} = 0V, V _{DS} = 64V	1			μ A	
I _{GSS}	Gate-to-Source Leakage Current	V _{DS} = 0V, V _{GS} = 20V	100			nA	
V _{GS(th)}	Gate-to-Source Threshold Voltage	V _{DS} = V _{GS} , I _D = 250 μ A	2.2	2.6	3.2	V	
R _{DS(on)}	Drain-to-Source On-Resistance	V _{GS} = 6V, I _D = 100A	2.9			mΩ	
		V _{GS} = 10V, I _D = 100A	2.6			mΩ	
g _{fs}	Transconductance	V _{DS} = 8V, I _D = 100A	262			S	
DYNAMIC CHARACTERISTICS							
C _{iss}	Input Capacitance	V _{GS} = 0V, V _{DS} = 40V, f = 1MHz	6090			7820	pF
C _{oss}	Output Capacitance		1600			2080	pF
C _{rss}	Reverse Transfer Capacitance		26			34	pF
R _G	Series Gate Resistance	V _{DS} = 40V, I _D = 100A	1.4			2.8	Ω
Q _g	Gate Charge Total (10V)		76				nC
Q _{gd}	Gate Charge Gate to Drain		11				nC
Q _{gs}	Gate Charge Gate to Source		25				nC
Q _{g(th)}	Gate Charge at V _{th}		15				nC
Q _{oss}	Output Charge	V _{DS} = 40V, V _{GS} = 0V	214				nC
t _{d(on)}	Turn On Delay Time	V _{DS} = 50V, V _{GS} = 10V, I _{DS} = 100A, R _G = 0Ω	31				ns
t _r	Rise Time		16				ns
t _{d(off)}	Turn Off Delay Time		62				ns
t _f	Fall Time		6				ns
DIODE CHARACTERISTICS							
V _{SD}	Diode Forward Voltage	I _{SD} = 100A, V _{GS} = 0V	0.9			1.1	V
Q _{rr}	Reverse Recovery Charge	V _{DS} = 40V, I _F = 100A,	400				nC
t _{rr}	Reverse Recovery Time	di/dt = 300A/ μ s	88				ns




4.2 Thermal Information

(T_A = 25°C unless otherwise stated)

THERMAL METRIC		MIN	TYP	MAX	UNIT
R _{θJC}	Junction-to-Case Thermal Resistance			0.5	°C/W
R _{θJA}	Junction-to-Ambient Thermal Resistance			62	

4.3 Typical MOSFET Characteristics

($T_A = 25^\circ\text{C}$ unless otherwise stated)






图 4-4. Gate Charge




图 4-5. Capacitance




图 4-6. Threshold Voltage vs Temperature




图 4-7. On-State Resistance vs Gate-to-Source Voltage




图 4-8. Normalized On-State Resistance vs Temperature




图 4-9. Typical Diode Forward Voltage




图 4-10. Maximum Safe Operating Area




图 4-11. Single Pulse Unclamped Inductive Switching




图 4-12. Maximum Drain Current vs Temperature

5 Device and Documentation Support

5.1 第三方产品免责声明

TI 发布的与第三方产品或服务有关的信息，不能构成与此类产品或服务或保修的适用性有关的认可，不能构成此类产品或服务单独或与任何 TI 产品或服务一起的表示或认可。

5.2 Documentation Support

5.2.1 Related Documentation

5.3 接收文档更新通知

要接收文档更新通知，请导航至 ti.com 上的器件产品文件夹。点击 [通知](#) 进行注册，即可每周接收产品信息更改摘要。有关更改的详细信息，请查看任何已修订文档中包含的修订历史记录。

5.4 支持资源

[TI E2E™ 中文支持论坛](#) 是工程师的重要参考资料，可直接从专家处获得快速、经过验证的解答和设计帮助。搜索现有解答或提出自己的问题，获得所需的快速设计帮助。

链接的内容由各个贡献者“按原样”提供。这些内容并不构成 TI 技术规范，并且不一定反映 TI 的观点；请参阅 TI 的 [使用条款](#)。

5.5 Trademarks

NexFET™ and TI E2E™ are trademarks of Texas Instruments.

所有商标均为其各自所有者的财产。

5.6 静电放电警告



静电放电 (ESD) 会损坏这个集成电路。德州仪器 (TI) 建议通过适当的预防措施处理所有集成电路。如果不遵守正确的处理和安装程序，可能会损坏集成电路。

ESD 的损坏小至导致微小的性能降级，大至整个器件故障。精密的集成电路可能更容易受到损坏，这是因为非常细微的参数更改都可能会导致器件与其发布的规格不相符。

5.7 术语表

[TI 术语表](#) 本术语表列出并解释了术语、首字母缩略词和定义。

6 Revision History

Changes from Revision B (October 2014) to Revision C (April 2024)	Page
---	------

- | | |
|--------------------------------|---|
| • 更新了整个文档中的表格、图和交叉参考的编号格式..... | 1 |
|--------------------------------|---|

Changes from Revision A (January 2014) to Revision B (October 2014)	Page
---	------

- | | |
|---|---|
| • 更新了脉冲漏极电流条件..... | 1 |
| • Updated the SOA in 图 4-10 | 4 |

Changes from Revision * (January 2014) to Revision A (February 2014)	Page
--	------

- | | |
|---------------------------------------|---|
| • 增加了脉冲漏极电流限值..... | 1 |
| • Updated 图 4-9 | 4 |

7 Mechanical, Packaging, and Orderable Information

The following pages include mechanical packaging and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.

PACKAGING INFORMATION

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead finish/ Ball material (6)	MSL Peak Temp (3)	Op Temp (°C)	Device Marking (4/5)	Samples
CSD19505KCS	ACTIVE	TO-220	KCS	3	50	RoHS-Exempt & Green	SN	N / A for Pkg Type	-55 to 175	CSD19505KCS	Samples

⁽¹⁾ The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

⁽²⁾ **RoHS:** TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (Cl) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

⁽³⁾ MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

⁽⁴⁾ There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

⁽⁵⁾ Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

⁽⁶⁾ Lead finish/Ball material - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

TUBE



*All dimensions are nominal

Device	Package Name	Package Type	Pins	SPQ	L (mm)	W (mm)	T (μm)	B (mm)
CSD19505KCS	KCS	TO-220	3	50	534.5	33	7000	3.4
CSD19505KCS	KCS	TO-220	3	50	532	34.1	700	9.6




PACKAGE OUTLINE

KCS0003B

TO-220 - 19.65 mm max height

TO-220



4222214/B 08/2018

NOTES:

1. Dimensions are in millimeters. Any dimension in brackets or parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M.
2. This drawing is subject to change without notice.
3. Reference JEDEC registration TO-220.

EXAMPLE BOARD LAYOUT

KCS0003B

TO-220 - 19.65 mm max height

TO-220



LAND PATTERN EXAMPLE
NON-SOLDER MASK DEFINED
SCALE:15X

4222214/B 08/2018

重要声明和免责声明

TI“按原样”提供技术和可靠性数据（包括数据表）、设计资源（包括参考设计）、应用或其他设计建议、网络工具、安全信息和其他资源，不保证没有瑕疵且不做任何明示或暗示的担保，包括但不限于对适销性、某特定用途方面的适用性或不侵犯任何第三方知识产权的暗示担保。

这些资源可供使用 TI 产品进行设计的熟练开发人员使用。您将自行承担以下全部责任：(1) 针对您的应用选择合适的 TI 产品，(2) 设计、验证并测试您的应用，(3) 确保您的应用满足相应标准以及任何其他功能安全、信息安全、监管或其他要求。

这些资源如有变更，恕不另行通知。TI 授权您仅可将这些资源用于研发本资源所述的 TI 产品的应用。严禁对这些资源进行其他复制或展示。您无权使用任何其他 TI 知识产权或任何第三方知识产权。您应全额赔偿因在这些资源的使用中对 TI 及其代表造成的任何索赔、损害、成本、损失和债务，TI 对此概不负责。

TI 提供的产品受 [TI 的销售条款](#) 或 [ti.com](#) 上其他适用条款/TI 产品随附的其他适用条款的约束。TI 提供这些资源并不会扩展或以其他方式更改 TI 针对 TI 产品发布的适用的担保或担保免责声明。

TI 反对并拒绝您可能提出的任何其他或不同的条款。

邮寄地址：Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024，德州仪器 (TI) 公司