

# **1.06 Gbps LVDS Buffer / Repeater (DS10BR150) Evaluation Kit**

## ***USER MANUAL***

**Part Number: DS10BR150EVK NOPB**

For the latest documents concerning these products and evaluation kit, visit [lvds.national.com](http://lvds.national.com). Schematics and gerber files are also available at [lvds.national.com](http://lvds.national.com).

## Table of Contents

Table of Contents .....	2
Overview .....	3
DS10BR150EVK Description.....	3
DS10BR150 Evaluation .....	4
Typical Performance .....	5


## Overview

The DS10BR150EVK is an evaluation kit designed for demonstrating performance of the 1.06 Gbps LVDS Buffer / Repeater (DS10BR150).

The purpose of this document is to: familiarize you with the DS10BR150EVK, suggest the test setup procedures and instrumentation, and guide you through some typical measurements that demonstrate performance of the device in typical applications.

## DS10BR150EVK Description

Figure 1 shows the top layer drawing of the PCB with the silkscreen annotations. It is a small six-layer PCB that has a single-device layout capable of demonstrating performance and all features of the DS10BR150.




**Figure 1.** DS10BR150EVK

## DS10BR150 Evaluation

This section provides recommended test setup procedure for the device evaluation. Figure 2 depicts a typical setup and instrumentation you may use for the device evaluation.

1. Apply the power to the device (3.3V typical) between VDD2 and GND connectors.
2. Connect a signal source (i.e. signal generator or an LVDS driver) to the input (R1 label) on the board and adjust the signal parameters (VOH, VOL, VCM) so that they comply with the device input recommendations.
3. Connect the output (U1 label) to an oscilloscope and view the output signals with an oscilloscope that has the bandwidth of at least 3 GHz.



**Figure 2.** DS10BR150 Test Setup Example

## Typical Performance

This section of the User Manual shows a typical eye diagram you can expect to see when evaluating the DS10BR150EVK.




Figure 2. DS10BR150 1.06 Gbps PRBS-7 Output Eye Diagram

6

5

4

3

2

1

REVISION RECORD			
LTR	ECO NO:	APPROVED:	DATE:
0	INITIAL RELEASE		

D

D

C


C

B

B

A

A



- M1
- M2
- M3
- M4
- M5
- M6
- M7
- M8
- M9
- M10

COMPANY: NATIONAL SEMICONDUCTOR

TITLE: SCHEMATIC  
DS25BR150/DS10BR150 EVK , ROHS

CODE:	SIZE: B	DRAWING NO: S-05800	REV: 0
-------	------------	------------------------	-----------

**Enercon** Technologies  
 25 NorthBrook Drive  
 Gray, Maine 04039  
 U.S.A.

DRAWN: ACF      DATED: 2/27/07

<b>ENERCON - BILL OF MATERIALS</b>		TITLE: <b>NATIONAL SEMICONDUCTOR PCBA, DS10BR150EVK, ROHS</b>		PL Number: <b>Z3054-01</b>	Rev: <b>0</b>	Rev By:	Rev Date: <b>2/27/2007</b>	PL Status: <b>Released</b>
Main Product: <b>PCBA, DS10BR150 EVK</b>				Responsible Eng/Mgr:		Creator: <b>Arlene Fox</b>		Creation Date: <b>2/27/2007</b>

Item	Part Type	Part Number/Value	Mfg	NoSub	Description	Qty	SMT	Ref Des	Notes	Rev
1	PCB	P-05797R0			DS10/25BR150K: 1.25x2.03x.060in, 6 layer	1			Bd: (31.75x 51.43mm)	0
2										
3	IC	DS10BR150	NAT			1		U1	CUSTOMER SUPPLIED	0
4										
5	CAP	0402YD104KAT	AVX		.1µF, 16V, ±10%, 0402, Ceramic, X5R, Pb-Free	1	X	C2		0
	<ALT>	ECJ-0EB1C104K	PANA		.1µF, 16V, ±10%, 0402, Ceramic, X5R, Pb-Free					
6	CAP	ECJ-3YB0J106K	PANA		10µF, 6.3V, ±10%, 1206, Ceramic, X5R, Pb-Free	1	X	C4		0
	<ALT>	12066D106KAT	AVX		10µF, 6.3V, ±10%, 1206, Ceramic, X5R, Pb-Free					
	<ALT>	C1206C106K9PAC	KEMET		10µF, 6.3V, ±10%, 1206, Ceramic, X5R, Pb-Free					
7										0
8	CONN	1287-ST	KEYSTONE		Faston, Male, .250x.032, Pb-Free	2		TAB1,3	VDD2, GND	0
9	CONN	142-0701-851	EMERSON		SMA, Jack Receptacle, 50 OHM, Pb-Free	4		SMAL,2,5,6		0
10										
11	STENCL	T-05801R1	ENERCON		STENCIL FABRICATION, TOP, DS25BR150/DS10BR150 EVK	1				0
12	STENCL	T-05802R1	ENERCON		STENCIL FABRICATION, BOTTOM, DS25BR150/DS10BR15...	1				0
13										
14	REF	C-05798R0	ENERCON		FABRICATION DWG, DS25BR150/DS10BR150 EVK, ROHS					0
15	REF	C-05799R1	ENERCON		PALLET DWG, DS25BR150/DS10BR150 EVK					0
16	REF	S-05800R0	ENERCON		SCHEMATIC, DS25BR150/DS10BR150 EVK					0
17										

<b>ENERCON - BILL OF MATERIALS</b>	TITLE: NATIONAL SEMICONDUCTOR PCBA, DS10BR150EVK, ROHS	PL Number: Z3054-01	Rev: 0	Rev By:	Rev Date: 2/27/2007	PL Status: Released
		Responsible Eng/Mgr:	Creator: Arlene Fox	Creation Date: 2/27/2007		
Main Product: PCBA, DS10BR150 EVK						

Notes:

DO NOT STUFF:

R1,2

U2

C1,3

TAB2

SMA3,4,7,8

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2012, Texas Instruments Incorporated