

Bill of Materials

TI DESIGNS

TIDA-00885

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint
1	11	3p3_LM_TP, 3p3_TPS_TP,	White	Test Point, Compact, White, TH	Keystone	5007	White Compact
2	1	C1_LF	560pF	CAP, CERM, 1800pF, 100V, +/-5%, X7R, 0603	Kemet	C0603C561K5RACTU	0603
3	1	C2_LF	0.047uF	CAP, CERM, 0.056uF, 16V, +/-10%, X7R, 0603	MuRata	GRM188R71H473KA61D	0603
4	1	C4_LF	6800pF	CAP, CERM, 6800 pF, 50 V, +/- 10%, X7R, 0603	MuRata	GRM188R71H682KA01D	0603
5	2	C7, C10	1uF	CAP, CERM, 1uF, 16V, +/-10%, X7R, 0603	TDK	C1608X7R1C105K	0603
6	8	C8, C9, C11, C12, C16,	0.1uF	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	AVX	0603YC104JAT2A	0603
7	6	C13, C14, C15, C17, C18,	100pF	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0,	MuRata	GRM1535C1H101JDD5D	0402
8	6	C21, C22, C23, C24, C25,	10uF	CAP, CERM, 10uF, 10V, +/-10%, C0G/NP0, 0603	TDK	C1608X5R1A106M	0603
9	1	C27	1uF	CAP, CERM, 1 uF, 6.3 V, +/- 10%, X5R, 0603	TDK	C1608X5R0J105K	0603
10	1	Cbias	1uF	CAP, CERM, 1 uF, 16 V, +/- 10%, X7R, 0603_095	Wurth Elektronik	885012206052	0603_095
11	1	Cboot	0.47uF	CAP, CERM, 0.47 uF, 10 V, +/- 10%, X5R, 0402	TDK	C1005X5R1A474K050BB	0402
12	1	Cff	10pF	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0,	MuRata	GRM1885C1H100JA01D	0603
13	1	Cin1	0.47uF	CAP, CERM, 0.47 uF, 50 V, +/- 10%, X7R, 0603	TDK	C1608X7R1H474K080A C	0603
14	2	Cin, Cin_0	10uF	CAP, CERM, 10 uF, 25 V, +/- 10%, X5R, 0805	MuRata	GRM219R61E106KA12D	0805
15	3	Cout0, Cout1, Cout2	22uF	CAP, CERM, 22 uF, 16 V, +/- 10%, X5R, 0805	TDK	C2012X5R1C226K125A C	0805
16	1	Css	3300pF	CAP, CERM, 3300 pF, 50 V, +/- 5%, C0G/NP0, 0603	MuRata	GRM1885C1H332JA01D	0603
17	1	CVcc	2.2uF	CAP, CERM, 2.2 uF, 10 V, +/- 10%, X5R, 0402	TDK	C1005X5R1A225K050BC	0402
18	1	D1	Green	LED, Green, SMD	Lite-On	LTST-C190GKT	1.6x0.8x0.8mm
19	4	L1, L2, L3, L4	18nH	Inductor, Multilayer, Air Core, 18 nH, 0.3 A, 0.36 ohm, SMD	MuRata	LQG15HS18NJ02D	0402 polarized
20	1	L1_LM	12uH	Inductor, Shielded Drum Core, Ferrite, 12 uH, 1.4 A, 0.16 ohm, SMD	Coilcraft	LPS5030-123MLB	LPS5030
21	1	L1_TPS	2.2uH	Inductor, Shielded, Composite, 2.2 uH, 3.7 A, 0.02	Coilcraft	XFL4020-222MEB	4x2x4mm
22	7	OSCinM, OSCinP,		Connector, SMT, End launch SMA 50 ohm	Emerson Network Power Connectivity	142-0701-851	SMA
23	1	R2_LF	150	RES, 150, 5%, 0.1 W, 0603	Vishay-Dale	CRCW0603150RJNEA	0603
24	1	R3_LF	12	RES, 270 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060312R0JNEA	0603

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	PCB Footprint
25	12	R4_LF, R12, R23, R24, R31, R36, R39, R40, R41, R42, R43, Rtps1	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	0603
26	4	R5, R6, R9, R13	12k	RES, 12k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060312K0JNEA	0603
27	4	R16, R18, R20, R22	18	RES, 18 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060318R0JNEA	0603
28	2	R19, R21	68	RES, 68 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060368R0JNEA	0603
29	4	R25, R27, R28, R30	18	RES, 18, 5%, 0.063 W, 0402	Vishay-Dale	CRCW040218R0JNED	0402
30	2	R26, R29	68	RES, 68, 5%, 0.063 W, 0402	Vishay-Dale	CRCW040268R0JNED	0402
31	2	R32, R34	49.9	RES, 49.9, 1%, 0.063 W, 0402	Vishay-Dale	CRCW040249R9FKED	0402
32	1	R37	10	RES, 10 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060310R0JNEA	0603
33	1	R38	680	RES, 680, 1%, 0.1 W, 0603	Yageo America	RC0603FR-07680RL	0603
34	1	R45	330	RES, 330 ohm, 5%, 0.1W, 0603	Yageo America	RC0603JR-07330RL	0603
35	1	Rfbb	442k	RES, 442 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW0402442KFKED	0402
36	1	Rfbb1	180k	RES, 180 k, 0.1%, 0.1 W, 0603	Yageo America	RT0603BRD07180KL	0603
37	1	Rfbbt	1.00Meg	RES, 1.00 M, 1%, 0.1 W, 0402	Panasonic	ERJ-2RKF1004X	0402
38	1	Rfbbt1	562 k	RES, 562 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW0603562KFKEA	0603
39	1	Rt	80.6k	RES, 80.6 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060380K6FKEA	0603
40	1	Rtps	0	RES, 0, 5%, 0.125 W, 0805	Vishay-Dale	CRCW08050000Z0EA	0805
41	1	U1		Dual output, 2-Phase, Stackable PMBLMX2592 test chip QFN 0.4mm-pitch 40-pin 6x6 PKG	Texas Instruments	LMX2592	RHA0040B
42	1	U2		SIMPLE SWITCHER 3.5 V to 36 V 1 A Synchronous Step-Down Voltage Converter, PWP0016G	Texas Instruments	LM43601PWPR	PWP0016G
43	1	U3		Buck Step Down Regulator with 3 to 17 V Input and 0.9 to 6 V Output, -40 to 85 degC, 16-Pin QFN (RGT), Green (RoHS & no Sb/Br)	Texas Instruments	TPS62150RGTR	RGT0016C
44	1	uWire		Header (shrouded), 100mil, 5x2, Gold plated, SMD	FCI	52601-S10-8LF	SMT Header
45	1	Y1		OSC 100.0000MHZ 3.3V +-25PPM SMD	Connor-Winfield	CWX813-100.0M	7x1.3x5mm
46	0	C1	0.1uF	CAP, CERM, 0.1uF, 16V, +/-5%, X7R, 0603	AVX	0603YC104JAT2A	0603
47	0	C2	10uF	CAP, CERM, 10uF, 10V, +/-10%, X5R, 0805	Kemet	C0805C106K8PACTU	0805
48	0	C3_LF	300pF	CAP, CERM, 3300pF, 100V, +/-5%, X7R, 0603	MuRata	GRM1885C2A301JA01D	0603
49	0	R3, R4, R7, R8, R10, R11, R14, R15	12k	RES, 12k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060312K0JNEA	0603
50	0	R16p	18	RES, 18 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060318R0JNEA	0603
51	0	R17	10	RES, 10 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW060310R0JNEA	0603
52	0	R33, R35	49.9	RES, 49.9, 1%, 0.063 W, 0402	Vishay-Dale	CRCW040249R9FKED	0402
53	0	R44, R1m1	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA	0603
54	0	R1m	0	RES, 0, 5%, 0.125 W, 0805	Vishay-Dale	CRCW08050000Z0EA	0805

IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2017, Texas Instruments Incorporated