

## ***bq20z70/bq20z75 to bq20z40/bq20z45 Change List***

Chase Richards

HVAL - Battery Management Solutions

### **ABSTRACT**

This document describes the differences between a bq20z70/bq20z75 design and a bq20z40/bq20z45 solution. Find the latest ordering information and data sheet on the World Wide Web at: <http://power.ti.com>.

### **Introduction**

The bq20z40/bq20z45 firmware has been released to enable several feature additions and improvements over the bq20z70/bq20z75. The bq20z40/bq20z45 devices are pin and footprint compatible with the bq20z70/bq20z75 devices for easy hardware upgrade.

Orderable part numbers for new devices are:

- bq20z40DBT
- bq20z40DBTR
- bq20z45DBT
- bq20z45DBTR

The latest version of the TI evaluation software is required to be able to read and write all the data flash configuration locations. The updated evaluation software can be obtained at <http://power.ti.com>.

### **Change Details**

#	CHANGE	bq20z40/bq20z45	bq20z70/bq20z75	COMMENTS
1	Added enhanced charging algorithm (satisfies JEITA specification) temperature ranges	Satisfies JEITA temperature range guidelines.	Does not satisfy JEITA temperature range guidelines.	Increased temperature safety
2	Charging voltage and charging current vary with enhanced charging algorithm (satisfies JEITA specification) temperature range	Can specify different charging voltages and charging currents for each temperature range.	Charging voltage is the same, except for the data flash name; charging current is different in pre-charge mode and during temp. throttling.	Improves safety and potential for increased cell life
3	Cell overvoltage thresholds vary with temperature range.	Can specify different cell overvoltage thresholds (1st - level and permanent failure) for each temperature range (this is part of the enhanced charging algorithm).	Only one cell overvoltage threshold. Only one PF overvoltage threshold, which is pack based rather than cell based.	Allows for enhanced customization and improves safety
4	Safety undervoltage 2nd level protection	Monitors the individual cell voltages for extreme undervoltage values (this is part of the enhanced charging algorithm).	Feature is not supported.	Improves safety
5	Added a discharge inhibit mode	If the temperature of the battery is too high, then the battery will not be allowed to start discharging.	Feature is not supported.	Improves safety

#	CHANGE	bq20z40/bq20z45	bq20z70/bq20z75	COMMENTS
6	Cell deterioration capacity limits and flags	Can specify warning and fault limits for reduced cell capacity as well as a cell life limit with flags to indicate each condition (this is part of the enhanced charging algorithm).	Feature is not supported.	Improves safety and provides more detailed battery information
7	Relative State of Charge (RSOC) improvements	Implements Impedance Track™ changes to improve RSOC performance. Added Load Select 7 (see SLUU313 for a description) which helps to improve Impedance Track™ accuracy.	Feature is not supported.	Improves gauging accuracy
8	Lifetime data	Lifetime data is recorded and is accessible through data flash or by using an extended SBS command.	Very limited lifetime data. Only accessible through data flash.	Improves data logging and troubleshooting capability
9	Manufacturer Data	Added 4 additional 19 byte data flash locations for storing manufacturing data ( <i>DF:Manuf. Block 1..4</i> ). <i>Manuf. Info 0</i> is still 31 bytes long. There is now a total of 107 bytes of Manufacturing Info storage.	Only has 31 byte <i>Manuf. Info 0</i> .	Provides enhanced customization and data storage
10	Permanent Fail status	Because of the addition of new permanent failure modes one status and two status logging registers were added. <b>SBS.PF Status 2</b> was added for status. <i>DF:Saved PF Flags 2</i> and <i>DF:Saved 1st PF Flags 2</i> was added for logging.	Only has 1 PF Status failure register and 2 logging registers.	Added to support new safety features (see change 4, 11, and 12)
11	Cell imbalance detection methods	Supports 2 mechanisms for cell imbalance detection: Active and at Rest with independent flags	Supports cell imbalance detection at Rest only	Improves safety
12	Independent temperature alarms for 2nd thermistor	Separate OTC, OTD, SOTC, and SOTD alarms and thresholds for TS1 and TS2	Only one set of alarms and thresholds	Improves safety and design customization
13	Ability to go to sleep without calibration	Enters sleep mode immediately when sleep command is received without performing calibration first (improves efficiency during manufacturing)	Calibration is always performed upon entry to sleep.	Improves efficiency during manufacturing
14	PF Fuse Blow features	New PF Fuse Blow features added. <i>DF:PF SOV Fuse Blow Delay</i> determines the length of time after a PF SOV event occurs before the fuse is blown. <i>DF:PF Min Fuse Blow Voltage</i> requires the battery be above this threshold before the fuse is blown.	Features are not supported.	Improves safety
15	Seal delay option added after sealing gauge	The <i>DF:Sealed Ship Delay</i> timer introduces a programmable delay before shutting off the FETs for ship mode after the seal commands are sent to the gauge.	Feature is not supported.	Adds convenience during production

## Summary

The following is a list of new data flash and SBS parameters added to bq20z40/bq20z45, sorted by table item. Descriptions can be found in the technical reference user's guide ([SLUU313](#)):

1. Added enhanced charging algorithm temperature ranges

- *DF:JT1*
- *DF:JT2*
- *DF:JT2a*
- *DF:JT3*
- *DF:JT4*
- **SBS:TempRange (0x72)**

2. Charging voltage and charging current vary with enhanced charging algorithm temperature range

- *DF:LT Chg Voltage*
- *DF:LT Chg Current1*
- *DF:LT Chg Current2*
- *DF:LT Chg Current3*
- *DF:ST1 Chg Voltage*
- *DF:ST1 Chg Current1*
- *DF:ST1 Chg Current2*
- *DF:ST1 Chg Current3*
- *DF:ST2 Chg Voltage*
- *DF:ST2 Chg Current1*
- *DF:ST2 Chg Current2*
- *DF:ST2 Chg Current3*
- *DF:HT Chg Voltage*
- *DF:HT Chg Current1*
- *DF:HT Chg Current2*
- *DF:HT Chg Current3*
- *DF:Cell Voltage Threshold1*
- *DF:Cell Voltage Threshold2*
- *DF:Cell Voltage Thresh Hys*

3. Cell overvoltage thresholds vary with temperature range

- *DF:LT COV Threshold*
- *DF:LT COV Recovery*
- *DF:ST COV Threshold*
- *DF:ST COV Recovery*
- *DF:HT COV Threshold*
- *DF:HT COV Recovery*
- *DF:LT SOV Threshold*
- *DF:ST SOV Threshold*
- *DF:HT SOV Threshold*

4. Safety undervoltage 2nd level protection

- *DF:SUV Threshold*
- *DF:SUV Time*

5. Added a discharge inhibit mode

- *DF:Hi Dsg Start Temp*

6. Cell deterioration capacity limits and flags

- *DF:Deterioration Warn Limit*

- *DF:Deterioration Fault Limit*
  - *DF:Cell Life Limit*
7. Relative State of Charge (RSOC) improvements
- *[OCV\_WGHT] in DF:Operation Cfg C*
  - *Option 7 in DF:Load Select*
8. Lifetime data
- *DF:Lifetime Max Cell Voltage*
  - *DF:Lifetime Min Cell Voltage*
  - *DF:Lifetime Max Pack Voltage*
  - *DF:Lifetime Min Pack Voltage*
  - *DF:Lifetime Max Chg Current*
  - *DF:Lifetime Max Dsg Current*
  - *DF:Lifetime Max Chg Power*
  - *DF:Lifetime Max Dsg Power*
  - *DF:Life Max AvgDsg Cur*
  - *DF:Life Max AvgDsg Pow*
  - *DF:Life Avg Temp*
  - **SBS:LifetimeData (0x73)**
9. Manufacturer Data
- *DF:Manuf. Block 1*
  - *DF:Manuf. Block 2*
  - *DF:Manuf. Block 3*
  - *DF:Manuf. Block 4*
  - **SBS:ManufBlock1..4 (0x6c..0x6f)**
10. Permanent Fail status
- *DF:Permanent Fail Cfg 2*
  - *DF:Saved PF Flags 2*
  - *DF:Saved 1st PF Flags 2*
  - **SBS:PFStatus2 (0x6b)**
11. Cell imbalance detection methods
- *DF:Rest CIM Current*
  - *DF:Rest CIM Fail Voltage*
  - *DF:Rest CIM Time*
  - *DF:CIM Battery Rest Time*
  - *DF:Rest CIM Check Voltage*
  - *DF:Active CIM Fail Voltage*
  - *DF:Active CIM Time*
  - *DF:Active CIM Check Voltage*
12. Independent temperature alarms for 2nd thermistor
- *DF:OT2 Chg Threshold*
  - *DF:OT2 Chg Time*
  - *DF:OT2 Chg Recovery*
  - *DF:OT2 Dsg Threshold*
  - *DF:OT2 Dsg Time*
  - *DF:OT2 Dsg Recovery*
  - *DF:SOT2 Chg Threshold*
  - *DF:SOT2 Chg Time*

- *DF:SOT2 Dsg Threshold*
  - *DF:SOT2 Dsg Time*
  - **SBS:TS1Temperature (0x5e)**
  - **SBS:TS2Temperature (0x5f)**
  - **SBS:SafetyStatus2 (0x69)**
14. PF Fuse Blow features
- *DF:PF SOV Fuse Blow Delay*
  - *DF:PF Min Fuse Blow Voltage*
15. Seal delay option added after sealing gauge
- *DF:Sealed Ship Delay*

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Broadband	<a href="http://www.ti.com/broadband">www.ti.com/broadband</a>
Digital Control	<a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Military	<a href="http://www.ti.com/military">www.ti.com/military</a>
Optical Networking	<a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Telephony	<a href="http://www.ti.com/telephony">www.ti.com/telephony</a>
Video & Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless">www.ti.com/wireless</a>

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2009, Texas Instruments Incorporated