

Filename: PMP10555_BOM_RevA.xls

Variant: 001

Generated: 10/17/2014 11:24:42 AM

PMP10555 Bill of Materials

Designator	Description	Manufacturer	PartNumber	Quantity
!PCB1	Printed Circuit Board	Any	SAT0105	1
C1, C2, C5	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E104KA01D	3
C3, C9, C10, C59	CAP, CERM, 10uF, 25V, +/-20%, X5R, 0805	MuRata	GRM21BR61E106MA73	4
C4, C73	CAP, CERM, 22uF, 6.3V, +/-20%, X5R, 0805	MuRata	GRM21BR60J226ME39L	2
C6, C16, C20, C56, C66, C70	CAP, CERM, 0.047uF, 25V, +/-10%, X7R, 0402	MuRata	GRM155R71E473KA88D	6
C7, C57	CAP, AL, 47uF, 25V, +/-20%, 0.36 ohm, SMD	Panasonic	EEE-FK1E470P	2
C8, C58	CAP, CERM, 22uF, 25V, +/-20%, X5R, 0805	MuRata	GRM21BR61E226ME44	2
C11, C12, C13, C17, C18, C19, C23, C24, C45, C46, C47, C48, C49, C50, C61, C62, C63, C67, C68, C69	CAP, CERM, 100uF, 6.3V, +/-20%, X5R, 1210	MuRata	GRM32ER60J107ME20L	20
C14, C15, C37, C44, C64, C65, C81	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E105KA12D	7
C21, C22, C25, C53, C71, C72, C74	CAP, CERM, 0.01uF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H103KA88D	7
C29	CAP, CERM, 1500pF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H152KA01D	1
C30, C79	CAP, CERM, 2200pF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H222KA01D	2
C31	CAP, CERM, 3300pF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H332KA01D	1
C32	CAP, AL, 100uF, 25V, +/-20%, 0.3 ohm, SMD	Panasonic	EEE-FC1E101P	1
C33	CAP, CERM, 330pF, 50V, +/-5%, C0G/NP0, 0402	MuRata	GRM1555C1H331JA01D	1
C34, C35, C36	CAP, CERM, 22uF, 25V, +/-10%, X5R, 1210	MuRata	GRM32ER61E226KE15L	3
C38, C51	CAP, CERM, 4700pF, 25V, +/-10%, X7R, 0402	MuRata	GRM155R71E472KA01D	2
C39	CAP, CERM, 0.1uF, 25V, +/-10%, X5R, 0402	MuRata	GRM155R61E104KA87D	1
C41, C42, C43	CAP, TA, 560uF, 2V, +/-20%, 0.003 ohm, SMD	Panasonic	EEF-GX0D561L	3
C52	CAP, CERM, 4.7uF, 16V, +/-10%, X5R, 0603	MuRata	GRM188R61C475KAAJ	1
C54	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	MuRata	GRM155R61A105KE15D	1
C55	CAP, CERM, 1000pF, 25V, +/-10%, X7R, 0603	MuRata	GRM188R71E102KA01D	1
C60	CAP, CERM, 4.7uF, 25V, +/-10%, X6S, 0805	MuRata	GRM21BC81E475KA12L	1
C78	CAP, CERM, 1800pF, 50V, +/-10%, X7R, 0402	MuRata	GRM155R71H182KA01D	1
C80	CAP, CERM, 8200pF, 25V, +/-10%, X7R, 0402	MuRata	GRM155R71E822KA01D	1
C203, C204	CAP, CERM, 100pF, 100V, +/-5%, C0G/NP0, 0603	MuRata	GRM1885C2A101JA01D	2
D1, D2	Diode, Zener, 5.1V, 300mW, SOD-523	Diodes Inc.	BZT52C5V1T-7	2
FID1, FID2, FID3, FID4, FID5, FID6	Fiducial mark. There is nothing to buy or mount.	N/A	N/A	6
H1, H2, H3, H4	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	B&F Fastener Supply	NY PMS 440 0025 PH	4

Designator	Description	Manufacturer	PartNumber	Quantity
H5, H6, H7, H8	Standoff, Hex, 0.5"L #4-40 Nylon	Keystone	1902C	4
J1	Header, 100mil, 5x2, Tin plated, TH	Sullins Connector Solutions	PEC05DAAN	1
J2, J3, J4, J7, J8, J9, J10	TERMINAL BLOCK 5.08MM VERT 2POS, TH	On-Shore Technology	ED120/2DS	7
J5, J6	Standard Banana Jack, Uninsulated	Keystone	6095	2
L1	Inductor, Shielded, Composite, 10uH, 3A, 0.084 ohm, SMD	Coilcraft	XAL4040-103MEB	1
L2, L3, L4, L9	Ferrite Bead, 5 ohm @ 100MHz, 0.7A, 0603	MuRata	BLM18BB050SN1D	4
L5, L10	Inductor, Shielded Drum Core, Ferrite, 4.7uH, 3.16A, 0.028 ohm, SMD	Würth Elektronik eiSos	7447779004	2
L6	Inductor, Shielded Drum Core, Ferrite, 3.3uH, 2.6A, 0.031 ohm, SMD	Würth Elektronik eiSos	74408943033	1
L7, L11	Inductor, Shielded Drum Core, Ferrite, 4.7uH, 2.2A, 0.045 ohm, SMD	Würth Elektronik eiSos	74408943047	2
L8	Inductor, Shielded Drum Core, Ferrite, 330nH, 27A, 0.00037 ohm, SMD	Würth Elektronik eiSos	744308033	1
L12	Inductor, Drum Core, Ferrite, 33uH, 0.64A, 0.54 ohm, SMD	Bourns	SDR0403-330KL	1
Q1	Transistor, NPN, 40V, 0.2A, SOT-23	Fairchild Semiconductor	MMBT3904	1
R1, R2, R3, R6, R7, R8	RES, 100k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603100KJNEA	6
R4	RES, 105k ohm, 0.1%, 0.1W, 0603	Yageo America	RT0603BRD07105KL	1
R5, R10, R14, R30	RES, 20.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-203-B-T5	4
R9, R29	RES, 88.7k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040288K7FKED	2
R11, R13, R15, R31, R33, R34, R35	RES, 10.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-103-B-T5	7
R12	RES, 12.6k ohm, 0.1%, 0.1W, 0603	Yageo America	RT0603BRD0712K6L	1
R16, R36	RES, 127k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW0402127KFKED	2
R17, R18	RES, 63.4k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040263K4FKED	2
R19, R23, R25, R40, R41, R42, R43, R44	RES, 49.9 ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040249R9FKED	8
R20	RES, 0 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04020000Z0ED	1
R21	RES, 0.33 ohm, 1%, 0.1W, 0603	Panasonic	ERJ-3RQFR33V	1
R22	RES, 15.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-153-B-T5	1
R24	RES, 30.0k ohm, 0.1%, 0.1W, 0603	Susumu Co Ltd	RG1608P-303-B-T5	1
R26	RES, 38.3k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040238K3FKED	1
R27	RES, 133k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW0402133KFKED	1
R28	RES, 10.5k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040210K5FKED	1
R32	RES, 45.3k ohm, 0.1%, 0.1W, 0603	Yageo America	RT0603BRD0745K3L	1
R37	RES, 84.5k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040284K5FKED	1
R38	RES, 17.4k ohm, 1%, 0.063W, 0402	Vishay-Dale	CRCW040217K4FKED	1
R39	RES, 10, 5%, 0.063 W, 0402	Vishay-Dale	CRCW040210R0JNED	1
R128, R129	RES, 68.1k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060368K1FKEA	2
R130	RES, 49.9 k, 1%, 0.1 W, 0603	Vishay-Dale	CRCW060349K9FKEA	1
R131	RES, 12.1k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW060312K1FKEA	1
TP1, TP9	Test Point, Miniature, Red, TH	Keystone	5000	2
TP2, TP10	Test Point, Miniature, Black, TH	Keystone	5001	2

Designator	Description	Manufacturer	PartNumber	Quantity
TP3, TP5, TP7, TP13, TP15, TP17, TP19, TP21, TP22, TP23, TP23	Test Point, Multipurpose, Red, TH	Keystone	5010	11
TP4, TP6, TP14, TP16, TP18	Test Point, Multipurpose, Black, TH	Keystone	5011	5
TP8, TP11, TP24, TP25, TP26, TP27, TP28	Test Point, Multipurpose, Orange, TH	Keystone	5013	7
TP12	Test Point, Miniature, SMT	Keystone	5015	1
U1, U3	Power Sequencer, 6-pin SOT-23	National Semiconductor	LM3880MF-1AA	2
U2	4.5V to 18V Input, 500mA Synchronous Step Down SWIFT Converter, DBV0005A	Texas Instruments	TPS560200DBV	1
U4, U6	4.5V to 18V Input Voltage, 3A/2A/2A Output Current Triple Synchronous Step-Down Converter, RHB0032E	Texas Instruments	TPS65261-1RHB	2
U5	TPS544B20 18V, 20A PMBUS SYNCHRONOUS BUCK CONVERTERS, RVF0040A	Texas Instruments	TPS544B20RVF	1
U7	IC, Single 2-Input Positive-OR Gate	TI	SN74AHC1G32DCK	1
U8	Single 2-Input Positive-AND Gate, DRL0005A	Texas Instruments	SN74AHC1G08DRL	1

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.