


Symbol	Count	Hole Size	Plated	Hole Type	Drill Layer Pair	Via/Pad	Pad Shape	Hole Tolerance (+)	Hole Tolerance (-)
⊗	1	39.37mil (1.000mm)	PTH	Rectangle	Top Layer - Bottom Layer	Pad	Rounded Rectangle	3.94mil (0.100mm)	3.94mil (0.100mm)
◇	2	23.62mil (0.600mm)	PTH	Slot	Top Layer - Bottom Layer	Pad	Rounded	3.00mil (0.076mm)	3.00mil (0.076mm)
▣	2	33.47mil (0.850mm)	PTH	Round	Top Layer - Bottom Layer	Pad	Rounded	3.00mil (0.076mm)	3.00mil (0.076mm)
⊗	2	39.37mil (1.000mm)	PTH	Rectangle	Top Layer - Bottom Layer	Pad	Rounded	3.94mil (0.100mm)	3.94mil (0.100mm)
▽	2	40.16mil (1.020mm)	NPTH	Round	Top Layer - Bottom Layer	Pad	Rounded	2.00mil (0.051mm)	2.00mil (0.051mm)
⊗	3	23.62mil (0.600mm)	PTH	Round	Top Layer - Bottom Layer	Pad	(Mixed)	3.00mil (0.076mm)	3.00mil (0.076mm)
□	3	43.31mil (1.100mm)	PTH	Round	Top Layer - Bottom Layer	Pad	(Mixed)	3.00mil (0.076mm)	3.00mil (0.076mm)
⊗	4	118.11mil (3.000mm)	PTH	Round	Top Layer - Bottom Layer	Pad	Rounded	3.00mil (0.076mm)	3.00mil (0.076mm)
▽	4	160.00mil (4.064mm)	NPTH	Round	Top Layer - Bottom Layer	Pad	Rounded	2.00mil (0.051mm)	2.00mil (0.051mm)
★	7	7.87mil (0.200mm)	PTH	Round	Top Layer - Bottom Layer	Via	Rounded		
☆	8	23.62mil (0.600mm)	PTH	Round	Top Layer - Bottom Layer	Pad	(Mixed)		
○	10	40.00mil (1.016mm)	PTH	Round	Top Layer - Bottom Layer	Pad	(Mixed)	3.00mil (0.076mm)	3.00mil (0.076mm)
⊗	684	8.00mil (0.203mm)	PTH	Round	Top Layer - Bottom Layer	Via	Rounded	3.00mil (0.076mm)	3.00mil (0.076mm)
⊗	3505	5.90mil (0.150mm)	PTH	Round	Top Layer - L2_GND1	Via	Rounded	0.00mil (0.000mm)	5.90mil (0.150mm)
	4237 Total								

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #:PROC176A	REV: A	SUN REV: 2993 [Scheduled for deletion]
LAYER NAME = Drill Drawing	TID #: N/A		
PLOT NAME = Fabrication Drawing 2	GENERATED : 14-03-2024 18:31:40	TEXAS INSTRUMENTS	