



www.ti.com SLPS443 – JUNE 2013

P-Channel NexFET™ Power MOSFET

Check for Samples: CSD25213W10

FEATURES

- Ultra Low Qg and Qgd
- Small Footprint 1mm x 1mm
- Low Profile 0.62mm Height
- Pb Free
- Gate-Source Voltage Clamp
- Gate ESD Protection
- RoHS Compliant
- Halogen Free


APPLICATIONS


- Battery Management
- Load Switch
- Battery Protection

DESCRIPTION

The device has been designed to deliver the lowest on resistance and gate charge in the smallest outline possible with excellent thermal characteristics in an ultra low profile.

Top View





PRODUCT SUMMARY

| V _{DS} | Drain to Source Voltage | -20 | V | |
|---------------------|---------------------------|-------------------------|----|----|
| Q_g | Gate Charge Total (4.5V) | 2.2 | | nC |
| Q_{gd} | Gate Charge Gate to Drain | 0.14 | nC | |
| R _{DS(on)} | Drain to Source On | $V_{GS} = -2.5V$ | 54 | mΩ |
| | Resistance | V _{GS} = -4.5V | 39 | mΩ |
| V _{GS(th)} | Threshold Voltage | -0.85 | V | |


ORDERING INFORMATION

| Device | Package | Media | Qty | Ship | |
|-------------|------------------------------|-------------|------|------------------|--|
| CSD25213W10 | 1 x 1 Wafer Level Package | 7-inch reel | 3000 | Tape and Reel | |

ABSOLUTE MAXIMUM RATINGS

| T _A = 25°C | unless otherwise stated | VALUE | UNIT |
|-----------------------------------|--|------------|------|
| V _{DS} | Drain to Source Voltage | -20 | ٧ |
| V _{GS} | Gate to Source Voltage | -6.0 | V |
| I _D | Continuous Drain Current, $T_A = 25^{\circ}C^{(1)}$ | -1.6 | Α |
| I _{DM} | Pulsed Drain Current, T _A = 25°C ⁽²⁾ | -16 | Α |
| I _G | Continuous Gate Clamp Current ⁽³⁾ | -5 | mA |
| P _D | Power Dissipation ⁽¹⁾ | 1 | W |
| T _J , T _{STG} | Operating Junction and Storage Temperature Range | -55 to 150 | °C |

- (1) $R_{\theta JA} = 75^{\circ}\text{C/W}$ on 1in^2 Cu (2 oz.) on 0.060" thick FR4 PCB.
- (2) Pulse width ≤300µs, duty cycle ≤2%
- (3) Limited by gate resistance.





Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.



SLPS443 - JUNE 2013 www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ELECTRICAL CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$

| PARAMETER | | TEST CONDITIONS | MIN | TYP | MAX | UNIT |
|---------------------|----------------------------------|--|-------|-------|-------|------|
| Static Ch | aracteristics | | | | | |
| BV _{DSS} | Drain to Source Voltage | $V_{GS} = 0V, I_{D} = -250\mu A$ | -20 | | | V |
| BV _{GSS} | Gate to Source Voltage; | $V_{DS} = 0V, I_{G} = -250\mu A$ | -6.0 | | | V |
| I _{DSS} | Drain to Source Leakage Current | V _{GS} = 0V, V _{DS} = -10V | | | -1 | μΑ |
| I _{GSS} | Gate to Source Leakage Current | $V_{DS} = 0V$, $V_{GS} = -6V$ | | | -100 | nA |
| V _{GS(th)} | Gate to Source Threshold Voltage | $V_{DS} = V_{GS}, I_{D} = -250 \mu A$ | -0.60 | -0.85 | -1.10 | V |
| D | Dunin to Course On Besistance | $V_{GS} = -2.5V, I_D = -1A$ | | 54 | 67 | mΩ |
| R _{DS(on)} | Drain to Source On Resistance | $V_{GS} = -4.5V, I_D = -1A$ | | 39 | 47 | mΩ |
| 9 _{fs} | Transconductance | $V_{DS} = -10V, I_{D} = -1A$ | | 6.2 | | S |
| Dynamic | Characteristics | | | | | |
| C _{ISS} | Input Capacitance | | | 368 | 478 | pF |
| Coss | Output Capacitance | $V_{GS} = 0V, V_{DS} = -10V, f = 10kHz$ | | 148 | 192 | pF |
| C _{RSS} | Reverse Transfer Capacitance | | | 7.8 | 10.1 | pF |
| R _G | Series Gate Resistance | | | 20 | | Ω |
| R _C | Series Clamp Resistance | | | 5000 | | Ω |
| Qg | Gate Charge Total (-4.5V) | | | 2.2 | 2.9 | nC |
| Q _{gd} | Gate Charge Gate to Drain | V _{DS} = -10V, I _D = -1A | | 0.14 | | nC |
| Q _{gs} | Gate Charge Gate to Source | | | 0.74 | | nC |
| Q _{g(th)} | Gate Charge at Vth | | | 0.43 | | nC |
| Q _{OSS} | Output Charge | $V_{DS} = -10V, V_{GS} = 0V$ | | 2.5 | | nC |
| t _{d(on)} | Turn On Delay Time | | | 510 | | ns |
| t _r | Rise Time | $V_{DS} = -10V, V_{GS} = -2.5V, I_D = -1A$ | | 520 | | ns |
| t _{d(off)} | Turn Off Delay Time | $R_G = 10\Omega$ | | 1000 | | ns |
| t _f | Fall Time | | | 970 | | ns |
| Diode Ch | naracteristics | | | | | |
| V _{SD} | Diode Forward Voltage | $I_S = -1A$, $V_{GS} = 0V$ | | -0.77 | -1 | V |
| Q _{rr} | Reverse Recovery Charge | $V_{DS} = -10V, I_F = -1A,$ di/dt = 200A/ μ s | | 4.0 | | nC |
| t _{rr} | Reverse Recovery Time | $V_{DS} = -10V, I_F = -1A,$ di/dt = 200A/ μ s | | 11 | | ns |

THERMAL CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$


| | PARAMETER | MIN | TYP | MAX | UNIT |
|-----------------|---|-----|-----|-----|------|
| D | Junction to Ambient Thermal Resistance ⁽¹⁾ | | 75 | | °C/W |
| $R_{\theta JA}$ | Junction to Ambient Thermal Resistance ⁽²⁾ | | 265 | | °C/W |

- (1) Device mounted on FR4 material with 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu.
 (2) Device mounted on FR4 material with minimum Cu mounting area.


Product Folder Links: CSD25213W10



www.ti.com SLPS443 – JUNE 2013



Max $R_{\theta JA} = 90^{\circ}C/W$ when mounted on 1inch² of 2 oz. Cu.



Max $R_{\theta JA} = 333^{\circ} C/W$ when mounted on minimum pad area of 2 oz. Cu.

TYPICAL MOSFET CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$




Figure 1. Transient Thermal Impedance

Product Folder Links: CSD25213W10

1.1

-V_{GS(th)} - Threshold Voltage (V)



TYPICAL MOSFET CHARACTERISTICS (continued)

(T_A = 25°C unless otherwise stated)







Figure 2. Saturation Characteristics



NSTRUMENTS

Figure 3. Transfer Characteristics





100 $T_C = 25^{\circ}C$ Id = -1A $R_{DS(on)}$ - On-State Resistance $(m\Omega)$ 90 $T_C = 125^{\circ}C \text{ Id} = -1A$ 80 70 60 50 40 30 20 3 -V_{GS} - Gate-to- Source Voltage (V)

Figure 7. On-State Resistance vs. Gate-to-Source Voltage

Figure 6. Threshold Voltage vs. Temperature



www.ti.com SLPS443 – JUNE 2013

TYPICAL MOSFET CHARACTERISTICS (continued)

(T_A = 25°C unless otherwise stated)




Figure 8. Normalized On-State Resistance vs. Temperature




Figure 9. Typical Diode Forward Voltage




Figure 10. Maximum Safe Operating Area




Figure 11. Single Pulse Unclamped Inductive Switching




Figure 12. Maximum Drain Current vs. Temperature

Copyright © 2013, Texas Instruments Incorporated


Product Folder Links: CSD25213W10

SLPS443 – JUNE 2013 www.ti.com

TEXAS INSTRUMENTS

MECHANICAL DATA

CSD25213W10 Package Dimensions




NOTE: All dimensions are in mm (unless otherwise specified)

Pin Configuration Table

| J | | | | | | | |
|----------|-------------|--|--|--|--|--|--|
| POSITION | DESIGNATION | | | | | | |
| A1 | Gate | | | | | | |
| B1 | Drain | | | | | | |
| A2, B2 | Source | | | | | | |

Land Pattern Recommendation



NOTE: All dimensions are in mm (unless otherwise specified)

Product Folder Links: CSD25213W10



PACKAGE OPTION ADDENDUM

10-Dec-2020

PACKAGING INFORMATION

| Orderable Device | Status | Package Type | Package Drawing | Pins | Package Qty | Eco Plan | Lead finish/ Ball material | MSL Peak Temp | Op Temp (°C) | Device Marking (4/5) | Samples |
|------------------|--------|--------------|--------------------|------|----------------|--------------|-------------------------------|--------------------|--------------|-------------------------|---------|
| | | | | | | | (6) | | | | |
| CSD25213W10 | ACTIVE | DSBGA | YZB | 4 | 3000 | RoHS & Green | SNAGCU | Level-1-260C-UNLIM | -55 to 150 | 213 | Samples |

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead finish/Ball material Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead finish/Ball material values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 18-Aug-2021

TAPE AND REEL INFORMATION





| A0 | |
|----|---|
| B0 | Dimension designed to accommodate the component length |
| K0 | Dimension designed to accommodate the component thickness |
| W | Overall width of the carrier tape |
| P1 | Pitch between successive cavity centers |


QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

| Device | Package Type | Package Drawing | | | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|-----------------|--------------------|---|------|--------------------------|--------------------------|------------|------------|------------|------------|-----------|------------------|
| CSD25213W10 | DSBGA | YZB | 4 | 3000 | 180.0 | 8.4 | 1.06 | 1.06 | 0.69 | 2.0 | 8.0 | Q1 |

www.ti.com 18-Aug-2021



*All dimensions are nominal

| Device | Device Package Type | | Pins | SPQ | Length (mm) | Width (mm) | Height (mm) | |
|-------------|---------------------|-----|------|------|-------------|------------|-------------|--|
| CSD25213W10 | DSBGA | YZB | 4 | 3000 | 182.0 | 182.0 | 20.0 | |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (https://www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2021, Texas Instruments Incorporated