

Measuring the Thermal Impedance of LDOs in Situ

Maxwell Robertson

LP Linear Regulators

ABSTRACT

This document describes a procedure for computing an integrated circuit's junction-to-ambient thermal impedance using its thermal shutdown temperature.

1 Introduction

The junction-to-ambient thermal impedance ($R_{\theta JA}$) of a device is an industry-standard metric of thermal performance. It defines the linear relationship between how much power a device dissipates and how much it heats up as a result. For a given ambient operating temperature, the thermal impedance can be used to determine a device's junction temperature as a function of its power dissipation. For this reason, it is an important parameter to know when designing a robust system.

Unfortunately, knowing a device's thermal impedance is not as simple as looking it up in a data sheet. Although semiconductor manufacturers typically provide a thermal impedance value, this value comes from measurements taken on industry standard test boards. Because a device's thermal performance depends strongly on the properties of the circuit board on which it is installed, these data sheet specifications of thermal impedance cannot be assumed valid across all board designs. The best way to determine the thermal impedance of a device installed on an application board is to measure it.

This application report focuses evaluating the thermal performance of low-dropout linear regulators (LDO), but the procedure described is applicable to any device in which the power dissipation can be controlled. LDOs were chosen as an example because of the ease of the power calculation, and because their dissipative nature requires thermal properties to be considered in every design.

2 Procedure

This section presents a simple method for determining the junction-to-ambient thermal impedance of an LDO regulator installed on a circuit board. Note that this method requires that the LDO have a thermal shutdown feature. Because this feature is not always present, it is critical to check the data sheet of the device in question before proceeding. This method also requires some way of regulating the ambient temperature (T_A) and the power dissipated in the device (P_D).

The junction temperature (T_J) of a device is given by the equation:

$$T_J = T_A + R_{\theta JA} \times P_D$$

To determine $R_{\theta JA}$ using this equation, all other parameters (T_A , P_D , and T_J) must be known. The ambient temperature can easily be measured by a thermometer, and the power dissipated in an LDO can be calculated easily. However, it is not possible to directly measure the junction temperature.

Because the junction temperature cannot be measured, it must be removed from the equation. This can be done by making clever use of the device's thermal shutdown temperature (T_{SD}). By choosing two sets of operating conditions that result in thermal shutdown, a device's thermal impedance can be determined. In this case, the operating conditions that are varied are power dissipation and ambient temperature.

First, choose a convenient level of power dissipation. For an LDO, this is given by

$$P_D = (V_{in} - V_{out}) \times I_{out} + V_{in} \times I_q$$

Note that the quiescent current (I_q , also called the ground current) of an LDO is typically small enough to be neglected in power calculations. The power dissipated then can be varied easily with input voltage, output voltage, or output current.

Next, increment the ambient temperature until thermal shutdown is reached. This typically means that the internal pass element is turned off, causing the LDO's output voltage to approach 0 V. In this state, the LDO no longer dissipates power, and its junction temperature may decrease enough to turn back on. Because of the potential of cycling back and forth between on and off states, it is best to detect thermal shutdown by monitoring the output voltage versus time on an oscilloscope. Also, keep in mind that temperature generally changes slowly; allow plenty of time after the ambient set point is incremented for thermal equilibrium to be reached. After thermal shutdown is reached, allow the device to cool and ensure that it is still operating properly.

Choose another power dissipation level and repeat the preceding procedure to determine the new ambient temperature level required for device shutdown. Once two sets of operating conditions are known, the following method may now be used to compute the thermal impedance:

$$\begin{aligned} \text{First measurement: } T_J' &= T_A' + R_{\theta JA} \times P_D' \\ \text{Second measurement: } T_J'' &= T_A'' + R_{\theta JA} \times P_D'' \end{aligned}$$

Because thermal shutdown was reached under both conditions,

$$T_J' = T_J'' = T_{SD}$$

Therefore,

$$T_A' + R_{\theta JA} \times P_D' = T_A'' + R_{\theta JA} \times P_D''$$

This equation can be rewritten to define the thermal impedance:

$$R_{\theta JA} = \frac{T_A' - T_A''}{P_D'' - P_D'}$$

When following this procedure, keep in mind a few additional things:

- Calculations often can be simplified by choosing an initial power dissipation of 0 W. This allows the device's shutdown temperature to be measured as well.
- Device features such as current limiting may cause the actual power dissipation to be less than desired, so it is a good idea to double-check the power dissipation by measuring input voltage, output voltage, and output current.
- Thermal impedance also varies greatly with the airflow over the device. For a conservative measurement, ensure that the airflow during testing is less than the expected airflow during normal operation.

3 Conclusion

Because a device's thermal behavior depends on the properties of its application board, data sheet specifications of thermal impedance are insufficient to predict thermal behavior in all designs. Fortunately, a simple way of measuring the thermal impedance of a device installed on an application board is possible. Following the method described in this document allows engineers to accurately determine the device's junction temperature under various operating conditions.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2010, Texas Instruments Incorporated