

## **Asynchronous Serial Mode for CC1110Fx and CC2510Fx**

By Siri Johnsrud

---

### **Keywords**

- *Asynchronous Serial Mode*
- *CC1110Fx*
- *CC2510Fx*

### **1 Introduction**

The purpose of this design note is to show how the CC1110Fx and CC2510Fx can be configured for asynchronous serial mode. This mode can be used in applications that

need to transmit and/or receive data packets not fitting with the standard packet format supported by the CC1110Fx and CC2510Fx.

## Table of Contents

KEYWORDS.....	1
1 INTRODUCTION.....	1
2 ABBREVIATIONS.....	2
3 CONFIGURATION.....	3
3.1 TX MODE.....	3
3.2 RX MODE.....	3
4 PSEUDO CODE.....	3
5 REFERENCES.....	5
6 GENERAL INFORMATION.....	6
6.1 DOCUMENT HISTORY.....	6

## 2 Abbreviations

EB	Evaluation Board
FEC	Forward Error Correction
GPIO	General Purpose Input Output
ms	Millisecond
MSK	Minimum Shift Keying
RF	Radio Frequency
RX	Receive
TX	Transmit

## 3 Configuration

The PKTCTRL0 register needs to be programmed to 0x32 in both RX and TX mode. This means that both PKTCTRL0.PKT\_FORMAT and PKTCTRL0.LENGHT\_CONFIG is set to values described as “Reserved” in the data sheets ([1] and [2]). It is important to note that when asynchronous serial mode is enabled it is not possible to use data whitening, FEC, Manchester encoding, or MSK. The CC1110Fx and CC2510Fx modulator samples the level of the asynchronous input 8 times faster than the programmed data rate and hence the error in the bit period for the asynchronous stream must be less than one eighth of the programmed data rate.

### 3.1 TX Mode

In TX mode, P0\_7 becomes serial data input and this pin must be configured to have peripheral function, meaning that POSEL.SELP0\_[7] should be set to 1. Since this pin is an input pin while in TX mode, it is not possible to write data directly to this pin. Instead, another port pin must be configured as a general purpose output pin and this pin must be connected to P0\_7. For the pseudo code example in Figure 1, P1\_5 is being used. Please note that if using SmartRF04EB to test this code, R107 must be removed, as P0\_7 is connected to the potmeter.

### 3.2 RX Mode

In RX mode, P1\_5, P1\_6, or P1\_7 can be configured as serial data output by setting IOCFG0, IOCFG1, or IOCFG2 to 0x0D respectively. Pseudo code showing how RX mode can be tested are shown in Figure 2.

## 4 Pseudo Code

```
// Pseudo code for testing asynchronous serial mode in TX. This code example assumes
// that P1_5 and P0_7 are connected. The code example shows how a simple 1010101...
// sequence can be transmitted in async. mode.

// 1) Init MCU (Operation of the RF transceiver requires that the high speed crystal
//    oscillator is used)

// 2) Configure Radio

// 3) Program P1.5 as an output (can be any other available GPIO)
P1DIR.DIR1_[5] = 1;

// 4) Make P0.7 becomes Serial Data Input in TX mode by configuring the pin to have
//    peripheral function
POSEL.SELP0_[7] = 1;

// 5) Enter TX state by issuing an STX strobe command
RFST = 0x03;

// 6) Wait for radio to enter TX state
while (MARCSTATE != 0x13);

// 7) Loop forever while transmitting a 1010101... sequence with period 2x ms
while (1) {
    P1_5 = 0;
    delay(x); // x is the delay in ms
    P1_5 = 1;
    delay(x); // x is the delay in ms
}
```

Figure 1. Pseudo Code for TX

# ***Design Note DN119***

```
// Pseudo code for testing asynchronous serial mode in RX. In this code example P1_6 is
// configured as Serial Data Output and the received data can be monitored or read from
// this pin

// 1) Init MCU (Operation of the RF transceiver requires that the high speed crystal
//    oscillator is used)

// 2) Configure Radio

// 3) Program P1.6 as Serial Data Output
IOCFG1 = 0x0D;

// 4) Enter RX state by issuing an SRX strobe command
RFST = 0x02;

// 5) Wait for radio to enter RX state
while (MARCSTATE != 0x0D);

// 6) Loop forever. The received data can be monitored by connecting an oscilloscope to
//    P1_6 or it can be read in SW by reading P1.P1[6]
while (1) {
}
```

**Figure 2. Pseudo Code for RX**

## **5 References**

- [1] CC1110Fx/CC1111Fx Low-Power Sub-1 GHz RF System-on-Chip (SoC) with MCU, Memory, Transceiver, and USB Controller (cc1110f32.pdf)
- [2] CC2510Fx/CC2511Fx Low-Power SoC (System-on-Chip) with MCU, Memory, 2.4 GHz RF Transceiver, and USB Controller (cc2510f32.pdf)

# ***Design Note DN119***

## **6 General Information**

### **6.1 Document History**

<b>Revision</b>	<b>Date</b>	<b>Description/Changes</b>
SWRA316	2010.01.26	Initial release.
SWRA316A	2012.03.21	Removed references to CC1111Fx and CC2511Fx as these devices do not have P0_7.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Automotive and Transportation	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2012, Texas Instruments Incorporated