

CC112X/CC120X On-Chip Temperature Sensor

Bjarte Nystøyl and Torstein Ermesjø

ABSTRACT

This application report provides the necessary information to use the temperature sensor of the CC112X and CC120X families. The temperature sensor is based on a proportional to absolute temperature (PTAT) current from a bandgap cell fed to a resistor to generate a PTAT voltage. It is possible to read out the temperature information as an analog voltage on a general-purpose input/output (GPIO) pin.

Contents

1	Analog Readout	2
2	References	6

List of Figures

1	GPIO1 Voltage vs Temperature	3
2	Temperature Error Due to Different Temperature Coefficients After Single-Point Calibration	4
3	Typical GPIO1 Measurements vs Supply Voltage	5

List of Tables

1	Register Settings for Temperature Sensor	2
2	Typical Temperature Sensor Parameters	2

Trademarks

All trademarks are the property of their respective owners.

1 Analog Readout

1.1 Operation

The temperature sensor is activated using the register settings of [Table 1](#), which makes the GBIAS output a single-ended voltage measurement on GPIO1.

Table 1. Register Settings for Temperature Sensor

Register	Value
IOCFG1	0x80
ATEST	0x2A
ATEST_MODE	0x0C
GBIAS1	0x07

Setting IOCFG1 to 0x80 configures the GPIO1 pad into analog mode (digital GPIO input and output is disabled). The remaining registers set up the ATEST (analog test) module to output the temperature value as a PTAT voltage on the GPIO1.

1.2 Temperature Sensor Parameters

General Information	Value	Unit
Temperature sensor fitted from	-40 to +85	°C
Effect of supply voltage deviance	1.17	mV/VDD-V
Effect of supply voltage deviance	0.44	°C /VDD-V

Changes in the supply voltage affect the voltage of the GPIO pin, and the supply voltage must be stable in order to get accurate temperature sensor readings.

Table 2. Typical Temperature Sensor Parameters

Technical Information	Value	Unit
VDD - 2 V		
Typical output voltage @ 0°C	727.42	mV
Typical output voltage @ 25°C	793.73	mV
Temperature coefficient	2.6598	mV/°C
VDD - 3 V		
Typical output voltage @ 0°C	728.55	mV
Typical output voltage @ 25°C	794.78	mV
Temperature coefficient	2.6733	mV/°C
VDD - 3.6 V		
Typical output voltage @ 0°C	730.62	mV
Typical output voltage @ 25°C	796.94	mV
Temperature coefficient	2.6773	mV/°C

1.3 Calibration

As seen in Figure 1, the CC112X/CC120X temperature sensor voltage is highly linear, but for some devices there is an offset in the GPIO1 voltage from the typical (average) value that could potentially give an error of up to $\pm 10^{\circ}\text{C}$ in the temperature reading. In order to ensure accurate temperature sensor measurements, the sensor must be calibrated. There are two simple approaches depending on the required accuracy level: single- and two-point calibration.




Figure 1. GPIO1 Voltage vs Temperature

1.4 Single-Point Calibration

This is a simple and fast approach that can be applied for applications targeting approximately $\pm 1^{\circ}\text{C}$ accuracy within a limited temperature range around the temperature used for the single-point calibration, or approximately $\pm 2^{\circ}\text{C}$ accuracy across the -40°C to $+85^{\circ}\text{C}$ temperature range.

1.4.1 Performing Single-Point Calibration

The calibration should be performed at the center of the temperature range in which the device will operate. A given temperature, T , will be given as:

$$T = T_{\text{CALIBRATION}} + \frac{(V_{\text{MEASURED}} - V_{\text{CALIBRATION}})}{t_c} \quad (1)$$

- $T_{\text{CALIBRATION}}$ is the temperature when the calibration is performed
- t_c is the temperature coefficient for the given supply voltage (see the typical temperature parameters in Table 2)
- V_{MEASURED} is the voltage of the GPIO1 pin at a given temperature
- $V_{\text{CALIBRATION}}$ is the GPIO1 voltage at the calibration temperature

Performing a single-point calibration removes the error caused by the device-specific voltage offset seen in Figure 1. The temperature reading accuracy is then limited by the accuracy of the individual temperature coefficients as the typical temperature coefficient is used in Equation 1.

Figure 2 shows the maximum error in the temperature reading when using the lowest and highest temperature coefficients out of 30 devices from different processing corners.

- Approximately $\pm 2^\circ\text{C}$ accuracy is possible across the -40°C to $+85^\circ\text{C}$ temperature range with single-point calibration and using the typical temperature coefficient in Table 2.
- Approximately $\pm 1^\circ\text{C}$ accuracy is possible across the temperature range defined by $T_{\text{CALIBRATION}} \pm 25^\circ\text{C}$ with single-point calibration and using the typical temperature coefficient in Table 2.




Figure 2. Temperature Error Due to Different Temperature Coefficients After Single-Point Calibration

1.4.2 Single-Point Calibration Example

A CC112X/CC120X device is operated using at 3 V supply voltage. The temperature coefficient is typically 2.673 mV/°C and for each degree Celsius increase in temperature the GPIO1 voltage increases by 2.673 mV.

The device is calibrated at room temperature (25°C), and the GPIO1 voltage is measured to be 793.0 mV. After changing the temperature, the GPIO1 voltage is measured to be 830.0 mV. This corresponds to a temperature T of:

$$T = 25^\circ\text{C} + \frac{(830 \text{ mV} - 793 \text{ mV})}{2.673 \text{ mV} / ^\circ\text{C}}$$

$$T = 25^\circ\text{C} + 13.84^\circ\text{C} = 38.84^\circ\text{C} \quad (2)$$

1.5 Two-Point Calibration

If the application requires better accuracy than given by the single-point calibration, a two-point calibration must be used to correct for chip-to-chip variations in the temperature coefficients. As the sensor is highly linear, a two-point calibration will ensure high accuracy across the full temperature range of the chip.

1.5.1 Performing Two-Point Calibration

Choose two calibration temperatures more than 10°C apart, called T_0 and T_1 , and set the reference voltage (V_{DD}) to what it will be in the final product.

NOTE: Changes in the voltage supply will influence the temperature sensor output.

Measure the output from the GPIO1 pin (V_0 and V_1) at the corresponding temperatures.

The temperature coefficient has a typical value of 2.673 mV/°C. The exact coefficient (t_c) for a given device is calculated as:

$$t_c = \frac{V_1 - V_0}{T_1 - T_0} \quad (3)$$

Using the exact coefficient, the measured voltage of the GPIO1 pin (V_{MEASURED}), the temperature (T_0) and the GPIO1 voltage (V_0) of the first calibration, the temperature, T , can be found as:

$$T = T_0 + \frac{(V_{\text{MEASURED}} - V_0)}{t_c} \quad (4)$$

1.5.2 Two-Point Calibration Example

A CC112X/CC120X device is operated using a 3 V supply voltage, and will have a typical temperature coefficient of 2.673 mV/°C.

The device is calibrated at two temperatures: 0°C and 25°C (T_0 and T_1). The respective GPIO1 voltages are measured to be 743.379 mV and 808.312 mV (V_0 and V_1). The exact temperature coefficient t_c is given as:

$$t_c = \frac{808.312 \text{ mV} - 743.379 \text{ mV}}{25^\circ\text{C} - 0^\circ\text{C}} = 2.5973 \text{ mV} / ^\circ\text{C} \quad (5)$$

At a given temperature T , the GPIO1 voltage is measured to be 921.465 mV. This corresponds to:

$$T = 0^\circ\text{C} + \frac{(921.465 \text{ mV} - 743.379 \text{ mV})}{2.5973 \text{ mV} / ^\circ\text{C}} = 68.57^\circ\text{C} \quad (6)$$

NOTE: Single-point calibration at 25°C, using the typical t_c of 2.673 mV/°C, would in this case give a temperature reading of 67.33°C, which would have an error of 1.24°C.

1.6 Change in Supply Voltage (V_{DD})

As seen in Figure 3, the voltage measured on the GPIO1 pin depends on the supply voltage. Changing the supply voltage affects the measured voltage on the GPIO1 pin by typically 1.17 mV/V. This means that if the supply voltage is decreased by 1 V, the voltage measured at the GPIO1-pin is typically 1.17 mV lower.




Figure 3. Typical GPIO1 Measurements vs Supply Voltage

2 References

1. [High Performance RF Transceiver for Narrowband Systems Data Sheet](#)
2. [High Performance Low Power RF Transceiver Data Sheet](#)
3. [Ultra-High Performance RF Narrowband Transceiver Data Sheet](#)
4. [CC112X/CC1175 Low-Power High Performance Sub-1 GHz RF Transceivers/Transmitter User's Guide](#)

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from C Revision (June 2014) to D Revision	Page
• Update was made in the Abstract of this document.	1
• Removed Section 2.	1

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2018, Texas Instruments Incorporated