

# Bill of Materials

TI DESIGNS

TIDA-01550

Item	Qty	Reference	Value	Part Description	Digikey Part Number	Manufacturer	Manufacturer Part Number	PCB Footprint	Note
1	2	C37, C40	10 pF	CAP CER 10PF 50V COG/NPO 0603	311-1058-1-ND	YAGEO	CC603JRNPO98N100	0603	
2	1	C1	10000PF	CAP CER 10000PF 50V 10% X7R 0603	445-1311-1-ND	TDK	C1608X7R1H103K080AA	0603	
3	10	C56, C57, C60, C61, C62, C63, C64, C65, C66, C67	0.1UF	CAP CER 0.1UF 25V 10% X7R 0603	445-1316-1-ND	TDK	C1608X7R1E104K080AA	0603	
4	8	R20, R21, R22, R37, R45, R56, R57, R58	100	RES 100 OHM 1/10W 5% 0603 SMD	RMCF0603J1100CT-ND	STACKPOLE	RMCF0603J1100R	0603	
5	5	R5, R6, R7, R17, R49	100K OHM	RES 100K OHM 1/8W 5% 0805 SMD	RMCF0805J1100KCT-ND	STACKPOLE	RMCF0805J1100K	0805	
6	7	C5, C16, C22, C29, C31, C32, C81	0.1 UF	CAP CER 0.1UF 50V Y5V 0603	311-1343-1-ND	YAGEO	CC603ZRY5V98B104	0603	
7	1	R19	10 OHM	RES 10 OHM 1/8W 5% 0805 SMD	RMCF0805J110R0CT-ND	STACKPOLE	RMCF0805J110R0	0805	
8	3	C35, C44, C48	10 UF	CAP, CERM, 10 uF, 16 V, +/- 10%, X5R, 0805	587-1295-1-ND	TAIYO	EMK212BJ106KG-T	0805	
9	12	D2, D3, D4, D5, D10, D11, D12, D13, D26, D27, D28, D29	DIODE	DIODE SWITCHING 75V 0.15A SOD523	1N4148XTMPSCT-ND	MICRO COMM	1N4148X-TP	SOD523	
10	2	D6, D7	DIODE	DIODE GEN PURP 75V 150MA SOD323F	1N4148WSFSC-ND	FAIRCHILD	1N4148WS	SOD323F	
11	1	C55	1UF	AP CER 1UF 25V 10% X7R 0603	445-5956-1-ND	TDK	C1608X7R1E105K080AB	0603	
12	3	C39, C42, C46	2200uF	CAP ALUM 2200UF 20% 10V RADIAL	PS128-ND	PANASONIC	ECA-1AM222	Through-hole	
13	4	C4, C15, C17, C30	4.7 UF	CAP CER 4.7UF 10V 10% X5R 0603	311-1455-1-ND	YAGEO	CC603KRX5R68B475	0603	
14	3	R8, R9, R10	470	RES 470 OHM 5W 5% AXIAL	45470E-ND	OHMITE	45470E	Through-hole	
15	3	C41, C45, C47	470n	CAP FILM 0.47UF 5% 630VDC RADIAL	P14532-ND	PANASONIC	ECQ-E6474F	Through-hole	
16	1	C54	47UF	CAP CER 47UF 25V 20% X5R 1206	445-8047-1-ND	TDK	C3216X5R1E476M160AC	1206	
17	3	ZD1, ZD2, ZD3	BZV55-B6V2.115	DIODE ZENER 6.2V 500MW SOD80C	568-6251-1-ND	NXP	BZV55-B6V2.115	SOD80C	
18	8	ACT, JP14, JP15, JP16, REACT, AFE1_EN, AFE2_EN, AFE3_EN	2-PIN CONNECTOR	CONN HEADER VERT SGL 2POS GOLD	3M9447-ND	3M	961102-6404-AR	Through-hole	
19	9	AFEPWR1, AFEPWR2, AFEPWR3, AFE1_EXTRA, AFE2_EXTRA, AFE3_EXTRA, HOST_EXTRA, LOGIC2	3-PIN CONNECTOR	CONN HEADER VERT SGL 3POS GOLD	3M9448-ND	3M	961103-6404-AR	Through-hole	
20	13	AFE1_COMM, AFE2_COMM, AFE3_COMM, HOST_COMM1, HOST_COMM2, HOST_COMM3, AFE1_JTAG, AFE2_JTAG, AFE3_JTAG, DGND, DVCC, ISO_PULSE, P7	4-PIN CONNECTOR	CONN HEADER VERT SGL 4POS GOLD	3M9449-ND	3M	961104-6404-AR	Through-hole	
21	3	BTN1, BTN2, RESET	SWITCH	SWITCH TACTILE SPST-NO 0.02A 15V	P80795CT-ND	PANASONIC	EVQ-11L05R	Through-hole	
22	3	U57, U513, U514	TERMINAL BLOCK	TERMINAL BLOCK 5.08MM VERT 2POS	ED1609-ND	ON-SHORE	ED120/2DS	Through-hole	
23	1	RS1	RS-232 CONNECTOR	CONN D-SUB RCPT R/A 9POS 30GOLD	A32119-ND	TE CONN	5747844-6	Through-hole	
24	3	D8, D9, D16	LLSD103B	DIODE SCHOTTKY 40V 350MA MINMELF	497-3274-1-ND	st	LLSD103B-7	MINMELF	
25	3	LED_PHASE_1, LED_PHASE_2, LED_PHASE_3	YELLOW LED	LED 3.1MM 585NM YELLOW TRANSP	511-1251-ND	ROHM	SLR-342YC3F	Through-hole	
26	2	LED_ACT, LED_REACT	GREEN LED	LED 3.1MM 563NM GREEN TRANSP	511-1247-ND	ROHM	SLR-342MC3F	Through-hole	
27	3	R2, R41, R63	VARISTOR	VARISTOR 275V RMS 20MM RADIAL	495-1417-ND	TDK	S20K275	20 MM Radial	
28	3	TVS1, TVS2, TVS3	DIODE	DIODE TVS 5.0V 400W BI 5% SMD	SMAJ5.0CABCT-ND	BOURNS	SMAJ5.0CA	SMD	
29	1	LCD1	LCD	160-segment LCD	Custom LCD	Custom	Custom	Custom	Custom LCD
30	1	U3	LDO	IC REG LDO 3.3V 0.15A SOT23-5	296-35483-1-ND	TI	TPS70933DBVR	SOT23-5	
31	1	U2	RS232	IC DVR/RCV RS232 MULTICH 16TSSOP	296-24863-1-ND	TI	TRS3232EQPWRQ1	16TSSOp	
32	3	U56, U57, and U58	LDO	IC REG LINEAR 3.3V 150MA SOT23-5	296-27946-2-ND	TI	TLV70433DBVT	SOT23-5	
33	1	XT1	CRYSTAL	CRYSTAL 32.768 KHZ 6PF SMD	300-8341-1-ND	CITIZEN FINETECH	CMR200T32768DZBT	SMD	
34	6	C3, C10, C51, C75, C92, C95	1 u	CAP, CERM, 1 uF, 50 V, +/-10%, X5R, 0603	490-12330-2-ND	Murata	GRT188R61H105KE13D	0603	
35	6	C8, C11, C52, C76, C93, C96	0.1u	CAP CER 0.1UF 25V X7R 0603	478-3713-2-ND	AVX Corporation	06033C104JAT2A	0603	
36	1	DNP	DNP	DNP	DNP	DNP	DNP	850IC	
37	1	U1	ISOLATION	DGTL ISO 3KV GEN PRP 850IC	ISO7721DR-ND	TI	ISO7721DR	850IC	
38	3	U51, U53, U54	ISOLATION	DGTL ISO 5KV 3CH GEN PURP 16SOIC	296-44935-5-ND	TI	ISO7731DW	16SOIC	
39	6	C34, C43, C77, C80, C87, C90	15nF	CAP CER 150PF 50V COG 0603	445-1283-1-ND	TDK	C1608C0G1H151J080AA	0603	
40	10	R33, R34, R36, R39, R40, R43, R55, R60, R62, R25	1k	RES SMD 1K OHM 1% 1/10W 0603	RMCF0603FG1K00TR-ND	Stackpole	RMCF0603FG1K00	0603	
41	3	C23, C33, C82	DNP	DNP	DNP	DNP	DNP	0603	DNP
42	3	R38, R46, R59	2.7k	RES SMD 2.7K OHM 5% 1/10W 0603	P2.7KGCT-ND	Panasonic	ERJ-3GEVJ272V	0603	
43	3	R26, R28, R51	20k	RES SMD 20K OHM 0.1% 1/10W 0603	P20KDBCT-ND	Panasonic	ERA-3AEB203V	0603	
44	9	R29, R30, R31, R32, R35, R42, R52, R53, R54	330k	RES SMD 330K OHM 5% 1/10W 0603	P330KGT-ND	Panasonic	ERJ-3GEVJ334V	0603	
45	3	C24, C49, C83	4.7u	CAP CER 4.7UF 10V Y5V 0603	311-1827-1-ND	YAGEO	CC603ZRY5V68B475	0603	
46	3	C25, C53, C84	470n	CAP CER 0.47UF 25V Y5V 0603	1276-2376-1-ND	Samsung	CL10F474Z8ANNNC	0603	
47	3	R27, R50, R61	47k	RES SMD 47K OHM 1% 1/10W 0603	P47.0KHCT-ND	Panasonic	ERJ-3KF4702V	0603	
48	12	C26, C27, C36, C38, C58, C59, C78, C79, C85, C86, C88, C89	47pF	CAP CER 47PF 50V COG 0603	445-1277-1-ND	TDK	C1608C0G1H470I080AA	0603	
49	3	U4, U10, U11	MSP430I2020	IC MCU 16BIT 32KB FLASH 28TSSOP	296-40426-1-ND	TI	MSP430I2041TPWR	TSOP-28	Note that this design could work with the MSP430I2020 or MSP430I2030 for lower cost. However, the MSP430I2041 was particularly used.

Item	Qty	Reference	Value	Part Description	Digikey Part Number	Manufacturer	Manufacturer Part Number	PCB Footprint	Note
50	22	R/L1, R/L2, R/L5, R/L6, R/L7, R/L9, R/L3, R/L4, R/L8, R/L10, R44, R47, R64, R65, R71, R72, R73, R74, R75, R76, R77, R78	0.0 OHM	RES 0.0 OHM 1/10W 0603 SMD	RMCF0603ZTOR00CT-ND	STACKPOLE	RMCF0603ZTOR00	0603	
51	9	TP1, TP2, TP3, TP4, TP5, TP6, TP7, TP8, TP9	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0603	
52	1	C18	100n	CAP CER 0.1UF 10V X5R 0402	445-4984-1-ND	TDK	C1005X5R1A104M0508A	0402	
53	1	C28	1n	CAP CER 1000PF 50V X7R 0402	445-1256-1-ND	TDK	C1005X7R1H102K0508A	10POS	
54	2	C6, C7	18pF	CAP CER 18PF 50V C0G 0402	445-1238-2-ND	TDK	C1005C0G1H180J0508A	0402	
55	1	R24	47k	RES 47.0K OHM 1/16W 1% 0402 SMD	311-47.0KLRCT-ND	Yageo	RCD402FR-0747KL	0402	
56	1	R23	91kOhm, 0.1%, 25ppm/C	RES 91K OHM 1/8W 0.1% 0805 SMD	P91KDACT-ND	Panasonic	ERA-6AE8913V	0805	
57	1	JTAG	JTAG	CONN HEADER 10POS DUAL VERT	SAM8909-ND	Samtec	FTSH-105-01-F-D-K		
58	1	MSP1	MSP432P4111	IC MCU 32BIT	N/A	TI	MSP432P4111IPZ	PZ	Samples of the 432 were obtained internally for this design
59	1	Q1	Q1	CRYSTAL 48.00 MHZ 10.0PF SMD	FA-238 48.0000MB-K3-ND	Epson	FA-238 48.0000MB-K3	SMD	
60	1	AFE1_ID0	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "0"
61	1	AFE1_ID1	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "0"
62	1	AFE2_ID0	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "1"
63	1	AFE2_ID1	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "0"
64	1	AFE3_ID0	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "0"
65	1	AFE3_ID1	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "1"
66	3	INB_SEL1, INB_SEL2, INB_SEL3	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "UTSI"
67	3	OUTC_SEL1, OUTC_SEL2, OUTC_SEL3	0.0 OHM	RES 0.0 OHM 1/8W 0805 SMD	RMCF0805ZTOR00CT-ND	STACKPOLE	RMCF0805ZTOR00	0805	Place resistor on center pad and pad that says "URSO"
68	9	AFE1_OPT1, AFE1_OPT2, AFE1_OPT3, AFE2_OPT1, AFE2_OPT2, AFE2_OPT3, AFE3_OPT1, AFE3_OPT2, AFE3_OPT3	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0805	
69	6	C2, C9, C50, C74, C91, C94	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0603	
70	1	CLK_GEN	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	Clk	
71	6	C68, C69, C70, C71, C72, C73	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0805	
72	1	C14	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0805	
73	7	R1, R11, R12, R13, R14, R48, R66	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	0603	
74	1	U9	Do not populate	Do not populate	Do Not Populate	Do not populate	Do not populate	DCU	
75	1	R18	75k	RES SMD 75K OHM 5% 1/8W 0805	RMCF0805JT75K0CT-ND	STACKPOLE	RMCF0805JT75K0	0805	
76	1	L2	4.7uH	INDUCTOR 4.7UH 300MA 0806	490-4044-1-ND	Murata	LQH2MNCN4R7M02L	LQM2MP_G0	

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated