


Complete solutions for all your video surveillance products




High-performance analog to complete the system:

TI offers a plethora of analog solutions that allow for the design of your next-generation video security systems complementing the new DM8168 and DMVA1 processors. Whether you need solutions to decode or filter video signals, power the processor or the full board, provide audio codec solutions, control touch screens, or simply to protect external interfaces such as HDMI from ESD events, TI is your one-stop shop with the all the easy-to-use tools available at your disposal.



Key TI products for IP camera

Function	Device	EVM/Demo	Features
Video processor	DMVA1, DM36x	DMVA	Simple / robust video analytics, Full DM36x pin-to-pin and software compatibility
PoE controller	TPS23753A	TPS23753AEVM-001	Single-chip solution w/ isolation
Analog front end	VSP2582		Complete 12-bit mixed-signal IC for CCD sensor outputs
Core and I/O power	TPS65053	TPS65053EVM-389	PMIC w/ 2 buck converters and 3 LDOs for processor power
Memory power	TPS51116	TPS51116EVM-001	Complete DDR, DDR2 and DDR3 synch buck controller
Audio codec	TLV320AIC3104	TLV320AIC3104EVM-K	Low-power stereo codec w/ 6 inputs, 6 outputs
Video amplifier	THS7315	THS7315EVM	3-Ch SDTV video amplifier with 5th-order filter
Clock	CDCE949	CDCE949PERF-EVM	Prog. 4-PLL VCXO clock w/ 2.5V or 3.3V LVCMOS outputs
Temp sensor	TMP175	TMP100EVM	Digital temp sensors w/ 2-wire interface




Key TI products for DVR / DVS

Function	Device	EVM/Demo	Features
Video processor	DM8168	TBD	4X HD video performance Complete DVR-on-a-chip
Video decoder	TVP5158	TVP5158EVM	4-Ch NTSC/PAL w/ independent scalers, noise reduction, and auto contrast, Seamless interface to DM8168
Ethernet PHY	TLK100	TLK100EXTEVM	10/100 BaseT with cable diagnostics
Core and I/O power	TPS65053	TPS65053EVM-389	PMIC w/ 2 buck converters and 3 LDOs for processor power
Memory power	TPS51116	TPS51116EVM-001	Complete DDR, DDR2 and DDR3 synch buck controller
System power	TPS54386	TLV320AIC3104EVM-K	Dual 3A non-synch buck converter w/ integrated high-side MOSFET, 600 kHz
Video amplifier	THS7314	THS7314EVM	3-Ch SDTV video amplifier with 5th-order filter
Clock	CDCE949	CDCE949PERF-EVM	Prog. 4-PLL VCXO clock w/ 2.5V or 3.3V LVCMOS outputs

Additional online information

▼ **Choose the right product to power your board!**



Zero in on analog solutions for your video/vision systems. ▲

Power-over-ethernet information:
www.ti.com/poe

Reference design information:
www.ti.com/ipcamera,
www.ti.com/dvr

Complete power solutions for TI's processors:
www.ti.com/processorpower

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products		Applications	
Amplifiers	amplifier.ti.com	Audio	www.ti.com/audio
Data Converters	dataconverter.ti.com	Automotive	www.ti.com/automotive
DLP® Products	www.dlp.com	Communications and Telecom	www.ti.com/communications
DSP	dsp.ti.com	Computers and Peripherals	www.ti.com/computers
Clocks and Timers	www.ti.com/clocks	Consumer Electronics	www.ti.com/consumer-apps
Interface	interface.ti.com	Energy	www.ti.com/energy
Logic	logic.ti.com	Industrial	www.ti.com/industrial
Power Mgmt	power.ti.com	Medical	www.ti.com/medical
Microcontrollers	microcontroller.ti.com	Security	www.ti.com/security
RFID	www.ti-rfid.com	Space, Avionics & Defense	www.ti.com/space-avionics-defense
RF/IF and ZigBee® Solutions	www.ti.com/lprf	Video and Imaging	www.ti.com/video
		Wireless	www.ti.com/wireless-apps

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2010, Texas Instruments Incorporated