Functional Safety Information

LM36x5C-Q1 Functional Safety FIT Rate, FMD, and Pin FMA



Table of Contents

1 Overview	
2 Functional Safety Failure In Time (FIT) Rates	
3 Failure Mode Distribution (FMD)	
4 Pin Failure Mode Analysis (Pin FMA)	
5 Revision History	

Overview www.ti.com

1 Overview

This document contains information for the LM36x5C-Q1 (WSON package) to aid in a functional safety system design. Information provided are:

- Functional Safety Failure In Time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (Pin FMA)

Figure 1-1 shows the device functional block diagram for reference.




Figure 1-1. Functional Block Diagram

The LM36x5C-Q1 were developed using a quality-managed development process, but were not developed in accordance with the IEC 61508 or ISO 26262 standards.



2 Functional Safety Failure In Time (FIT) Rates

This section provides Functional Safety Failure In Time (FIT) rates for the WSON package of the LM36x5C-Q1 based on the followingtwo different industry-wide used reliability standards:

- Table 2-1 provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- Table 2-2 provides FIT rates based on the Siemens Norm SN 29500-2

Table 2-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

FIT IEC TR 62380 / ISO 26262	FIT (Failures Per 10 ⁹ Hours)
Total Component FIT Rate	12
Die FIT Rate	7
Package FIT Rate	5

The failure rate and mission profile information in Table 2-1 comes from the Reliability data handbook IEC TR 62380 / ISO 26262 part 11:

Mission Profile: Motor Control from Table 11

Power dissipation: 600 mW
Climate type: World-wide Table 8
Package factor (lambda 3): Table 17b

Substrate Material: FR4EOS FIT rate assumed: 0 FIT

Table 2-2. Component Failure Rates per Siemens Norm SN 29500-2

Table	Category	Reference FIT Rate	Reference Virtual T _J
5	CMOS, BICMOS Digital, analog or mixed	25 FIT	55°C

The Reference FIT Rate and Reference Virtual T_J (junction temperature) in Table 2-2 come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.

5%

5%

3 Failure Mode Distribution (FMD)

RESET false trip or fails to trip

Short circuit any two pins

The failure mode distribution estimation for the LM36x5C-Q1 in Table 3-1 comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity and from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures due to misuse or overstress.

 Die Failure Modes
 Failure Mode Distribution (%)

 No output voltage
 35%

 Output not in specification -- voltage or timing
 45%

 SW driver FET stuck on
 10%

Table 3-1. Die Failure Modes and Distribution

The FMD in Table 3-1 excludes short circuit faults across the isolation barrier. Faults for short circuit across the isolation barrier can be excluded according to ISO 61800-5-2:2016 if the following requirements are fulfilled:

- 1. The signal isolation component is OVC III according to IEC 61800-5-1. If a SELV/PELV power supply is used, pollution degree 2/OVC II applies. All requirements of IEC 61800-5-1:2007, 4.3.6 apply.
- 2. Measures are taken to ensure that an internal failure of the signal isolation component cannot result in excessive temperature of its insulating material.

Creepage and clearance requirements should be applied according to the specific equipment isolation standards of an application. Care should be taken to maintain the creepage and clearance distance of a board design to ensure that the mounting pads of the isolator on the printed-circuit board do not reduce this distance.



4 Pin Failure Mode Analysis (Pin FMA)

This section provides a Failure Mode Analysis (FMA) for the pins of the LM36x5C-Q1. The failure modes covered in this document include the typical pin-by-pin failure scenarios:

- Pin short-circuited to Ground (see Table 4-2)
- Pin open-circuited (Table 4-3)
- Pin short-circuited to an adjacent pin (Table 4-4)
- Pin short-circuited to VIN (Table 4-5)

Table 4-2 through Table 4-5 also indicate how these pin conditions can affect the device as per the failure effects classification in Table 4-1.

Table 4-1. IT Classification of Failure Lifects		
Class	Failure Effects	
A	Potential device damage that affects functionality	
В	No device damage, but loss of functionality	
С	No device damage, but performance degradation	
D	No device damage, no impact to functionality or performance	

Table 4-1 TI Classification of Failure Effects

Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Device used within the Recommended Operating Conditions and the Absolute Maximum Ratings found in both LM636x5-Q1 data sheet.
- Configuration as shown in the Example Application Circuit found in the LM636x5-Q1 data sheet.

Figure 4-1 shows the LM36x5C-Q1 pin diagram for the WSON package. For a detailed description of the device pins please refer to the *Pin Configuration and Functions* section in the LM636x5-Q1 data sheet.




Figure 4-1. Pin Diagram for DRR0012E (WSON-12)



Table 4-2. Pin FMA for Device Pins Short-Circuited to Ground

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
SW	1	Damage to internal power FET or FETs, other internal circuits, or both	Α
BOOT	2	Damage to internal circuits	Α
N/C	3	No effect	D
VCC	4	Fault mode shuts the device off.	В
SYNC/MODE	5	Depends on exact application configuration. For the application circuit as shown in the <i>Example Application Circuit</i> in the device data sheet, no effect is produced. If a 0Ω jumper is used to connect the SYNC/MODE input to VCC, then the VCC output is pulled to ground; see short to ground on pin 4.	В
RESET	6	RESET functionality is lost.	В
FB	7	The regulator operates at the maximum duty cycle. The output voltage rises to nearly the input voltage (V _{IN}) level. Possible damage to customer load, output stage components, or both, can occur. No effect on the device.	В
N/C	8	No effect	D
AGND	9	No effect	D
EN	10	Loss of ENABLE functionality The device remains in shutdown mode.	В
N/C	11	No effect	D
VIN	12	The device does not operate. No output voltage is generated. Output capacitors discharge through input short. Large reverse current can damage device.	А
PGND	13	No effect	D

Table 4-3. Pin FMA for Device Pins Open-Circuited

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
SW	1	Loss of output voltage	В
BOOT	2	Loss of output voltage regulation; low or no output voltage. Damage to the internal device.	Α
N/C	3	No effect	D
VCC	4	VCC LDO is unstable. Loss of output voltage regulation and possible damage to internal circuits.	Α
SYNC/MODE	5	Internal pulldown places the device in auto mode.	В
RESET	6	Loss of RESET functionality	В
FB	7	Loss of output voltage regulation. Output voltage can rise or fall outside of intended regulation window. Possible damage to the customer load.	В
N/C	8	No effect	D
AGND	9	Loss of output voltage regulation. Possible damage to the internal circuits.	Α
EN	10	Loss of ENABLE functionality. Erratic operation; probable loss of regulation	В
N/C	11	No effect	D
VIN	12	Loss of output voltage	В
PGND	13	Possible device damage	Α



Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

Pin Name	Pin No.	Shorted to	Description of Potential Failure Effect(s)	Failure Effect Class
SW	1	воот	Loss of output regulation, possible damage to internal circuits	Α
воот	2	N/C	No effect	D
N/C	3	VCC	No effect	D
VCC	4	SYNC/MODE	Depends on exact application configuration. For application circuit as shown in the <i>Example Application Circuit</i> in the device data sheet, VCC is shorted to ground; see "short to ground on pin 4." For all other configurations, the effect is FPWM mode; loss of auto mode function.	В
SYNC/MODE	5	RESET	Depends on exact application configuration. For the application circuit as shown in the <i>Example Application Circuit</i> in the device data sheet, RESET is shorted to ground; see short to ground on pin 6. For all other configurations, the effect is either no change or erratic operation, loss of RESET, SYNC/MODE functionality, or both with possible damage to device internal circuits	A
FB	7	N/C	No effect	D
N/C	8	AGND	No effect	D
AGND	9	EN	Loss of enable function. The devices shut down.	В
EN	10	N/C	No effect	D
N/C	11	VIN	No effect	D

Table 4-5. Pin FMA for Device Pins Short-Circuited to VIN

Pin Name	Pin No.	Description of Potential Failure Effect(s)	Failure Effect Class
SW	1	Damage to internal power FET or FETs, other internal circuits, or both	Α
BOOT	2	Damage to internal circuits	Α
N/C	3	No effect	D
VCC	4	Damage to internal circuits for V _{IN} > 5.5V	Α
SYNC/MODE	5	Depends on exact application configuration. For application circuit as shown in the <i>Example Application Circuit</i> in the device data sheet, no damage occurs. For all other configurations, damage to internal circuits occurs for V _{IN} > 5.5V.	А
RESET	6	Damage to internal circuits	Α
FB	7	Damage to internal circuits	Α
N/C	8	No effect	D
AGND	9	Possible damage to internal circuits or package	Α
EN	10	No damage to device. Loss of ENABLE functionality	В
N/C	11	No effect	D
VIN	12	No effect	D
PGND	13	Possible damage to internal circuits or package	А

Revision History INSTRUMENTS
www.ti.com

5 Revision History

С	Changes from Revision * (June 2022) to Revision A (March 2024)				
•	Updated document title	2			
	Changed SW output to No output voltage in Failure Mode Distribution (FMD) section				
•	Changed SW output not in specification to Output not in specificationin				
	Failure Mode Distribution (FMD) section	4			
•	Corrected typo in Failure Mode Distribution (FMD) section				

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2024, Texas Instruments Incorporated