Highly integrated industrial drive to connect, control and communicate

TEXAS INSTRUMENTS

David Zaucha Applications, Processors

Thomas Leyrer System Architect, Industrial Communication and Control

Punya Prakash Business Manager, Processors

Texas Instruments

Introduction

With rising energy costs and increasing government regulations, energy-efficient systems are the need of the hour. Electric motors account for 40 to 50 percent of global energy consumption and the industry is focused on improving the overall productivity of the motors. Constant-speed drives are inherently inefficient; these are being actively replaced with adaptable-speed drives controlled by processors. This new connected motor control technology is predicted to reduce energy consumption by nearly 30 percent. With this transformation in drive solution and convergence of inverter and AC drives, it is especially important that the systems continue to be reliable while being more effective.

Continuing this trend of connected drive solutions, intelligent industrial systems are adopting digital motor feedback systems. This digitization of motor control feedback coupled with industrial Ethernet for communication provides for higher efficiency in factory and energy sectors. Connected drives have a variety of communication interfaces depending on the automation system used in the field. Commissioning the communication protocol in the field provides significant cost saving in product design and product completion.

The drives industry is adopting processor-based solutions which offer higher precision to connect, control and communicate. This white paper discusses the overall drive architecture with emphasis on the highly integrated industrial drive solution by Texas Instruments.

Rule-driven integrated industrial motor control

The primary entities of a industrial motor drive are motor control, industrial communication and application to manage control and communication functions. An intelligent modular design that integrates these core functions is able to reduce platform cost while increasing platform flexibility. A single-chip drive solution employs a hybrid architecture that has the design simplicity of a compact solution with the integrated capability to support a broad range of system solutions at an economical system cost. By using a programmable infrastructure, both the high performance of a differentiated system and the flexibility to support multiple protocols, algorithms and configurations can be achieved simultaneously in a compact and highly integrated package. Central to this architecture is a modular design which provides compact and deterministic interfaces between the real-time communication, application, and control functions to permit broad flexibility in system tailoring. The modular single-chip drive solution is implemented on this foundation by incorporating the motor control peripherals with the communications and application functions. With drive synchronization on a single chip, the latency between communication and control is significantly reduced.




Figure 1: Industrial drive architecture overview

A highly integrated industrial drive includes motor control, industrial communication and the application to manage control and communication functions on a single-chip solution. (See Figure 1.)

- The communications interface provides the real-time communications link and synchronized system timing with the field network. The communications interface is connected to a PLC or motion controller.
- The application provides the high-level control of the drive managing the overall drive communications and control functions. This can include configuration, startup/shutdown, status, operation, motion control and other management functions.
- The control portion includes the Field Of Control (FOC) algorithm, the motor PWM controller and the current and position feedback system components which provide quiet operation and long life.


These three components of the industrial drive architecture can

further be implemented in a variety of configurations. At a high level, there are three primary processor drive configurations in the industrial environment:

- Inverter
- Servo drive (single axis, motor integrated option)
- AC premium drive (multi axis, wide selection of power stage)

Inverter

Inverters are increasingly connected to a high layer control system and therefore the integration of industrial communication is moving from what was traditionally optional to being a standard feature. (See Figure 2.)








Figure 3: Servo drive with real-time Ethernet

For hot side primary drive configurations, a single chip with an integrated FOC can provide a low-cost one-axis drive. In this configuration, the isolation between the hot and cold domains is performed in the field bus interface.

Servo drive

The next increment is a cold side one-axis singlechip drive with a multi-protocol real-time Ethernet, multi-protocol encoder feedback and sigma-delta decimation filters. In this configuration, the isolation between the hot and cold domains is performed at the drive, current feedback and position feedback interface. The sigma-delta interface for current measurement provides a powerful solution when high isolation and high-precision current measurement performance are required. (See Figure 3 above.)

AC premium drive

The third architecture is a two-chip solution which provides a multi-axis drive with multiprotocol field bus and real-time Ethernet, advanced application algorithms, advanced control performance, increased hardware acceleration and high performance analog integration. (See Figure 4.)

Integration of communication function in drives

Communication is the backbone of all the industrial components for competent automation production systems. Traditional serial-based systems are moving to faster and more deterministic Ethernetbased real-time communication systems. Industrial




Figure 4: Multi-axis drive with real-time Ethernet

Ethernet offers higher speeds, increased connection distance and enables connection of more nodes than ever before. There are many different industrial Ethernet protocols driven by various industrial equipment manufacturers that help connect industrial systems, including motor drives. These protocols include EtherCAT[®], PROFINET[®], EtherNet/IP[™], Sercos[®] III, among others. For more information on various industrial communication standards and protocol please **refer to this link**.

| Ethernet and Fieldbus Protocols | Key Sponsors |
|---------------------------------|---|
| EtherCAT [®] | Beckhoff |
| EtherNet/IP™ | Rockwell Automation Schneider Electric |
| POWERLINK | B&R Automation |
| PROFIBUS® | Siemens |
| PROFINET [®] RT & IRT | Siemens |
| SERCOS [®] III | Rexroth Bosch group Schneider Electric |

Table 1: Some of the multiple industrialcommunications protocols and their key sponsors

A connected industrial drive solution

TI platform architecture includes a single consolidated processor that can perform motor/ motion control, real-time industrial Ethernet communications and data acquisition. The connected industrial drive is composed of an ARM[®] Cortex[®] processor plus a powerful set of programmable and fixed-function peripherals for industrial communications, measurement and control.

This permits a single device to replace multiple devices with a single easy-to-use, compact, flexible and high-performance solution. The singlechip, high-performance ARM Cortex processor includes floating-point acceleration to maximize the performance of the control loop and motion-control algorithms. (See Figure 5.)

TI processor architecture offers a quad-core programmable real-time unit (PRU) industrial communication subsystem (ICSS). This enables the Sitara[™] single-chip drive family to provide concurrent industrial Ethernet, feedback protocol and control functions. The ICSS system supports PROFINET, EtherCAT, PROFIBUS, EtherNet/IP, POWERLINK, SERCOS 3 protocols, among others. See Figure 6 on the following page.

Motor drives are used in a very diverse range of industrial applications and come with wide range of voltage and power levels. Industrial drives include, but are not limited to, AC and DC drives as well as servo drives that use a motor feedback system to



Figure 5: Texas Instruments highly integrated connected industrial drive solution




Figure 6: Integrated connected industrial drive building blocks

control and adjust the behavior and performance of servomechanisms.

The motor control functions include a motor Field Oriented Control (FOC), a multi-channel EnDat2.2 master per PRU, and multi-channel Sigma Delta Sinc3 Filter per PRU, plus multiple Pulse Width Modulators. The Sitara single-chip drive solution also includes a number of integrated subsystems to support industrial applications including a real-time clock, Quadrature Encoder Pulse (QEP) drivers, analogto-digital converters (ADC), a dual camera interface, dual CANs, dual Gigabit Ethernet interfaces and other peripheral interfaces (see Figure 7).




Figure 7: Connected industrial drive processor

The Sitara single-chip drive supports multiple absolute digital position encoder interfaces for absolute position/angle and speed feedback to support sensored FOC operation (see Table 2).

| Protocol | EnDAT 2.2 | Hiperface DSL | BiSS C |
|-----------------------|---------------------------------------|-----------------------------|---------------------------|
| Sponsor | Heidenhain | Sick Stegman | iC Haus |
| Phy interface | RS-485 | RS-485 | RS-422/485 |
| Speed | 100 kbit – 8/16 Mbit | 9.375 Mbit | 1/2/5/10 Mbit |
| Reach | 100 meter, 300m at lower speed. | 100 meter | 100 meter |
| Cable | 4 wire | 2 wire, motor integrated | 4 wire |
| Max frame length | ~ 31+116 bit | Continuous frame 117 bit | 64 bit / frame |
| Delay compensation | Yes | Yes | Yes |
| Oversampling | Yes | Yes | Yes |
| Overhead channels | Two additional | 8 V frames | 1 bit per frame |
| Synchronization | Start pulse – bit time | Async pulse | Start pulse – bit time |

Table 2: Multiple position encoder interfaces supported

Connected drive attributes of industrial drive software

The Sitara single-chip drive uses a modular software architecture which provides compact and deterministic interfaces between the realtime communication, application and control functions. The single-chip drive software is based upon the low-footprint TI RTOS Real-time kernel and the Industrial Software Development Kit. The SDK is optimized to support real-time industrial communications protocols such as EtherCAT, PROFIBUS, EtherNet/IP, PROFINET and others. In addition to real-time industrial communications, the SDK supports motor feedback protocols such as EnDAT and the Sigma-Delta Decimation filter for higher precision current sensing (see Figure 9 on the following page).




Figure 8: Sitara AM437x processor could also function as a multi-axis drive controller




Figure 9: Industrial drive software

Single-chip drive – control cycle

Figure 10 (on the following page) shows typical industrial communications operations. EtherCAT communication consists of cyclic and acyclic communications. The cyclic communications contain the normal process information. These communications are initiated by the PLC master or motion controller at a periodic interval (every 50 to 500 µs) to exchange information with the Sitara single-chip drive. The information that is transmitted to the PLC or motion controller by the Sitara single-chip drive can include measurements and status information. The received information from the motion controller or PLC can include position sequences and other control information. The real-time portion of the industrial communications operations are performed by the PRU-ICSS exchanging output and input information with the

communications stacks managed by the ARM. The received cyclic position sequences are translated by an ARM motion-control application into three motion-control sequences each communications cycle. The motion-control sequences provide the velocity / position input to a field-oriented control algorithm that generates 3-phase PWM motor control commands. The field-oriented control algorithm uses position and current feedback inputs from an EnDAT 2.2 encoder and a Delta Sigma modulator to provide closed-loop control. Status and error information from these operations are returned to the motion controller or PLC during the next communications cycle.

This processing uses only a fraction of the ARM's processing capacity. This permits the ARM to support other acyclic (non-periodic) communications and processing functions such as a web server to support other remote status, control and programming operations.





Figure 10: Connected industrial drive control cycle

Connected industrial motor control benchmark


Single-Chip Drive for Industrial Communications and Motor Control Reference Design (**TIDEP-0025**) is a design report of a single-chip motor control benchmark using a Sitara AM437x processor at 600 MHz under the TI-RTOS. The motor control benchmark configuration is composed of a single 3-phase motor drive with current and EnDAT 2.2 position feedback. Operating concurrently with the motor control is an EtherCAT slave communicating with PLC master at a 100-µs cycle time. The EtherCAT distributed clocks are used to provide a low-jitter distributed clock. (See Figure 11 on the following page.)

This benchmark demonstrates that a single-axis 47-kHz control loop speed is easily achievable with the 600-MHz AM437x processor with an ARM Cortex-A9 while simultaneously performing a 100-µs cycle time communication with a PLC master over the industrial Ethernet communication. While this benchmark is performed using TI-RTOS, more data on OS-independent interrupt latencies and further system-level optimization will be continued on this highly integrated single-chip industrial drive platform. (See Table 3 on the following page.)

| Function | Processing time | |
|--|-----------------------------------|--------------------------------------|
| | Level 4 (closed speed loop) | Level 5 (closed position loop) |
| ADC sampling and conversion | 1.33 µs | 1.33 µs |
| SYS/BIOS interrupt latency | 1.26 µs | 1.26 µs |
| FOC close current/torque loop to PWM update | 5.79 µs | 5.83 µs |
| Elapsed time – Sample to PWM update | 8.38 µs | 18.42 µs |
| 25% head room | 2.1 µs | 2.11 µs |
| Elapsed time + 25% headroom | 10.48 µs | 10.53 µs |
| Maximum operational rate | 47 kHz | 47 kHz |



Benchmark results






Figure 11: Single-chip drive motor control configuration and benchmark timing on AM437x processors

| More industrial communications TI Designs | | | |
|---|--|--|--|
| | • Single-Chip Drive for Industrial Communications and Motor Control | | |
| Ether CAT. | • EtherCAT for Connected Industrial Drives | | |
| | EtherCAT Communications Development Platform | | |
| EnDat 2.2 | EnDat2.2 for Connected Industrial Drives Reference Design for an Interface to a Position Encoder with EnDat 2.2 | | |
| $\Sigma\Delta$ | Isolated Current Shunt and Voltage Measurement Reference Design for Motor Drive | | |
| PROFO [®] Net | PROFINET Communications Development Platform | | |
| BISS | • ARM MPU with Integrated BiSS C Master Interface | | |
| EtherNet/IP> | EtherNet/IP Communications Development Platform | | |
| sercos | • SERCOS III Communications Development Platform | | |
| ETHERNET POWERLINK | • Ethernet POWERLINK Development Platform | | |
| PROFU [®] BUS | PROFIBUS Communications Development Platform | | |

Table 3: Some of the multiple industrialcommunications protocols and their key sponsors

Conclusion

The AM437x processor with integrated PRU-ICSS provides the flexibility to enable multiple protocols for position feedback on motor control and at the same time also enable multiple protocols for communication. This industry's first and only hybrid *multi-multi protocol* solution provides the ability to commission protocols in the field, in-turn providing significant cost saving in product design and product completion. The principal advantage of having a programmable solution architected for time-critical applications is the flexibility to adopt the ever-changing standards in industrial enablement while significantly reducing the overall latency.

Among the communication protocols supported by the PRU are PROFIBUS, EtherCAT, PROFINET, EtherNet/IP, SERCOS III, POWERLINK and others. The quad-core PRU in the AM437x processor is capable of supporting communication protocols and a motor feedback control protocol such as EnDat 2.2, BISS, HiperFace and others in parallel, making it a compelling single-chip industrial drive solution. The AM437x Industrial Development Kit (IDK) provides a development platform for customers to evaluate this highly differentiated multi-*multi protocol* to connect, control and communicate industrial drives using one single processor.

With the single-chip industrial drive solution, higher integration can be achieved while improving the overall product efficiency. With system integration of functional blocks to connect, control and communicate, Texas Instruments offers a solution that equips customers to build compact and differentiated products achieving better energy savings.

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

Sitara is a trademark of Texas Instruments. All trademarks are the property of their respective owners.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

| Products | | Applications | |
|------------------------------|---------------------------------|-------------------------------|-----------------------------------|
| Audio | www.ti.com/audio | Automotive and Transportation | www.ti.com/automotive |
| Amplifiers | amplifier.ti.com | Communications and Telecom | www.ti.com/communications |
| Data Converters | dataconverter.ti.com | Computers and Peripherals | www.ti.com/computers |
| DLP® Products | www.dlp.com | Consumer Electronics | www.ti.com/consumer-apps |
| DSP | dsp.ti.com | Energy and Lighting | www.ti.com/energy |
| Clocks and Timers | www.ti.com/clocks | Industrial | www.ti.com/industrial |
| Interface | interface.ti.com | Medical | www.ti.com/medical |
| Logic | logic.ti.com | Security | www.ti.com/security |
| Power Mgmt | power.ti.com | Space, Avionics and Defense | www.ti.com/space-avionics-defense |
| Microcontrollers | microcontroller.ti.com | Video and Imaging | www.ti.com/video |
| RFID | www.ti-rfid.com | | |
| OMAP Applications Processors | www.ti.com/omap | TI E2E Community | e2e.ti.com |
| Wireless Connectivity | www.ti.com/wirelessconnectivity | | |

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated