CC3100 MODBOOST/ TIDC-CC3100MODBOOST

BOM Revision - 1.0 Date : 11-November -2014

NO.	Qty	Part Reference	Value	Manufacturer	Mfr. PN	Description
1	1	C15	0.1uF	Murata	GRM155R61A104KA01D	CAP CER 100nF 10% 10V SMD 0402 GP/HF X5R 0.5mm
		R15 R22 R29 R36 R37 R38 R44 R46 R48 R65 R66 R73	0.24.		01111120110127112011111012	S. H. CELL EGOIN 1070 107 GIND 0102 GI / HI 7/GIL GISHINI
2	14	R81 R82	0ohm	Yageo	RC0402JR-070RL	RES C SMD 0402 0ohm 5% GP/HF
3	2	R12 R14	100ohm	Yageo	RC0402JR-07100RL	RES C SMD 0402 100ohm 5% GP/HF
4	4	R4 R7 R112 R113	100Kohm	Yageo	RC0402FR-07100KL	RES C SMD 0402 1000nm 1% GP/HF
5	2	C65 C66	100k6iiiii	MURATA	GRM32ER60J107ME20L	CAP CER 100uF 20% 6.3V SMD 1210 GP/HF X5R 2.5mm
6	4	R8 R114 R209 R210	10Kohm	Yageo	RC0402FR-0710KL	RES C SMD 0402 10Kohm 1% GP/HF
7	2	C3 C7	10nF	MURATA	GRM155R71H103KA88D	CAP CER 10nF 10% 50V SMD 0402 GP/HF X7R T=0.5mm
8	1	C67	10pF			CAP CER 101F 10% 30V 3MD 0402 GP/HF X/K 1-0.5111111
9	1	C64	1.0pF	WALSIN	0402N100C500LT	CAP CER 1.0pF +-0.25pF 50V SMD 0402 GP/HF NPO U.SHIIII
		R13	150K	WALSIN TA-I	0402N1R0C500LT RM04FTN1503	EU-GP RES C SMD 0402 150Kohm 1% GP/HF
10	1	SW1 SW2 SW3				•
11	3	R9 R20	SW-4PIN	POWERWAY	DTST-61K-Q RC0402FR-071KL	SW TACT 50mA 12V DIP ST GP
12	2		1Kohm	Yageo		RES C SMD 0402 1Kohm 1% GP/HF
13	1	C47	1uF	MURATA	GRM155R60J105KE19D	CAP CER 1uF 10% 6.3V SMD 0402 GP/HF X5R 0.5mm
14	1	L1	1uH	MURATA	LQH3NPN1R0MM0L	CN-GP IND WW 1uH 20% 1.4A 0.044ohm SMD GP/
15	1	ANT1	2.4GHz ANT	Taiyo_Yuden	AH316M245001-T	2.4G WIFI chip antenna
17	1	C23	22pF	MURATA	GRM1555C1H220JA01D	CN-GP CAP CER 22pF 5% 50V SMD 0402 GP/HF N
18	1	C4	22uF	MURATA	GRM21BR60J226ME39L	CN-GP CAP CER 22uF 20% 6.3V SMD 0805 GP/HF
18.1	0	C4	22uF	TDK	C2012X5R0J226MT	CN-GP CAP CER 22uF 20% 6.3V SMD 0805 GP/HF
19	1	C17	2.2uF	MURATA	GRM21BR71C225KA12L	CAP CER 2.2uF 10% 16V SMD 0805 GP/HF X7R T=1.25mm
19.1	0	C17	2.2uF	WALSIN	0805B225K160CT	CAP CER 2.2uF 10% 16V SMD 0805 GP/HF X7R T=1.25mm
20	2	R71 R72	270ohm		RC0402JR-07270RL	RES C SMD 0402 270ohm 5% GP/HF
21	1	R78	3.3K	TA-I	RM04JTN332	RES C SMD 0402 3.3Kohm 5% GP/HF
22	1	L4	3.6nH	TAIYO	HK10053N6S-T	IND C 3.6nH 0.3nH 300mA 0.2ohm Q=8 SMD 0402 GP/HF
23	1	R205	330ohm		RC0402FR-07330RL	RES C SMD 0402 330ohm 1% GP/HF
24	2	R77 R84	33k	TA-I	RM04FTN3302	RES C SMD 0402 33Kohm 1% GP/HF
25	1	R21	39K	TA-I	RM04FTN3902	EU-GP RES C SMD 0402 39Kohm 1% GP/HF
26	1	R5	430K	WALSIN	WR04X4303FTL	RES C SMD 0402 430Kohm 1% GP
27	2	FB17 FB18	60R	CHILISIN	UPB160808T-600Y-N	BEAD C 60ohm 25% 4A 0.02ohm SMD 0603 GP/HF
28	1	J8	CON3X1	CVILUX	CH31032V200	HEADER PIN 3P 2.54mm DIP MALE ST GP
29	1	J2	CONN_U.FL	FOXCONN	KK23017-01-7F	HEADER RF 1*1PORT D0.5/D2.0mm SMD MALE ST GP/HF
30	1	U1	TLV62090	TI	TLV62090RGTR	IC DC-DC 2.5~5.5V SMD QFN16 GP TLV62090RGTR
31	1	D8	DIODE	DIODES	B240A-13-F	DIODE SBD 40V 2A SMD SMA GP B240A-13-F DIODES
32	2	J9 J10	Header Male 2x10	Samtec	SSQ-110-03-G-D	
34	2	J5 J6	JUMPER MALE	CVILUX	CH31022V202	HEADER PIN 1*2P 2.54mm DIP MALE ST GP
35	1	D6	LED_Green	LITEON	LTST-C190KGKT	LED CHIP 35mcd G 571nm 2P SMD 1.6*0.8mm GP/HF LTST-C190KGKT
36	1	D1	LED_Orange	LITEON	LTST-C190KFKT	LED CHIP 60mcd O 605nm 2P SMD 1.6*0.8mm GP/HF LTST-C190KFKT
37	1	D5	LED_Red	LITEON	LTST-C190KRKT	LED CHIP 45~180mcd R 624~638nm 2P SMD 1.6*0.8mm GP/HF
38	1	J7	USB-MicroB	POWERWAY	SUA-160M3B-L2E-TR1	CONN MICRO USB B 5PIN 0.65mm SMD FEMALE RT GP
39	1	J3	RF Connector	MURATA	MM8030-2610RJ3	HEADER RF 1*1PORT D=0.5/1.35mm SMD FEMALE ST GP
40	2	Q7 Q8	BSS138LT3G	On Semi	BSS138LT3G	MOSFET N-CH 50V 200MA SOT-23
41	3		JUMPER FEMALE	FOXCONN	SJ2520H-A0	CONN JUMPER 2P 2.54mm FEMALE RT GP
42	1	РСВ	PCB	ZHENDING/APCB	307.00587.025	PCB 2L OSP REV.025 8PCS GP/HF 43.18*50.8mm 95.1200T00
43	0.2		SOLDER PASTE	KOKI	S3X58-M500	CN-GP SOLDER PASTE S3X58 M500 GP/HF
43.1	0		SOLDER PASTE	KOKI	S01X7C58-M500	CN-GP SOLDER PASTE S01X7C58-M500 GP/HF
44	2	D3 D4	DIODE	On Semi	MBR130T1G	DIODE SBD 30V 1A SMD SOD123 GP

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, Is GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.