

Bill of Materials

TI DESIGNS

TIDA-00574

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint
1	1	!PCB		Printed Circuit Board	Any	TIDA-00574		
2	6	C0, C1, C2, C3, C30, C31	22uF	CAP, CERM, 22 μ F, 10 V, +/-	Taiyo Yuden	LDK105EBJ226MV-F		0402
3	4	C4, C5, C6, C7	10uF	CAP, CERM, 10 μ F, 6.3 V, +/-20%, X5R, 0402	MuRata	GRM155R60J106ME44D		0402
4	2	C5_1, C6_1	22uF	CAP, CERM, 22uF, 10V, +/-20%, X5R, 0805	Taiyo Yuden	LMK212BJ226MG-T	-	0805
5	2	C5_2, C6_2	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	Kemet	C0603C106M9PACTU	-	0603
6	1	C8	0.1uF	CAP, CERM, 0.1uF, 10V, +/-10%,	Samsung	CL03A104KP3NNNC	GMD033R60J104KE11	0201
7	1	C9	68uF	CAP, TA, 68 μ F, 16 V, +/- 20%,	Panasonic	16TQC68MYF		7.3x2.0x4.3mm
8	1	C10	22uF	CAP, CERM, 22 μ F, 16 V, +/-	MuRata	GRM32ER61C226KE20L		1210
9	2	C11, C29	10pF	CAP, CERM, 10pF, 50V, +/-5%,	MuRata	GRM1885C1H100JA01D		0603
10	2	C12, C13	15pF	CAP, CERM, 15pF, 100V, +/-5%, C0G/NP0, 0603	MuRata	GRM1885C2A150JA01D		0603
11	5	C14, C21, C23, C39, C48	10uF	CAP, CERM, 10uF, 16V, +/-20%,	Taiyo Yuden	EMK107BBJ106MA-T		0603
12	13	C15, C16, C17, C18, C19,	0.1uF	CAP, CERM, 0.1uF, 25V, +/-10%,	MuRata	GRM188R71E104KA01D		0603
13	4	C27, C32, C36, C42	1uF	CAP, CERM, 1 μ F, 10 V, +/- 10%, X7S, 0402	TDK	C1005X7S1A105K050BC		0402
14	1	C34	10uF	CAP, CERM, 10uF, 16V, +/-10%, X5R, 0805	Taiyo Yuden	EMK212BJ106KG-T		0805
15	5	C37, C41, C43, C45, C47	1uF	CAP, CERM, 1uF, 25V, +/-10%, X5R, 0603	MuRata	GRM188R61E105KA12D		0603
16	1	C40	0.01uF	CAP, CERM, 0.01uF, 50V, +/-10%, X5R, 0603	MuRata	GRM188R61H103KA01D		0603
17	1	C49	2200pF	CAP, CERM, 2200 pF, 25 V, +/-10%, X5R, 0402	MuRata	GRM155R61E222KA01D		0402
18	1	C50	47uF	CAP, CERM, 47 μ F, 10 V, +/-10%, X5R, 1210	MuRata	GRM32ER61A476KE20L		1210
19	1	C51	100uF	CAP, Polymer, 100 μ F, 6.3 V, +/-20%, 0.018 ohm, 7343-20 SMD	Panasonic	6TPE100MI		7343-20
20	3	FID1, FID2, FID3		Fiducial mark. There is nothing to buy or mount.	N/A	N/A		Fiducial
21	4	H1, H2, H3, H4		MACHINE SCREW PAN	B&F Fastener Supply	NY PMS 440 0050 PH	-	Screw
22	4	H5, H6, H7, H8		Standoff, Hex, 0.5"L #4-40 Nylon	Keystone	1902C	-	Standoff
23	1	J4		Header, TH, 100mil, 2x2, Gold	Samtec, Inc.	TSW-102-07-G-D	-	TSW-102-07-G-

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint
24	1	J6		Conn Rcpt Mini USB2.0 Type B	TE Connectivity	1734035-2		USB Mini Type B
25	1	J9		Header, TH, 100mil, 2x1, Gold	Samtec, Inc.	TSW-102-07-G-S	-	TSW-102-07-G-
26	4	L0, L1, L2, L3	470nH	Inductor, Shielded, Metal	Toko	DFE201610R-H-R47M		2.0x1.0x1.6mm
27	2	L4, L6	10uH	Inductor, Wirewound, Ferrite, 10uH, 0.12A, 0.5 ohm, SMD	Taiyo Yuden	LB2012T100KR		0805
28	1	R1	0.01	RES, 0.01 ohm, 1%, 3W, 2512 High Power Current Sense Chip Resistor	Bourns	CRA2512-FZ-R010ELF	-	2512
29	3	R2, R3, R6	1.8k	RES, 1.8k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06031K80JNEA	-	0603
30	1	R4	6.80k	RES, 6.80k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-076K8L		0603
31	2	R5, R7	39.0	RES, 39.0 ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-0739RL		0603
32	1	R8	47.0k	RES, 47.0k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-0747KL		0603
33	1	R9	27.0k	RES, 27.0k ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-0727KL		0603
34	8	R10, R11, R13, R14, R15, R16, R17, R22	0	RES, 0 ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW06030000Z0EA		0603
35	2	R12, R23	1.00	RES, 1.00 ohm, 1%, 0.1W, 0603	Yageo America	RC0603FR-071RL		0603
36	1	R18	274	RES, 274, 1%, 0.063 W, 0402	Vishay-Dale	CRCW0402274RFKED		0402
37	1	R19	105k	RES, 105 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW0402105KFKED		0402
38	2	R20, R21	1.00k	RES, 1.00k ohm, 1%, 0.1W, 0603	Vishay-Dale	CRCW06031K00FKEA		0603
39	1	R24	7.87k	RES, 7.87 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW04027K87FKED		0402
40	1	R25	68.1k	RES, 68.1 k, 1%, 0.063 W, 0402	Vishay-Dale	CRCW040268K1FKED		0402
41	1	R29	470k	RES, 470k ohm, 5%, 0.1W, 0603	Vishay-Dale	CRCW0603470KJNEA		0603
42	1	R_J1	0	RES, 0 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04020000Z0ED		0402
43	3	SH-J9, SH-J10, SH-J12	1x2	Shunt, 100mil, Gold plated, Black	3M	969102-0000-DA	SNT-100-BK-G	Shunt
44	10	TP1, TP2, TP3, TP4, TP5, TP6, TP9, TP12, TP15, TP19	Yellow	Test Point, TH, Miniature, Yellow	Keystone	5004	-	Keystone5004
45	2	TP11, TP13	Double	Terminal, Turret, TH, Double	Keystone	1502-2		Keystone1502-2
46	1	U1		LP8758 Multiphase 4-Core Step-Down Converter, YFF0035	Texas Instruments	LP8758		YFF0035
47	1	U2		AT91SAM ARM-based Flash MCU, LQFP100	Atmel	ATSAM3U2C-AU		100 pin LQFP
48	1	U3		Dual Linear Regulator with 300mA and 150mA Outputs and Power-On-Reset, 10-pin LLP, Pb-Free	Texas Instruments	LP3996SD-1833/NOPB		SDA10A
49	1	U4		SOT-23 Precision Low Dropout Voltage Reference	Texas Instruments	LM4132AMF-2.5		MF05A

Item	Qty	Reference	Value	Part Description	Manufacturer	Manufacturer Part Number	Alternate Part	PCB Footprint
50	1	U5		3A SIMPLE SWITCHER Power Module with 4.5V-14.5V Input in QFN Package, RUQ0047A	Texas Instruments	LMZ31503RUQ		RUQ0047A
51	1	U6		Ultra Low-Noise, 250-mA Linear Regulator for RF and Analog Circuits - Requires No Bypass Capacitor, YKE0004AAAA	Texas Instruments	LP5907UVE-2.5/NOPB		YKE0004AAAA
52	1	U8		150mA Linear Voltage Regulator for Digital Applications, 4-pin Micro SMD, Pb-Free	Texas Instruments	LP3990TL-1.35/NOPB		TLA04AMA
53	7	VOUT0, VOUT1, VOUT2, VOUT3, VOUT5, VOUT6, X4_Vin 12V	2x1	Conn Term Block, 2POS, 5.08mm, TH	Phoenix Contact	1715721		2POS Terminal Block
54	2	X5, X10		Header, 2 Pos, 6A, 63V	Phoenix Contact	1725656		6.2x8.5x5.54 mm
55	1	X6		Terminal Block, 8x1, 2.54 mm, TH	Phoenix Contact	1725711		8POS Terminal Block
56	1	Y1		Crystal, 12Mhz, 18pF, SMD	Abracon Corpotation	ABM3-12.000MHZ-B2-T		ABM3
57	0	C0_1, C1_1, C2_1, C3_1	22uF	CAP, CERM, 22uF, 10V, +/-20%, X5R, 0805	Taiyo Yuden	LMK212BJ226MG-T	-	0805
58	0	C0_2, C1_2, C2_2, C3_2	10uF	CAP, CERM, 10uF, 6.3V, +/-20%, X5R, 0603	Kemet	C0603C106M9PACTU	-	0603
59	0	J0		SMT Jumper Link	Harwin Inc	S1911-46R	5102	S1911-46R
60	0	J12, J13, J14, J15, J16, J17	0	RES, 0 ohm, 5%, 0.063W, 0402	Vishay-Dale	CRCW04020000Z0ED		0402
61	0	LBL1		Thermal Transfer Printable Labels, 1.250" W x 0.250" H - 10,000 per roll	Brady	THT-13-457-10		PCB Label 1.25"H x 0.250"W
62	0	TP10, TP14, TP16, TP17, TP18		Header, TH, 100mil, 2x1, Gold plated, 230 mil above insulator	Samtec, Inc.	TSW-102-07-G-S	-	TSW-102-07-G-S
63	0	X7, X9		Connector, 7 pos, 2.54mm, R/A, SMT	Samtec	OPP-07-01-T-S-M		30x3.6x9.2mm

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.