

Filename: Pro2F34.tmp  
 Variant: 001  
 Generated: 5/22/2017 10:07:26 AM  
 TID #: N/A



PMP20850 REV A Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	C1, C2	2	2.2uF	C1210C225K1RACTU	Kemet	CAP, CERM, 2.2 uF, 100 V, +/- 10%, X7R, 1210	1210
2	C3	1	330uF	APXF6R3ARA331MF80G	Chemi-Con	CAP, Aluminum Polymer, 330 uF, 6.3 V, +/- 20%, 0.009 ohm, D6.3xL7.7mm SMD	D6.3xL7.7mm
3	C4, C6, C10, C15, C16	5	1uF	06033C105KAT2A	AVX	CAP, CERM, 1 uF, 25 V, +/- 10%, X7R, 0603	0603
4	C5	1	0.1uF	CC1206KKX7RYBB104	Yageo America	CAP, CERM, 0.1 uF, 250 V, +/- 10%, X7R, 1206	1206
5	C7	1	1uF	UMK107AB7105KA-T	Taiyo Yuden	CAP, CERM, 1 uF, 50 V, +/- 10%, X7R, 0603	0603
6	C8	1	22uF	TMK325B7226MM-TR	Taiyo Yuden	CAP, CERM, 22 uF, 25 V, +/- 20%, X7R, 1210	1210
7	C9	1	1000pF	GR442QR73D102KW01L	MuRata	CAP, CERM, 1000 pF, 2000 V, +/- 10%, X7R, 1808	1808
8	C11	1	0.033uF	GRM155R71A333KA01D	MuRata	CAP, CERM, 0.033 uF, 10 V, +/- 10%, X7R, 0402	0402
9	C12	1	1000pF	C0402C102J3RACTU	Kemet	CAP, CERM, 1000 pF, 25 V, +/- 5%, X7R, 0402	0402
10	C13	1	100pF	0402YC101KAT2A	AVX	CAP, CERM, 100 pF, 16 V, +/- 10%, X7R, 0402	0402
11	C14	1	0.047uF	C1005X7R1C473K050BC	TDK	CAP, CERM, 0.047 uF, 16 V, +/- 10%, X7R, 0402	0402
12	C17	1	22uF	C4532X7R1E226M250KC	TDK	CAP, CERM, 22 uF, 25 V, +/- 20%, X7R, 1812	1812
13	D1, D2, D4, D5	4	100V	MMDL914-TP	Micro Commercial Components	Diode, Switching, 100 V, 0.2 A, SOD-323	SOD-323
14	D3	1	12V	BZT52C12T-7	Diodes Inc.	Diode, Zener, 12 V, 300 mW, SOD-523	SOD-523
15	GND, PGND	2		5011	Keystone	Test Point, Multipurpose, Black, TH	Black Multipurpose Testpoint
16	J1, J2	2		ED120/2DS	On-Shore Technology	Terminal Block, 5.08 mm, 2x1, Brass, TH	2x1 5.08 mm Terminal Block
17	L1	1	2.8uH	PG0077.282NLT	Pulse Engineering	Inductor, Flat Wire, 2.8 uH, 19 A, 0.0042 ohm, SMD	14x13mm
18	Q1, Q6	2	25V	CSD16414Q5	Texas Instruments	MOSFET, N-CH, 25 V, 100 A, DQH0008A (VSON-CLIP-8)	DQH0008A
19	Q2, Q3	2	60 V	MMBT2907A	Fairchild Semiconductor	Transistor, PNP, 60 V, 0.8 A, SOT-23	SOT-23
20	Q4	1	-150V	IRF6216TRPBF	International Rectifier	MOSFET, P-CH, -150 V, -2.2 A, SOIC-8	SOIC-8
21	Q5	1	150V	Si4488DY-T1-GE3	Vishay-Siliconix	MOSFET, N-CH, 150 V, 3.5 A, SO-8	SO-8
22	Q7	1	50 V	PBSS4250X,115	Nexperia	Transistor, NPN, 50 V, 2 A, SOT-89	SOT-89
23	R1, R2	2	10	CRCW060310R0JNEAHP	Vishay-Dale	RES, 10, 5%, 0.25 W, 0603	0603
24	R3, R4, R13	3	10.0k	CRCW040210K0FKED	Vishay-Dale	RES, 10.0 k, 1%, 0.063 W, 0402	0402
25	R5	1	0.068	MCR50JZHFSR068	Rohm	RES, 0.068, 1%, 0.5 W, AEC-Q200 Grade 0, 2010	2010
26	R6	1	0	CRCW04020000Z0ED	Vishay-Dale	RES, 0, 5%, 0.063 W, 0402	0402
27	R7, R12	2	499	CRCW0402499RFKED	Vishay-Dale	RES, 499, 1%, 0.063 W, 0402	0402
28	R8, R9	2	1.00k	CRCW04021K00FKED	Vishay-Dale	RES, 1.00 k, 1%, 0.063 W, 0402	0402
29	R10	1	10.0k	ERJ-2RKF1002X	Panasonic	RES, 10.0 k, 1%, 0.1 W, 0402	0402
30	R11	1	1.00k	ERJ-2RKF1001X	Panasonic	RES, 1.00 k, 1%, 0.1 W, 0402	0402
31	R14, R16	2	100k	RC0402FR-07100KL	Yageo America	RES, 100 k, 1%, 0.0625 W, 0402	0402
32	R15	1	75.0k	CRCW040275K0FKED	Vishay-Dale	RES, 75.0 k, 1%, 0.063 W, 0402	0402
33	R17	1	49.9k	CRCW040249K9FKED	Vishay-Dale	RES, 49.9 k, 1%, 0.063 W, 0402	0402
34	R18	1	6.49k	CRCW04026K49FKED	Vishay-Dale	RES, 6.49 k, 1%, 0.063 W, 0402	0402
35	R19	1	6.04k	CRCW04026K04FKED	Vishay-Dale	RES, 6.04 k, 1%, 0.063 W, 0402	0402
36	R20	1	3.74k	CRCW04023K74FKED	Vishay-Dale	RES, 3.74 k, 1%, 0.063 W, 0402	0402
37	T1	1	100uH	PA3856.001NLT	Pulse Engineering	Transformer, 100 uH, SMT	SMD, 10-Leads, Body 14.5x14.5mm
38	TP1	1		5008	Keystone	Test Point, Compact, Orange, TH	Orange Compact Testpoint
39	U1	1		UCC2897ARGPT	Texas Instruments	Advanced Current-Mode Active Clamp PWM Controller with Current Control, -40 to +125 degC, 20-pin QFN (RGP), Green (RoHS & no Sb/Br)	RGP0020D
40	U2	1		TCMT1107	Vishay-Semiconductor	Optocoupler, 3.75 kV, 80-160% CTR, SMT	SOP-4
41	U5	1		TLV431AIDBZR	Texas Instruments	Low Voltage Adjustable Precision Shunt Regulator, 39 ppm / degC, 15 mA, -40 to 85 degC, 3-pin SOT-23 (DBZ), Green (RoHS & no Sb/Br)	DBZ0003A
42	Vin, Vout	2		5010	Keystone	Test Point, Multipurpose, Red, TH	Red Multipurpose Testpoint

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated