


All measurements taken with a 48V input unless otherwise noted.

Efficiency



J2	J2	J1	J1	
Iout	Vout	Iin	Vin	Eff
0.00	5.051	0.038	48.00	0.0%
0.25	5.050	0.064	48.00	41.1%
0.50	5.050	0.091	48.00	57.8%
0.75	5.050	0.118	48.00	66.9%
1.00	5.049	0.145	48.00	72.5%
1.50	5.049	0.199	48.00	79.3%
2.00	5.048	0.254	48.00	82.8%
2.50	5.047	0.309	48.00	85.1%
3.00	5.046	0.365	48.00	86.4%
3.50	5.046	0.421	48.00	87.4%
4.00	5.045	0.479	48.00	87.8%
4.50	5.044	0.536	48.00	88.2%
5.00	5.043	0.594	48.00	88.4%
5.50	5.042	0.653	48.00	88.5%
6.00	5.041	0.712	48.00	88.5%

Ripple and Noise

Ripple measurements taken with a 6A load and 20MHz BWL.

Output Ripple (J2)
20mV/div, 2usec/div
Measured 33.3mV pk-pk:




Input Ripple (J1)
20mV/div, 2usec/div
Measured 41.3mV pk-pk:




Dynamic Loading

Load Step
3A to 6A step load
200mV/div, 500usec/div
Measured 407mVpp:




Turn On Response

6A Load, 2msec/div
Top: Output, 1V/div
Bottom: Input, 20V/div:




0A Load, 2msec/div
Top: Output, 1V/div
Bottom: Input, 20V/div:




Waveforms


Vds, Q3, 60V Input, 6A Load
20V/div, 2usec/div



Vds, Q1, 60V Input, 0A Load
10V/div, 2usec/div




Vds, Q1, 60V Input, 6A Load
10V/div, 20usec/div



Stability

Loop response of the converter with a 6A load.



BW=4Khz PM=51 degrees GM=10dB

Thermal:





Photo:



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated