


1 Startup

The photo below shows the startup waveforms. The input voltage is 12V, the outputs are not loaded. The timebase is set to 1ms/Division.

Channel 1 : 5.0V Output – Yellow (1V/Division)

Channel 2 : 3.3V Output – Pink (1V/Division)




2 Shutdown

The photo below shows the shutdown waveforms. The input voltage is 12V. The timebase is set to 1ms/Division. The outputs are fully loaded.

Channel 1 : 5.0V Output – Yellow (1V/Division)


Channel 2 : 3.3V Output – Pink (1V/Division)




3 Output Ripple Voltage

The output voltage ripple is shown in the figures below. The input is 12V.

Channel 3 : Output Voltage – Blue (20mV/Division; AC Coupled)



5V Output; 5A Load




3.3V Output; 5A Load


4 Load Transients

The photos below show the transient response. The current is pulsed from 0.5A to 4.5A. The timebase is set to 100us/Division.

Channel 3 : Output Voltage – Blue (50mV/Division)
Channel 4 : Output Current – Green (2A/Division)




5V Output



3.3V Output


5 Efficiency


The efficiency of the converter is shown in the figure below.



6 Load Regulation

The load regulation is shown in the figures below.





7 Switching Waveforms

The plots below show the switching waveforms for the converter. The input is 12V.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated