Functional Safety Information TPS3435, TPS3436, TPS35, and TPS36 Functional Safety FIT Rate, FMD and Pin FMA for Pinout B

TEXAS INSTRUMENTS

Table of Contents

1 Overview	.2
2 Functional Safety Failure In Time (FIT) Rates	3
3 Failure Mode Distribution (FMD)	
4 Pin Failure Mode Analysis (Pin FMA)	
4 Pin Failure Mode Analysis (Pin FMA)	.5

Trademarks

All trademarks are the property of their respective owners.




1 Overview

This document contains information for TPS3435, TPS3436, TPS35, and TPS36, (DDF package) to aid in a functional safety system design. Information provided are:

- Functional Safety Failure In Time (FIT) rates of the semiconductor component estimated by the application of industry reliability standards
- · Component failure modes and their distribution (FMD) based on the primary function of the device
- Pin failure mode analysis (Pin FMA)

Figure 1-1 and Figure 1-2 show the device functional block diagrams for reference.






Figure 1-1. TPS34 and TPS35 Pinout Option B

TPS3435, TPS3436, TPS35, and TPS36 were developed using a quality-managed development process, but were not developed in accordance with the IEC 61508 or ISO 26262 standards.



2 Functional Safety Failure In Time (FIT) Rates

This section provides Functional Safety Failure In Time (FIT) rates for TPS3435, TPS3436, TPS35, and TPS36 based on two different industry-wide used reliability standards:

- Table 2-1 provides FIT rates based on IEC TR 62380 / ISO 26262 part 11
- Table 2-2 provides FIT rates based on the Siemens Norm SN 29500-2

Table 2-1. Component Failure Rates per IEC TR 62380 / ISO 26262 Part 11

FIT IEC TR 62380 / ISO 26262	FIT (Failures Per 10 ⁹ Hours)
Total Component FIT Rate	4
Die FIT Rate	2
Package FIT Rate	2

The failure rate and mission profile information in Table 2-1 comes from the Reliability data handbook IEC TR 62380 / ISO 26262 part 11:

- Mission Profile: Motor Control from Table 11
- Power dissipation: 364 µW
- Climate type: World-wide Table 8
- Package factor (lambda 3): Table 17b
- Substrate Material: FR4
- EOS FIT rate assumed: 0 FIT

Table 2-2. Component Failure Rates per Siemens Norm SN 29500-2

Table	Category	Reference FIT Rate	Reference Virtual T _J
5	CMOS, BICMOS Digital, analog / mixed	25 FIT	55°C

The Reference FIT Rate and Reference Virtual T_J (junction temperature) in Table 2-2 come from the Siemens Norm SN 29500-2 tables 1 through 5. Failure rates under operating conditions are calculated from the reference failure rate and virtual junction temperature using conversion information in SN 29500-2 section 4.

3 Failure Mode Distribution (FMD)

The failure mode distribution estimation for TPS3435, TPS3436, TPS35, and TPS36 in Table 3-1 and Table 3-2 comes from the combination of common failure modes listed in standards such as IEC 61508 and ISO 26262, the ratio of sub-circuit function size and complexity and from best engineering judgment.

The failure modes listed in this section reflect random failure events and do not include failures due to misuse or overstress.

Die Failure Modes	Failure Mode Distribution (%)					
False Assert on Reset or WDO	1%					
RESET or WDO remain asserted	3%					
Incorrect Timing Operation (Early or late WDO faults, Reset/WDO de-assertion delays)	66%					
Reset Trip outside of specification.	24%					
Supply Current is out of spec	6%					

Table 3-1. Die Failure Modes and Distribution TPS35 and TPS36

Table 3-2. Die Failure Modes and Distribution TPS3435 and TPS3436

Die Failure Modes	Failure Mode Distribution (%)
False Assert on Reset or WDO	1%
RESET or WDO remain asserted	4%
Incorrect Timing Operation (Early or late WDO faults, Reset/WDO de-assertion delays)	87%
Supply Current is out of spec	8%



4 Pin Failure Mode Analysis (Pin FMA)

This section provides a Failure Mode Analysis (FMA) for the pins of the TPS3435, TPS3436, TPS35, and TPS36. The failure modes covered in this document include the typical pin-by-pin failure scenarios:


- Pin short-circuited to Ground (see Table 4-2)
- Pin open-circuited (see Table 4-3)
- Pin short-circuited to an adjacent pin (see Table 4-4)
- Pin short-circuited to supply (see Table 4-5)

Table 4-2 through Table 4-5 also indicate how these pin conditions can affect the device as per the failure effects classification in Table 4-1.

Class	Failure Effects
A	Potential device damage that affects functionality
В	No device damage, but loss of functionality
C	No device damage, but performance degradation
D	No device damage, no impact to functionality or performance

Table 4-1. TI Classification of Failure Effects

Figure 4-1 and Figure 4-2 shows the TPS3435, TPS3436, TPS35, and TPS36 pin diagrams. For a detailed description of the device pins please refer to *TPS3435*, *TPS3436*, *TPS35*, *or TPS36* in the *Pin Configuration and Functions* section of the data sheet.



Following are the assumptions of use and the device configuration assumed for the pin FMA in this section:

- Output reset Pullup Resistor (R_{PULLUP}) = 10 kΩ, Output reset pullup voltage (V_{PULLUP} = 5.5 V, output reset load (C_{LOAD}) = 10 pF.
- Tables valid over the operating free-air temperature range of 40°C to 125°C, unless otherwise noted.
- Typical values are at $T_A = 25^{\circ}C$, VDD = 6.0 V unless stated otherwise.

PIN NAME	PIN NO.	DESCRIPTION OF POTENTIAL FAILURE EFFECT(S)	FAILURE EFFECT CLASS
SET0	1	Unexpected behavior if application needs SET0 = 1.	В
CWD	2	Capacitance value is detected after startup, or error detection. If it's shorted to ground then the WD is disabled.	В
CRST (TPS35 and TPS36)	3	t_D is the max value. Please refer to the switching characteristics table in the <i>TPS35, or TPS36</i> data sheets for more information.	В
CRST (TPS3435 and TPS3436)	3	WDO stays asserted.	В
GND	4	Expected operating condition.	D
SET1	5	Unexpected behavior if application needs SET1 = 1.	В
WDI	6	Constant WD timeout faults.	В
WDO / RESET(Open Drain)	7	WDO / RESET constantly asserted; some additional current can flow through pullup resistor.	В
WDO / RESET(Push Pull)	7	Functionality lost and can cause permanent damage.	A
VDD	8	Device non-operational.	В

Table 4-2. Pin FMA for Device Pins Short-Circuited to Ground

Table 4-3. Pin FMA for Device Pins Open-Circuited

PIN NAME	PIN NO.	DESCRIPTION OF POTENTIAL FAILURE EFFECT(S)	FAILURE EFFECT CLASS
SET0	1	Leads to large indeterminate voltage levels. This causes large currents that can damage the device. The output behavior is not deterministic.	А
CWD	2	Output is asserted.	В
CRST	3	Nothing happens until error condition, then reset delay is 2 mS.	С
GND	4	Device is non-operational.	В
SET1	5	Leads to large indeterminate voltage levels. This causes large currents that can damage the device. The output behavior is not deterministic.	A
WDI	6	Leads to large indeterminate voltage levels. This causes large currents that can damage the device.	A
WDO / RESET(Open Drain)	7	Constant high, no WDO/RESET functionality.	В
WDO / RESET(Push Pull)	7	High impedance output, no WDO/RESET functionality.	В
VDD	8	Device is non-operational.	В

Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin

PIN NAME	PIN NO.	SHORTED TO	DESCRIPTION OF POTENTIAL FAILURE EFFECT(S)	FAILURE EFFECT CLASS
SET0	1	CWD	If SET0 is pulled up with a resistor, then the device can charge CWD capacitor at an unpredictable rate that depends on pullup resistor value. If SET0 is low, then the WD is disabled.	С
CWD	2	CRST	Device stays in error condition. Output assert time can be higher than expected. If either capacitor is outside the range, then the WD can be disabled.	В
CRST (TPS35 and TPS36)	3	GND	t_D is the max value. Please refer to the switching characteristics table in the <i>TPS35, or TPS36</i> data sheets for more information.	В
CRST (TPS3435 and TPS3436)	3	GND	WDO stays asserted.	В

PIN NAME	PIN NO.	SHORTED TO	DESCRIPTION OF POTENTIAL FAILURE EFFECT(S)	FAILURE EFFECT CLASS
GND	4	SET1	Unexpected behavior if application needs SET1 = 1.	В
SET1	5	WDI	SET1 toggles with WDI.	В
WDI	6	WDO / RESET(Open Drain)	Incorrect error ouput. If WDI is being driven high, then high current can flow into an active low WDO/RESET. This causes damage if the current is higher than the abs max. Please refer to the Absolute Maximum Ratings table in the <i>TPS3435</i> , <i>TPS3436</i> , <i>TPS35</i> , or <i>TPS36</i> data sheets for more information.	A
WDI	6	WDO / RESET(Push Pull)	Incorrect error ouput. If WDI is being driven high, then high current can flow into an active low WDO/RESET. This causes damage if the current is higher than the abs max. Please refer to the Absolute Maximum Ratings table in the <i>TPS3435</i> , <i>TPS3436</i> , <i>TPS35</i> , or <i>TPS36</i> data sheets for more information.	A
WDO / RESET(Open Drain)	7	VDD	Large current can flow into WDO/RESET when in error condition. This can cause permanant damage.	A
WDO / RESET(Push Pull)	7	VDD	Can cause permanent damage.	A
VDD	8	SET0	Unexpected behavior if application needs SET0 = 0.	В

Table 4-4. Pin FMA for Device Pins Short-Circuited to Adjacent Pin (continued)

Table 4-5. Pin FMA for Device Pins Short-Circuited to VDD

PIN NAME	PIN NO.	DESCRIPTION OF POTENTIAL FAILURE EFFECT(S)	FAILURE EFFECT CLASS
SET0	1	Unexpected behavior if application needs SET0 = 0.	В
CWD	2	WDO / RESET asserts. Possibility of high current which can cause device damage.	A
CRST	3	t_D is 2 ms. Possibility of high current which can cause device damage.	A
GND	4	Device is non-operational.	В
SET1	5	Unexpected behavior if application needs SET1 = 0.	В
WDI	6	Constant WD timeout faults.	В
WDO / RESET(Open Drain)	7	Large current can flow into WDO/RESET when in error condition. This can cause permanant damage.	A
WDO / RESET(Push Pull)	7	Can cause permanent damage.	A
VDD	8	Normal operation.	D

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2023, Texas Instruments Incorporated