

Specifications

- Input Power \approx 8W
- Output Power \approx 7W
- Line Voltage = 198VAC~264VAC
- Line Frequency = 50Hz
- LED Forward Voltage = 20V
- LED Current \approx 350mA
- Efficiency \approx 84%
- Power Factor \geq 0.9
- Topology: Flyback- Transition Mode
- Solution size: 56mm(L) x 18mm(W) x 19mm(H)

Test Conditions

- Line Voltage = 220VAC/50Hz unless otherwise specified
- LED Forward Voltage \approx 20V
- LED Current \approx 350mA
- Ambient Temperature \approx 25°C

Electrical Performance

V_{IN} (VAC)	I_{IN} (A)	f_{LINE} (Hz)	P_{IN} (W)	PF	V_{OUT} (V)	I_{OUT} (A)	P_{OUT} (W)	η_{SYS} (%)
198.4	0.042	50	7.93	0.948	19.62	0.343	6.73	84.9
200.4	0.042	50	7.94	0.946	19.62	0.344	6.74	84.9
210.4	0.040	50	7.98	0.938	19.62	0.345	6.77	84.8
220.4	0.039	50	8.03	0.930	19.62	0.346	6.79	84.6
230.4	0.038	50	8.08	0.921	19.62	0.348	6.82	84.5
240.4	0.037	50	8.14	0.912	19.62	0.349	6.85	84.1
250.4	0.036	50	8.20	0.902	19.62	0.351	6.89	84.0
264.5	0.035	50	8.28	0.888	19.63	0.352	6.92	83.5




FIGURE 1. Efficiency vs. Line Voltage from 198VAC to 264VAC/50Hz




FIGURE 2. LED Current vs. Line Voltage from 198VAC to 264VAC/50Hz




FIGURE 3. Power Factor vs. Line Voltage from 198VAC to 264VAC/50Hz




FIGURE 4. Current Harmonic Performance vs. EN/IEC61000-3-2 Class C Limits at 220VAC/50Hz

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated