BILL OF MATERIALS

TI Designs#

TIDA-00168

E:u I	D	D	F		D (N)	0 " 0 110
Fitted Fitted	Description	Designator C26	Footprint 0402	Manufacturer	PartNumber	Quantity RoHS
		C30	0805	MuRata	GRM155R70J222KA01D	1 Y
	CAP, CERM, 10 μF, 10 V, +/- 10%, X7R, 0805 CAP, CERM, 1uF, 50V, +/-10%, X7R, 0603	C7	0603	MuRata	GRM21BR71A106KE51L	1 Y
Fitted		C8	0603	Taiyo Yuden	UMK107AB7105KA-T	1 Y
Fitted		D10	LED 0603	MuRata	GRM188R60J475KE19D	
Fitted	, , -	D11	LED_0603	Wurth Elektronik eiSos	150060VS75000	1 Y
	, , ,	D7	SMA	Wurth Elektronik eiSos	150060YS75000	
Fitted		D8	1.7x0.65x0.8mm	Rohm OSRAM	PTZTE253.6B LG L29K-G2J1-24-Z	1 Y 1 Y
Fitted	, ,	D9	LED_0603	Wurth Elektronik eiSos	150060SS75000	1 Y
	, , ,	H1	_		PCC-SMP-CLIP	1 Y
	Circuit Board Thermocouple Connector, Miniature Size, Type K, Horizontal installation, TH	J1	20.8x6.3x15.5 mm	Omega Omega	PCC-SMP-K-5-R	1 Y
Fitted	TERMINAL BLOCK 5.08MM VERT 2POS, TH	J3	TERM_BLK, 2pos, 5.08mm	On-Shore Technology	ED120/2DS	1 Y
Fitted	Header (shrouded), 100 mil, 7x2, Gold plated, TH	J9	7x2 Shrouded Header	Ü	SBH11-PBPC-D07-ST-BK	1 Y
Fitted		R12	0603	Yageo America	RC0603JR-07390RL	1 Y
Fitted	RES, 0 ohm, 5%, 0.063W, 0402	R13	0402	Vishay-Dale	CRCW04020000Z0ED	1 Y
Fitted	RES, 3.24k ohm, 0.1%, 0.333W, 1206	R14	1206	TT Electronics/IRC	PFC-W1206R-12-3241-B	1 Y
Fitted	RES, 47k ohm, 5%, 0.063W, 0402	R22	0402	Vishay-Dale	CRCW040247K0JNED	1 Y
Fitted	Temperature Sensor, 100ohm, TC=+3850ppm, TO-92, TH	RT1	TO-92, 2pin	Heraeus Sensor Technolog		1
Fitted	Test Point, Miniature, Red, TH	TP3	Red Miniature Testpoint	Keystone	5000	1 Y
	Test Point, Multipurpose, Grey, TH	TP6	Grey Multipurpose Testpoint		5128	1 Y
	Low-Power, Low-Noise, 24-Bit Analog-to-Digital Converter		.,, ., ., .,		0.20	
Fitted	,	U1	RVA0016A	Texas Instruments	ADS1220IRVA	1 Y
	Low Noise, Very Low Drift, Precision Voltage Reference, - 40 to 125 degC, 8-pin MSOP (DGK), Green (RoHS & no Sb/Br)	U2	DGK0008A	Texas Instruments	REF5020IDGKT	1
Fitted	Low Noise, High-Bandwidth PSRR Low-Dropout 150mA	U3	DSE0006A	Texas Instruments	TPS71733DSE	1 Y
	MSP430FR5949 16 MHz Ultra-Low-Power Microcontroller			Toxac metramente	11 67 11 600 60	
Fitted		U4	RHA0040B	Texas Instruments	MSP430FR5949IRHA	1 Y
	Remote 16-Bit I2C and SMBus, Low-Power I/O Expander with Interrupt Output and Config Register, 1.65 to 5.5 V, -40 to 85 degC, 24-pin QFN (RTW), Green (RoHS & no Sb/Br)		RTW0024B	Texas Instruments	TCA9535RTWR	1
Fitted	Crystal, Tuning Fork, 30kHz - 200kHz, SMD	Y1	6.7 x 1.40 mm	Micro Crystal AG	MS3V-T1R	1
Fitted	CAP, CERM, 1uF, 10V, +/-10%, X7R, 0603	C14, C18	0603	MuRata	GRM188R71A105KA61D	2 Y
Fitted	CAP, CERM, 10uF, 6.3V, +/-10%, X7R, 0805	C20, C21	0805	MuRata	GRM21BR70J106KE76L	2 Y
Fitted	CAP, CERM, 10pF, 50V, +/-5%, C0G/NP0, 0402	C24, C25	0402	MuRata	GRM1555C1H100JA01D	2 Y
Fitted	CAP, CERM, 0.22uF, 6.3V, +/-10%, X5R, 0402	C3, C4	0402	MuRata	GRM155R60J224KE01D	2 Y
Fitted	CAP, CERM, 0.1 µF, 100 V, +/- 10%, X7R, 1206	C31, C32	1206	AVX	12061C104KAT2A	2 Y
Fitted	CAP, CERM, 0.27uF, 6.3V, +/-10%, X5R, 0402	C5, C10	0402	MuRata	GRM155R60J274KE01D	2 Y
Fitted	Diode, Switching, 70V, 0.215A, SOT-23	D2, D3	SOT-23	Micro Commercial Compo	BAV199-TP	2 Y
Fitted	Diode, Schottky, 40V, 0.5A, SOD-123	D5, D6	SOD-123	ON Semiconductor	MBR0540T1G	2 Y
			HEADER, RECEPTACLE, 100mil,			
Fitted	Connector, Receptacle, 100mil, 10x2, Gold plated, TH	J4, J10	10x2	Samtec, Inc.	SSW-110-23-F-D	2 Y
		R1, R11	0603	Vishay-Dale	CRCW060310R0FKEA	2 Y
Fitted	RES, 100 k, 5%, 0.063 W, 0402	R15, R16	0402	Vishay-Dale	CRCW0402100KJNED	2 Y
Fitted	RES, 2.00Meg ohm, 1%, 0.063W, 0402	R2, R10	0402	Vishay-Dale	CRCW04022M00FKED	2 Y
Fitted	RES, 1.5k ohm, 5%, 0.063W, 0402	R20, R21	0402	Vishay-Dale	CRCW04021K50JNED	2 Y
		S1, S2	2.9x2x3.9mm SMD	Alps	SKRKAEE010	2 Y
	Test Point, Multipurpose, White, TH	TP1, TP2	White Multipurpose Testpoint		5012	2 Y
Fitted	Test Point, Multipurpose, Black, TH	TP4, TP5	Black Multipurpose Testpoint	Keystone	5011	2 Y
Fitted	CAP, CERM, 2.2uF, 10V, +/-10%, X7R, 0603	C13, C15, C16	0603	MuRata	GRM188R71A225KE15D	3 Y
		R17, R18, R19	0402	Vishay-Dale	CRCW0402470RJNED	3 Y
	RES, 47 ohm, 5%, 0.063W, 0402	R5, R6, R7	0402	Vishay-Dale	CRCW040247R0JNED	3 Y
	CAP, CERM, 1uF, 10V, +/-10%, X5R, 0402	C1, C2, C11, C12	0402	MuRata	GRM155R61A105KE15D	4 Y
	Diode, TVS, Uni, 13V, 600W, SMD, 2-Leads, Body	C6, C9, C28, C29	SMD, 2-Leads, Body 4x2.7mm,	TDK	C1005X7R1H104K050BB	4 Y
	· •	D1, D4, D12, D13	Height 1.1mm	NXP Semiconductor	PTVS13VP1UP_115	4 Y
Fitted	, , ,	R3, R4, R8, R9	0402	Vishay-Dale	CRCW0402499RFKED	4 Y
Fitted	CAP, CERM, 0.1uF, 10V, +/-10%, X7R, 0402	C17, C19, C22, C23, C27	0402	MuRata	GRM155R71A104KA01D	5 Y
Fitted	Header, 100mil, 3x1, Tin plated, TH	J2, J5, J6, J7, J8	Header, 3 PIN, 100mil, Tin	Sullins Connector Solution		5 Y
	, , , , , , , , , , , , , , , , , , , ,	SH-J1, SH-J2, SH-J3, SH-J4, SH-J5	Shunt	3M	969102-0000-DA	5 Y
Fitted	Fiducial mark. There is nothing to buy or mount.	FID1, FID2, FID3, FID4, FID5, FID6	Fiducial	N/A	N/A	6
		R23	0402	Vishay-Dale	CRCW04022M00FKED	0 Y

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design. TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have *not* been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.