

Filename: Pro5EF0.tmp  
 Variant: 001  
 Generated: 2/13/2017 1:58:51 PM  
 TID #: N/A



TIDA-01381 REV E1 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference
1	!PCB1	1		TIDA-01381	Any	Printed Circuit Board	
2	C1, C2, C25	3	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603
3	C3, C9, C10	3	0.1uF	C2012X7R2A104K125AA	TDK	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 0805	0805
4	C4	1	3300pF	GRM188R71E332KA01D	MuRata	CAP, CERM, 3300 pF, 25 V, +/- 10%, X7R, 0603	0603
5	C5, C7, C11, C12, C17, C18, C19, C20	8	4.7uF	C3225X7S2A475K200AE	TDK	CAP, CERM, 4.7 uF, 100 V, +/- 10%, X7S, 1210	1210
6	C6	1	0.033uF	GRM216R71E333KA01D	MuRata	CAP, CERM, 0.033 uF, 25 V, +/- 10%, X7R, 0805	0805
7	C8	1	10pF	CGA3E2C0G1H100D080AA	TDK	CAP, CERM, 10 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 1, 0603	0603
8	C13	1	2.2uF	C0805C225K4RACTU	Kemet	CAP, CERM, 2.2 uF, 16 V, +/- 10%, X7R, 0805	0805
9	C16	1	1000pF	06031C102JAT2A	AVX	CAP, CERM, 1000 pF, 100 V, +/- 5%, X7R, 0603	0603
10	C21, C22, C23	3	100pF	CGA3E2NP01H101J080AA	TDK	CAP, CERM, 100 pF, 50 V, +/- 5%, C0G/NP0, AEC-Q200 Grade 0, 0603	0603
11	C24, C26	2	0.1uF	C3216X7R2A104K160AA	TDK	CAP, CERM, 0.1 uF, 100 V, +/- 10%, X7R, 1206	1206
12	C27	1	2.2uF	GRT188R61H225KE13D	MuRata	CAP, CERM, 2.2 uF, 50 V, +/- 10%, X5R, AEC-Q200 Grade 3, 0603	0603
13	D2	1	100V	PDS3100Q-13	Diodes Inc.	Diode, Schottky, 100 V, 3 A, AEC-Q101, PowerDI5	PowerDI5
14	D5	1	100V	PMEG10030ELPX	NXP Semiconductor	Diode, Schottky, 100 V, 3 A, AEC-Q101, SOD-128	SOD-128
15	D6	1	24V	SMCJ24A	Fairchild Semiconductor	Diode, TVS, Uni, 24 V, SMC	SMC
16	H1, H3, H5, H7	4		1902C	Keystone	Standoff, Hex, 0.5"L #4-40 Nylon	Standoff
17	H2, H4, H6, H8	4		NY PMS 440 0025 PH	B&F Fastener Supply	Machine Screw, Round, #4-40 x 1/4, Nylon, Philips panhead	Screw
18	J1, J3	2		1727010	Phoenix Contact	Conn Term Block, 2POS, 3.81mm, TH	2POS Terminal Block
19	J2	1		1725698	Phoenix Contact	Terminal Block, 6x1, 2.54mm, TH	Terminal Block, 6x1, 2.54mm, TH
20	J4	1		D3082-05	Harwin	1mm Uninsulated Shorting Plug, 10.16mm spacing, TH	Shorting Plug, 10.16mm spacing, TH
21	J5	1		1725672	Phoenix Contact	Terminal Block, 4x1, 2.54 mm, Green, TH	Terminal Block, 4x1, 2.54 mm, TH
22	L1, L2	2	220 ohm	FBMH3216HM221NTV	Taiyo Yuden	Ferrite Bead, 220 ohm @ 100 MHz, 4 A, 1206	1206
23	L3	1	3.3uH	CLF7045T-3R3N	TDK	Inductor, Shielded, Ferrite, 3.3 uH, 5 A, 0.0213 ohm, SMD	Inductor, 6.2x4.5x5.9mm
24	L4	1	22uH	IHLP4040DZER220M8A	Vishay-Dale	Inductor, Shielded Drum Core, Powdered Iron, 22 uH, 4.1 A, 0.0705 ohm, AEC-Q200 Grade 0, SMD	IHLP-4040DZ
25	L5, L6	2	600 ohm	BLM31PG601SH1L	MuRata	Ferrite Bead, 600 ohm @ 100 MHz, 1.5 A, 1206	1206
26	NEG(-), POS (+)	2	Double	1502-2	Keystone	Terminal, Turret, TH, Double	Keystone1502-2
27	Q1	1	100V	STL8N10LF3	STMicroelectronics	MOSFET, N-CH, 100 V, 20 A, AEC-Q101, 8-PowerVDFN	8-PowerVDFN
28	R1	1	20.0k	CRCW060320K0FKEA	Vishay-Dale	RES, 20.0 k, 1%, 0.1 W, 0603	0603
29	R2	1	100k	CRCW0603100K0FKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603
30	R3	1	1.43k	CRCW06031K43FKEA	Vishay-Dale	RES, 1.43 k, 1%, 0.1 W, 0603	0603
31	R4	1	10.0	CRCW120610R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.25 W, 1206	1206
32	R5	1	0	CRCW06030000Z0EA	Vishay-Dale	RES, 0, 5%, 0.1 W, 0603	0603
33	R6	1	100	CRCW0603100R0FKEA	Vishay-Dale	RES, 100, 1%, 0.1 W, 0603	0603
34	R7	1	0.06	CSRN2010FK60L0	Stackpole Electronics Inc	RES, 0.06, 1%, 1 W, 2010	2010
35	R8	1	487k	CRCW0603487K0FKEA	Vishay-Dale	RES, 487 k, 1%, 0.1 W, 0603	0603
36	R9	1	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603
37	R10, R12	2	10.0	CRCW060310R0FKEA	Vishay-Dale	RES, 10.0, 1%, 0.1 W, 0603	0603
38	R11	1	0.16	MCR25JZHFLR160	Rohm	RES, 0.16, 1%, 0.5 W, 1210	1210
39	R13	1	220	CRCW0603220RJNEA	Vishay-Dale	RES, 220, 5%, 0.1 W, 0603	0603
40	RS1, RS2, RS3, RS4, RS5, RS6	6	0	ERJ-3GEY0R00V	Panasonic	RES, 0, 5%, 0.1 W, 0603	0603
41	U1	1		TPS92691QPWPQRQ1	Texas Instruments	Multi-Topology LED Driver with Rail-to-Rail Current Sense Amplifier, PWP0016J	PWP0016J
42	U2	1		TMP423AQDCNRQ1	Texas Instruments	+/- 1 C Remote and Local TEMPERATURE SENSOR, DCN0008A (SOT-8)	DCN0008A
43	C14	0	0.1uF	GRM188R71H104KA93D	MuRata	CAP, CERM, 0.1 uF, 50 V, +/- 10%, X7R, 0603	0603
44	FID1, FID2, FID3	0		N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated