


Product Bulletin – Wireless Infrastructure

TMS320TCI6482 High Performance, Low Power, Programmable DSP for Wireless Base Stations

Optimized Baseband Architecture for Base Stations

The TMS320TCI6482 (TCI6482) Digital Signal Processor (DSP) for wireless infrastructure applications provides a power-efficient platform for multi-standard, soft digital baseband solutions in wireless base stations. The TCI6482 has the latest TMS320C64x™ DSP core based on TI's advanced very long instruction word (VLIW) architecture, which can perform up

to eight 32-bit instructions during every cycle (cycle time is 1ns). On top of the 1 Gigahertz (GHz) performance of the basic architecture, the TCI6482 has added new extensions that facilitate code size reduction and the processing of complex arithmetic and bit manipulation functions across wireless standards. Among these enhancements are:



The TMS320TCI6482 DSP offers the best combination of power efficiency and high performance for soft digital baseband processing in wireless infrastructure equipment.

Key Features

- Leverages industry-leading 90nm process technology
- Leading power efficiency:
 - Approximately 3 watts or less
- 28 new instructions improve baseband performance
- Industry's first DSP with serial RapidIO™
- Unprecedented integration:
 - 3GPP/3GPP2 compliant Turbo and Viterbi co-processors
 - Four 1x serial RapidIO interfaces (12.5 Gbps maximum performance throughput)
 - 10/100/1000 Ethernet MAC, UTOPIA
- New Rake, RACH, Search and Spread Assist instruction set extension for complex correlation functions required in CDMA base standards
- High-performance memory sub-system:
 - 2 MB of L2 memory
 - DDR2 external memory interface
- A dedicated software pipelined loop buffer (SPLOOP) instruction that reduces VLIW code size and allows fully optimized code to be interrupted
- Compact 32- and 16-bit instructions that reduce code size
- New wireless infrastructure DSP instructions such as packing, sorting, bit manipulation and Galois field multiplications:
 - New Complex Multiply (CMPY) instruction to improve Chip and Symbol rate performance
- Instruction set extension for correlation functions required for CDMA base standards

TCI6482 Improves Performance in Wireless Applications

Included in the core architecture is a new feature for Rake, RACH, Search and Spread Assist (RSA) which helps applications primarily using CDMA standards. CDMA standards are among the most difficult to implement on a DSP and traditionally have been based on an ASIC or FPGA. The TCI6482, seamlessly performs complex multiply accumulate functions found in CDMA resulting in higher channel density while maintaining an all soft implementation. As a result, the TCI6482 addresses the requirements of CDMA systems more successfully than any previous DSP solution.

Twenty-eight new instructions have been added to the TCI6482 to improve performance in wireless infrastructure applications. These instructions improve performance for Symbol Rate and Chip Rate processing found in 3rd Generation (3G) wireless standards, matrix operations found in TD-SCDMA and GSM-EDGE equalizer applications, and FFT/IFFT operations found in OFDM applications such as 802.16. These instructions show as much as a 30 percent improvement over the current C64x™ core in key wireless infrastructure benchmarks. Because the TCI6482 is a member of TI's C64x DSP family, the leading architecture used in 3G wireless base station systems, OEMs can re-use their existing software code base and evolve their system architectures, resulting in a time-to-market advantage.

High Performance and Low Power for an Efficient, High-Density Platform

Operating at 1 GHz and performing up to 8000 million instructions per second (MIPS) with a 1ns


instruction cycle, the TCI6482 consumes approximately 3 Watts when operating at full speed. It is capable of 8- x 16-bit complex MACs (4 real, 4 imaginary) per cycle for a total of 8000 MMACs. These figures represent nearly twice the performance and less than half the power consumed versus other DSPs aimed at soft baseband implementations.

This outstanding performance/power consumption ratio makes it practical to use the DSP soft baseband approach out of the laboratory and in real-world applications. Equipment manufacturers can design more devices on a single board without causing thermal problems and pack more features and channels into the same cabinet. The combination enables service providers to lower their operating costs and offer additional services to their customers.

As an example, the TCI6482 can easily support three full TD-SCDMA carriers on a single channel card, leading to the lowest cost and lowest power TD-SCDMA solution.

Greater Connectivity for Board Level Efficiency

The TCI6482 wireless infrastructure processor is the industry's first DSP to feature a serial RapidIO™ interface, designed to add scalable connectivity and control among processing components in embedded systems. This high-speed, peer-to-peer interconnection fabric helps to lower system cost by providing a low pin count standard-based serial interface that eliminates the need for glue logic. Low latency and reduced overhead for packet processing improves system performance by simplifying the distribution of tasks across serial RapidIO enabled processing elements.





Serial RapidIO enables efficient BTS communication.

The Gigabit Ethernet Media Access Control (MAC) enables the TCI6482 to communicate directly with the network in order to support TCP/IP stacks, User Datagram Protocol (UDP) termination and other network control applications. The Ethernet MAC supports MII, RMII, GMII and RGMII physical interfaces, allowing a wide variety of connectivity choices.

Other interfaces that provide flexibility for wireless infrastructure includes Universal Test and Operations Interface for Asynchronous Transfer Mode (UTOPIA), Peripheral Control Interface (PCI), Host Peripheral Interface (HPI) and general purpose I/O (GPIO). An Enhanced Direct Memory Access (EDMA) controller, more advanced than any other C64x DSP, functions as a low-latency crossbar connecting all modules with seamless arbitration. It features a high-speed, 64-channel read/write transfer controller synchronized to system events.

Integrated Coprocessors

In addition, the highly integrated TCI6482 DSP provides many advanced features for greater flexibility in designing wireless system hardware and software. Included on chip is an enhanced Viterbi decoder coprocessor (VCP2) and an enhanced Turbo



TI's industry specific enablers maximize 3G wireless performance and services.

decoder coprocessor (TCP2), both of which significantly speed up channel decoding operations. The VCP2 can decode more than 763 adaptive multi-rate (AMR) voice channels at 12.2 Kbps; and the TCP2 can decode up to 44 turbo encoded 384 kbps data channels or eight 2 Mbps turbo encoded channels. The VCP2 and TCP2 are designed to support most cellular standards including GSM-EDGE, UMTS (3GPP), TD-SCDMA and CDMA2000 (3GPP2).

Generous Memory Subsystem

The TCI6482 memory sub-system has 2 MBs of on chip memory to support the high performance of the DSP core. It also has Layer1 program (L1P) and Layer1 data (L1D) scalable cache memory with sizes of 4, 8, 16 and 32 K for added flexibility. The Internal Direct Memory Access (IDMA) supports dynamic pre-loading of critical code mapped to L1 from L2, freeing the CPU from the data movement task which increases density and lower cost per channel. The TCI6482 also has memory protection to prevent rogue processes from overwriting user selected areas of memory. This feature allows for a more stable system during software development, contributes to shortened time spent in debug and helps to improve time-to-market.

Standards and Applications

With designs based on the TCI6482 DSP, wireless infrastructure equipment manufacturers can use a single hardware platform for many different applications, saving development time and costs in new designs, as well as allowing existing products to be upgraded quickly and efficiently. Among the many standards, features and applications supported by the TCI6482 DSP are:

Wireless Standards

- TD-SCDMA
- UMTS (3GPP)
- CDMA2K (EV-DO, EV-DV)
- GSM-EDGE
- 802.16

Applications

- Macro and micro base stations
- Pico and other small form factor base stations
- HSPDA
- MAC-HS
- OFDM based applications
- TCP/IP

Worldwide Support and Manufacturing

Tools and application software from TI and the industry's largest DSP third-party network provide in-depth support that helps to speed up development and reduce time-to-market. TI's Code Composer Studio™ Integrated

Benefits

- Power efficiency allows more on-board functionality and improved reliability
- Device programmability supports all wireless standards
- Software-based approach shortens development time and enables future upgrades in the field
- 1 GHz performance results in higher channel density with acceleration for key wireless routines
- Serial RapidIO simplifies system design, enables low latency and high band-width interface
- Software compatibility with legacy TMS320C6000™ software shortens development time
- TI's industry leading development tool, Code Composer Studio™, improves debug and shortens time-to-market

Development Environment (IDE), the most advanced DSP IDE available, provides proven tools and a familiar look and feel for programmers. A range of application software optimized for C6000™ family DSPs is available and rapidly increasing.

Developers in all regions can rely on TI's long-term expertise with many wireless network standards. And TI's leadership in 90nm process technology and manufacturing presence throughout the world assures quality and steady supply when it comes to a volume production.

For More Information

To learn more about the TMS320TCI6482 DSP—or other wireless solutions from TI—visit www.ti.com/wi

Find out how the TCI6482 software baseband processor can add flexibility and performance to your next wireless infrastructure design.

TI Worldwide Technical Support

Internet

TI Semiconductor Product Information Center

Home Page

support.ti.com

TI Semiconductor KnowledgeBase Home Page

support.ti.com/sc/knowledgebase

Product Information Centers

Americas

Phone +1(972) 644-5580
Fax +1(972) 927-6377
Internet/Email support.ti.com/sc/pic/americas.htm

Europe, Middle East, and Africa

Phone
Belgium (English) +32 (0) 27 45 54 32
Finland (English) +358 (0) 9 25173948
France +33 (0) 1 30 70 11 64
Germany +49 (0) 8161 80 33 11
Israel (English) 1800 949 0107
Italy 800 79 11 37
Netherlands (English) +31 (0) 546 87 95 45
Russia +7 (0) 95 7850415
Spain +34 902 35 40 28
Sweden (English) +46 (0) 8587 555 22
United Kingdom +44 (0) 1604 66 33 99
Fax +1(49) (0) 8161 80 2045
Internet support.ti.com/sc/pic/euro.htm

Japan

Fax International +81-3-3344-5317
Domestic 0120-81-0036
Internet/Email International support.ti.com/sc/pic/japan.htm
Domestic www.tij.co.jp/pic

Asia

Phone
International +886-2-23786800
Domestic Toll-Free Number
Australia 1-800-999-084
China 800-820-8682
Hong Kong 800-96-5941
Indonesia 001-803-8861-1006
Korea 080-551-2804
Malaysia 1-800-80-3973
New Zealand 0800-446-934
Philippines 1-800-765-7404
Singapore 800-886-1028
Taiwan 0800-006800
Thailand 001-800-886-0010
Fax 886-2-2378-6808
Email tiasia@ti.com
ti-china@ti.com
Internet support.ti.com/sc/pic/asia.htm

Important Notice: The products and services of Texas Instruments Incorporated and its subsidiaries described herein are sold subject to TI's standard terms and conditions of sale. Customers are advised to obtain the most current and complete information about TI products and services before placing orders. TI assumes no liability for applications assistance, customer's applications or product designs, software performance, or infringement of patents. The publication of information regarding any other company's products or services does not constitute TI's approval, warranty or endorsement thereof.

A011905

Technology for Innovators, the black/red banner, TMS320C64x, C64x, TMS320C6000, C6000, VLYNQ and Code Composer Studio are trademarks of Texas Instruments. All other trademarks are the property of their respective owners.