


Symbol	Count	Hole Size	Plated	Hole Tolerance (+)	Hole Tolerance (-)	Hole Length
⊕	1	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	137.79mil (3.500mm)
⊞	2	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	51.18mil (1.300mm)
◇	2	33.47mil (0.850mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
✕	2	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	118.11mil (3.000mm)
★	2	40.16mil (1.020mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
✕	3	43.31mil (1.100mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
□	4	118.11mil (3.000mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
○	4	160.00mil (4.064mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
⊕	7	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
⌒	10	40.00mil (1.016mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
▽	2905	8.00mil (0.203mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2942 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



DETAIL-A(V-GROOVE DETAILS)
SCALE : NTS

NOTES:

- BOARD SHALL MEET THE REQUIREMENTS OF UL-796E WITH FLAMMABILITY RATING OF MINIMUM 94V-0. UL LOGO, MANUFACTURER'S IDENTIFICATION AND DATE CODE LETTER SHALL BE RENDERED IN SILKSCREEN.
- VENDOR MAY ADJUST SOLDERMASK WHEREVER SOLDERMASK PADS ARE THE SAME SIZE (1:1) AS PER THE MANUFACTURING CAPABILITIES AND ALL OTHER SOLDER MASK PADS SHALL NOT BE MODIFIED, PROVIDED NO ADJACENT COPPER IS EXPOSED AND NO CONFLICT IS PRODUCED WITH ANY STATED "VIA TENTING/COVERING" REQUIREMENTS.
- MANUFACTURER'S IDENTIFICATION,DATECODE LETTER SHALL BE SILKSCREENED ON SOLDER SIDE OF THE BOARD.
- TRACE WIDTH SHOULD BE ACCURATELY ETCHED. MAX TOLERANCE +/- 1 MIL
- LAYER TO LAYER REGISTRATION SHALL BE WITHIN +/-2 MIL
- REFER IMPEDANCE TABLE FOR IMPEDANCE CONTROL TRACES ON LAYER 1, 3, 6 & 8.
- FOR ACCURACY OF THE ANTENNA DIMENSION, NEED TO BE MEASURE THE ANTENNA DIMENSIONS ON ONE BOARD
- ALL VIAS ARE TENTED ON BOTH SIDES UNLESS OTHERWISE SOLDER MASK OPENED IN GERBER.
- VIA HOLE OFFSET SHALL BE WITHIN 1MILS OF ITS ORIGINAL LOCATION

LAYER STACK-UP :

Layer	Name	Material	Thickness	Constant	Board Layer Stack
	Top Overlay				
	Top Solder	Solder Resist	0.80mil	1	
	Top Layer		1.60mil		
1	Dielectric 1	Isola FR408HR (DUAL PLY, 2x1067, SPREAD GLASS)	5.00mil	3.3	
2	L2_GND1		1.20mil		
	Dielectric 2	PCL370HR	5.85mil	3.9	
3	L3_SIG1		1.20mil		
	Dielectric 3	PCL370HR	10.00mil	4.25	
4	L4_PWR1		1.20mil		
	Dielectric 4	PCL370HR	5.65mil	3.9	
5	L5_PWR2		1.20mil		
	Dielectric 5	PCL370HR	10.00mil	4.25	
6	L6_SIG2		1.20mil		
	Dielectric 6	PCL370HR	5.50mil	3.9	
7	L7_GND2		1.20mil		
	Dielectric 7	PCL370HR	5.00mil	4.25	
8	Bottom Layer		1.60mil		
	Bottom Solder	Solder Resist	0.80mil	1	
	Bottom Overlay				


NOTE :

- THIS IS AN IMPEDANCE CONTROLLED BOARD.
- EXTERNAL LAYER CU THICKNESSES ARE FINISHED THICKNESS AFTER PLATING.

IMPEDANCE TABLE : 6

LAYER	TRACE WIDTH	SPACING	IMPEDANCE +/- 10%	REFERENCE LAYER
TOP	9.3 MILS	5.3 MILS	50 OHM	LAYER-2 (GND LAYER)

LAYER	TRACE WIDTH	SPACING	IMPEDANCE +/- 10%	REFERENCE LAYER
TOP	5.2 MILS	5 MILS	100 OHM	LAYER-2
L3	4.8 MILS	7.2 MIL	100 OHM	LAYER-2
L3 & L6	6 MILS	-	50 OHM	LAYER-2, LAYER 7
TOP	9.42 MILS	7 MILS	90 OHM	LAYER-2
BOTTOM	6 MILS	5 MILS	90 OHM	LAYER-7



DESIGN INFORMATION	
MIN. TRACK WIDTH:	3.9 MIL
MIN. CLEARANCE:	3.9 MIL
MIN. VIA PAD SIZE:	18 MIL
MINIMUM ANNULAR RING 0.127mm (5.0MIL) EXTERNAL	
PER IPC-D-275 CLASS 2 LEVEL C	
REGISTRATION TOLERANCES: METAL +/-	5 MIL, HOLES +/- 3 MIL
HOLE SIZE TOLERANCE (UNLESS OTHERWISE SPECIFIED): +/-	3 MIL

MATERIAL:	
<input type="checkbox"/> FR-408	<input type="checkbox"/> FR-4 High Tg <input checked="" type="checkbox"/> OTHER REFER STACK-UP
THICKNESS:	<input type="checkbox"/> 62 MIL (1.6mm) +/-10% <input checked="" type="checkbox"/> OTHER 59 MIL +/-10%
TOLERANCE:	<input checked="" type="checkbox"/> ANSI IPC-6012 TYPE 3 CLASS 2
	<input type="checkbox"/> OTHER +/-
BOW & TWIST:	<input checked="" type="checkbox"/> ANSI IPC-6012 TYPE 3 CLASS 2
	<input type="checkbox"/> OTHER +/-

DRILLING:	
REFERENCE:	<input checked="" type="checkbox"/> AS SHOWN <input checked="" type="checkbox"/> NC_DRILL FILES
PTH COPPER THICKNESS:	<input checked="" type="checkbox"/> 20-30 um <input type="checkbox"/> OTHER

BOARD FINISH:	
SILKSCREEN:	<input checked="" type="checkbox"/> TOP <input checked="" type="checkbox"/> BOTTOM
SILKSCREEN COLOR:	<input checked="" type="checkbox"/> WHITE <input type="checkbox"/> OTHER
SOLDER RESIST COLOR:	<input type="checkbox"/> GREEN <input checked="" type="checkbox"/> OTHER RED
	<input type="checkbox"/> MATTE <input checked="" type="checkbox"/> SEMI-GLOSS

SURFACE FINISH:	
<input type="checkbox"/> IMM. TIN/SILVER OR EQUIV	<input checked="" type="checkbox"/> OTHER IMM. SILVER

ARRAY/PANEL:	
<input type="checkbox"/> CUT AND TRIM PER M1 BOARD OUTLINE	<input checked="" type="checkbox"/> N.C. ROUTE <input checked="" type="checkbox"/> V. SCORE

CERTIFICATION: MATERIALS AND WORKMANSHIP FOR ALL PCBs TO MEET OR EXCEED THE REQUIREMENTS OF:	
<input checked="" type="checkbox"/> ANSI IPC-A-600F CLASS ->	<input type="checkbox"/> 1 <input checked="" type="checkbox"/> 2 <input type="checkbox"/> 3
	<input checked="" type="checkbox"/> RoHS <input type="checkbox"/> OTHER PER ORDER

ALL BOARDS MUST MEET OR EXCEED UL94-V0 REQUIREMENTS.
PCB MUST BEAR THE UL94V-0 UL REGISTERED MATERIAL ID NUMBER

ADDITIONAL REQUIREMENTS:	
MICROSECTION: <input type="checkbox"/> YES	
BARE BOARD ELEC. TEST: <input type="checkbox"/> NONE <input checked="" type="checkbox"/> REQUIRED <input type="checkbox"/> PER ORDER	
<input type="checkbox"/> XX MIL VIAS REQUIRE NON-CONDUCTIVE FILL AND PLANARIZE	
<input type="checkbox"/> XX MIL VIAS REQUIRE CONDUCTIVE FILL AND PLANARIZE	
<input type="checkbox"/> OUTER XX MIL TRACES REQUIRE 50 OHM SINGLE-ENDED IMPEDANCE	
<input type="checkbox"/> LAYER 1 & 6 (INNER LAYERS) XX MIL WIDE, XX MIL SPACE TRACES REQUIRE 100 OHM DIFFERENTIAL IMPEDANCE	



PROJECT TITLE: xWRL6432BOOST	
DESIGNED FOR: Public Release	
FILE NAME: PROC117B_PCB.PcbDoc	
ENGINEER: Mistral	LAYOUT BY: Mistral
SCALE: 1.00	ALTUM DESIGNER VERSION: 22.11.1.43

ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SUN REV: 1460 [Modified]
LAYER NAME = 07055B ^{M1 Board Outline}	TID #: N/A		
PLOT NAME = Fabrication Drawing 1	GENERATED : 20-07-2023 12:07:12	TEXAS INSTRUMENTS	

Texas Instruments (TI) and/or its licensors do not warrant the accuracy or completeness of this specification or any information contained therein. TI and/or its licensors do not warrant that this design will meet the specifications, will be suitable for your application or fit for any particular purpose, or will operate in an implementation. TI and/or its licensors do not warrant that the design is production worthy. You should completely validate and test your design implementation to confirm the system functionality for your application.

Symbol	Count	Hole Size	Plated	Hole Tolerance (+)	Hole Tolerance (-)	Hole Length
⊕	1	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	137.79mil (3.500mm)
⊞	2	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	51.18mil (1.300mm)
◇	2	33.47mil (0.850mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
✕	2	39.37mil (1.000mm)	PTH	3.94mil (0.100mm)	3.94mil (0.100mm)	118.11mil (3.000mm)
✱	2	40.16mil (1.020mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
⊗	3	43.31mil (1.100mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
□	4	118.11mil (3.000mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
○	4	160.00mil (4.064mm)	NPTH	2.00mil (0.051mm)	2.00mil (0.051mm)	-
⊕	7	23.62mil (0.600mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
⌒	10	40.00mil (1.016mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
▽	2905	8.00mil (0.203mm)	PTH	3.00mil (0.076mm)	3.00mil (0.076mm)	-
	2942 Total					

Slot definitions : Routed Path Length = Calculated from tool start centre position to tool end centre position.
Hole Length = Routed Path Length + Tool Size = Slot length as defined in the PCB layout



ALL ARTWORK VIEWED FROM TOP SIDE	BOARD #: PROC117	REV: B	SUN REV: 1460 [Modified]
LAYER NAME = ^{MI Board Outline} Drill Drawing	TID #: N/A		
PLOT NAME = Fabrication Drawing 2	GENERATED : 20-07-2023 12:07:17		TEXAS INSTRUMENTS