
Product Overview Analog Front End for 3-Lead and 5-Lead ECG

🥼 Texas Instruments



Capabilities Using One or Two AFE4960 Devices

More Information on ECG Systems Design

- TI's patient monitoring video tutorials
- Contact TI for design-in tools •
- Evolving Semiconductor Technologies for Modern Telehealth Applications White Paper
- TI Support Forums

AFE4960 Unboxing Video

- AFE4960 Hardware and Software Operation Video
- AFE4960 Signal Chain Video
- AFE4960 ECG Demo Video

Design Considerations

Upcoming design deadlines? AFE4960 is highly integrated, just add patient protection and an MCU for a functioning system. Need more than a 3-Lead ECG Pair two AFE4960 devices in parallel to realize a 5-Lead ECG (4 ECG, 2 RESP) system. AFE4960P comes with 4 LED, 4 PD PPG signal support for SpO2 measurement. Need high-fidelity signal? AFE4960 features 1+ GΩ input impedance, CMRR > 100 dB, and programmable-gain INA.

AFE Configuration	1-ECG	2-ECG	ECG and RESP	IDLE	
Power Consumption (Typical Conditions)	About 520 µW	About 820 µW	About 1.26 mW	About 27µW	

Related Devices

system?

Need SpO2?

Feature	AFE4950	AFE49I30	AFE4960	AFE4960P	ADS1294	ADS1294R	ADS1296	ADS1296R	ADS1298	ADS1298R	ADS1299
ECG Channels	1	1	2	2	4	4	6	6	8	8	8
Respiration?	-	-	Integrated	Integrated	-	Analog	-	Analog	-	Analog	-
Pace?	-	-	Integrated								
PPG?	Integrated	Integrated	-	Integrated	-	-	Ι	-	-	-	-

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2022, Texas Instruments Incorporated