

Certificate of Compliance

Certificate Number(s):

UL-US-L181974-14-
32205102-10

Report Reference:

E181974-20150223

Issue Date:

2026-03-12

Issued to:

**Texas Instruments Incorporated
12500 T I BLVD, DALLAS, TX, 75243, US**

This certificate confirms that representative samples of:

FPPT2 - Nonoptical Isolating Devices - Component

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

UL 1577, Edition 5, Issue Date 2014-04-25, Revision Date 2023-07-06

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



David Piecuch
UL Mark Certification Program Manager



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

CERTIFICATE OF COMPLIANCE

Certificate number(s): UL-US-L181974-14-32205102-10
Report reference: E181974-20150223
Issue Date: 2026-03-12

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Single protected non-optical isolators providing 3000 Vac isolation

Model(s): ISO7721FS*

Model(s): ISO1212S (16DBQ pkg), ISO1211S (8D pkg) *May be followed by any suffix.*

Single protected non-optical isolators providing 3000 Vac isolation,

Model(s): ISO6721 (8D pkg)*, ISO7021*, ISO1044*, ISO1640 (8D pkg)*, ISO1641 (8D pkg)*, ISO6720 (8D pkg)*

Single protected non-optical isolators providing 5000 Vac isolation

Model(s): ISOW1412*, ISOW7740*, ISOW7741*, ISOW7743*, ISOW7742*, ISOW7744*

Single protected non-optical isolators providing 5000 Vac isolation,

Model(s): ISO6720 (8DWV pkg)*, ISO6721 (8DWV pkg)*, ISO6731*, ISO6740*, ISO6741*, ISO6742*

Single protection non-optical isolators at 3000 Vac isolation voltage

Model(s): ISO6721R (8D Pkg), ISOS141 (16DBQ Pkg), ISOUSB111B (16DW Pkg), ISOUSB211B (28DP Pkg) *May be followed by any suffix.*

Single protection non-optical isolators at 3750 Vac / 5303 Vdc isolation voltage

Model(s): TPSI2140-Q1, TPSI2072-Q1 *May be followed by any suffix.*

Single protection non-optical isolators at 3750 Vac isolation voltage

Model(s): ISOM8710, ISOM8711 *May be followed by any suffix.*

Single protection non-optical isolators at 5000 Vac isolation voltage

Model(s): AMC0380D16DFX, AMC0300RQDWV, AMC0330RDWV, AMC0380D04DFX, AMC0380D10QDFX, AMC0300DQDWV, AMC0311SQDWV, AMC0330SDWV, AMC0311RQDWV, AMC0311DDWV, AMC0386M06DFX, AMC0381D04QDFX, AMC0303QDWV, AMC0300DDWV, AMC0330DDWV, AMC0381D06QDFX, AMC0380D10DFX, AMC0311DQDWV, AMC0306M05QDWV, AMC0302DWV, AMC0381D06DFX, AMC0386M16QDFX, AMC0386M04DFX, AMC0381D16DFX, AMC0381D10DFX, AMC0386M16DFX, AMC0306M25DWV, AMC0302DQDWV, AMC0300RDWV, AMC0386M10QDFX, AMC0311SDWV, AMC0330SQDWV, AMC0386M06QDFX, AMC0380D04QDFX, AMC0330RQDWV, AMC0303DWV, AMC0330DQDWV, AMC0381D04DFX, AMC0306M25QDWV, AMC0380D06DFX, AMC0302RDWV, AMC0302RDWV, AMC0386M04QDFX, AMC0302RQDWV, AMC0380D16QDFX, AMC0381D16QDFX, AMC1200(C)(-,Q)DWV, AMC0311RDWV, AMC1200(C)(-,Q)DUB, AMC0386M10DFX, AMC0381D10QDFX, AMC0336QDWV, AMC0380D06QDFX *May be followed by -. R Q1, RQ1 or any other suffix.*

Model(s): ISOW1044 (20-DFM PKG), ISOW1432 (20-DFM PKG), ISO6760 (16DW Pkg), ISO6761 (16DW Pkg), ISO6762 (16DW Pkg), ISO6763 (16DW Pkg), ISOW7721, ISO1640 (16DW Pkg), ISO1641 (16DW Pkg), ISO1642 (16DW Pkg), ISO1643 (16DW Pkg), ISO1644 (16DW Pkg) *May be followed by any suffix.*

Single protection non-optical isolators at 5700 Vac isolation voltage

Model(s): ISOUSB111 (16DW Pkg), ISOUSB111 (DWX pkg), ISOUSB211 (28DP Pkg) *May be followed by any suffix.*

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



CERTIFICATE OF COMPLIANCE

Certificate number(s): UL-US-L181974-14-32205102-10
Report reference: E181974-20150223
Issue Date: 2026-03-12

Single protection, non-optical isolators at 3000 Vac isolation voltage

Model(s): ISO7741FS*, ISO7310*, ISO7330*, ISO7331*, ISO7342*, ISO1211*, ISO7762 (16DBQ pkg)*, SN003021 (8D pkg)*, ISO7321*, ISO7341*, ISO7041*, ISO7742FS*, ISO7320*, ISO7763 (16DBQ pkg)*, ISO1212*, ISO7340*, ISO7760 (16DBQ pkg)*

Model(s): ISO7710 (8D pkg), ISO7763 (16DBQ pkg), ISO7761 (16DBQ pkg), ISO7760 (16DBQ pkg), ISO7730 (16DBQ pkg), SN003021 (8D pkg), ISO6721R (8D pkg), ISO7741 (16DBQ pkg), ISO1228, ISO7721FS (8D pkg), ISO7731 (16DBQ pkg), ISO7730 (16DW pkg), ISO7761 (16DBQ pkg)*, ISO7721 (8D pkg), ISO1500 (16DBQ pkg), ISO7741FS (16DBQ pkg), ISO7761 (16DW pkg), ISO7762 (16DBQ pkg), ISO7742 (16DBQ pkg), ISO7720 (8D pkg), ISO7742FS (16DBQ pkg) *May be followed by any suffix.*

Single protection, non-optical isolators at 3750 Vac isolation voltage

Model(s): ISOM8116, ISOM8610, ISOM8113, ISOM8115, ISOM8112, ISOM8110, ISOM8111, ISOM8117, ISOM8118 *May be followed by any suffix.*

Single protection, non-optical isolators at 5000 Vac isolation voltage

Model(s): ISOW7840*, ISOW7843*, ISOW7822*, ISOW7844*, ISOW7820*, ISOW7841*, ISOW7821*, ISOW7842*

Model(s): ISO7742FT, ISO7742T, ISO7741T, ISO6163, ISO1410 (16DW pkg), ISO1430 (16DW pkg), ISO1432 (16DW pkg), ISO1412 (16DW pkg), ISO1042 (8DWV pkg), ISO1450 (16DW pkg), ISO1452 (16DW pkg), ISO7741FT, ISO1042 (16DW pkg) *May be followed by any suffix.*

Single protection, non-optical isolators at 5700 Vac isolation voltage

Model(s): SN1506011*, ISO7720*, ISO7821LLS*, ISO7830*, ISO5451*, ISO7842*, ISO7820*, ISO7710*, ISO7761 (16DW pkg)*, ISO7821LL*, ISO7841*, ISO7810*, ISO5852S*, ISO7821*, ISO7721*, SN005721*, ISO7820LL*, ISO7831*, ISO5452*, ISO7840*, ISO5851*

Model(s): ISO6742 (16DWW pkg), ISO7741 (16DWW pkg), ISO7740 (16DBQ pkg), ISO7721 (16DW pkg), ISO7720 (16DW pkg), ISO7710 (16DW pkg), ISO7760 (16DW pkg), ISO7710 (8DWV pkg), ISO7762 (16DW pkg), ISO7731 (16DW pkg), ISO7720 (8DWV pkg), ISO7763 (16DW pkg), ISO7740 (16DW pkg), ISO7741E-Q1 (16DW pkg), ISO7721 (8DWV pkg), ISO7741 (16DW pkg), ISO7742 (16DW pkg) *May be followed by any suffix.*

Certificate of Compliance

Certificate Number(s):

UL-CA-L181974-24-
32205102-7

Report Reference:

E181974-20150223

Issue Date:

2026-03-12

Issued to:

Texas Instruments Incorporated
12500 T I BLVD, DALLAS, TX, 75243, US

This certificate confirms that representative samples of:

FPPT8 - Nonoptical Isolating Devices Certified for Canada - Component

See Addendum Page for Product Designation(s).

Have been evaluated by UL in accordance with the component requirements in the Standard(s) indicated on this Certificate. UL Recognized components are incomplete in certain constructional features or restricted in performance capabilities and are intended for installation in complete equipment submitted for investigation to UL LLC.

CSA Component Acceptance Service Notice No. 5A, Issue Date: 1998-01-23

Additional Information:

See UL Product iQ® at <https://iq.ulprospector.com> for additional information.

This Certificate of Compliance indicates that representative samples of the product described in the certification report have met the requirements for UL certification. It does not provide authorization to apply the UL Recognized Component Mark. Only the Authorization Page that references the Follow-Up Services Procedure for ongoing surveillance provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



David Piecuch
UL Mark Certification Program Manager



Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.

CERTIFICATE OF COMPLIANCE

Certificate number(s): UL-CA-L181974-24-32205102-7
Report reference: E181974-20150223
Issue Date: 2026-03-12

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

Single protected non-optical isolators providing 3000 Vac isolation,

Model(s): ISO6721 (8D pkg)*, ISO7021*, ISO1044*, ISO1640 (8D pkg)*, ISO1641 (8D pkg)*, ISO6720 (8D pkg)*

Single protected non-optical isolators providing 5000 Vac isolation,

Model(s): ISO6720 (8DWV pkg)*, ISO6721 (8DWV pkg)*, ISO6731*, ISO6740*, ISO6741*, ISO6742*

Single protection non-optical isolators at 3750 Vac / 5303 Vdc isolation voltage

Model(s): TPSI2140-Q1, TPSI2072-Q1 *May be followed by any suffix.*

Single protection non-optical isolators at 5000 Vac isolation voltage

Model(s): AMC0380D16DFX, AMC0300RQDWV, AMC0330RDWV, AMC0380D04DFX, AMC0380D10QDFX, AMC0300DQDWV, AMC0311SQDWV, AMC0330SDWV, AMC0311RQDWV, AMC0311DDWV, AMC0386M06DFX, AMC0381D04QDFX, AMC0303QDWV, AMC0300DDWV, AMC0330DDWV, AMC0381D06QDFX, AMC0380D10DFX, AMC0311DQDWV, AMC0306M05QDWV, AMC0302DWV, AMC0381D06DFX, AMC0386M16QDFX, AMC0386M04DFX, AMC0381D16DFX, AMC0381D10DFX, AMC0386M16DFX, AMC0306M25DWV, AMC0302DQDWV, AMC0300RDWV, AMC0386M10QDFX, AMC0311SDWV, AMC0330SQDWV, AMC0386M06QDFX, AMC0380D04QDFX, AMC0330RQDWV, AMC0303DWV, AMC0330DQDWV, AMC0381D04DFX, AMC0306M25QDWV, AMC0380D06DFX, AMC0302RDWV, AMC0336DWV, AMC0386M04QDFX, AMC0302RQDWV, AMC0380D16QDFX, AMC0381D16QDFX, AMC1200(C)(-,Q)DWV, AMC0311RDWV, AMC1200(C)(-,Q)DUB, AMC0386M10DFX, AMC0381D10QDFX, AMC0336QDWV, AMC0380D06QDFX *May be followed by -. R Q1, RQ1 or any other suffix.*

Model(s): ISO6760 (16DW Pkg) *May be followed by any suffix.*

Single protection, non-optical isolators at 3000 Vac isolation voltage

Model(s): ISO7041*

Model(s): ISO7710 (8D pkg), ISO7763 (16DBQ pkg), ISO7761 (16DBQ pkg), ISO7760 (16DBQ pkg), ISO7730 (16DBQ pkg), SN003021 (8D pkg), ISO6721R (8D pkg), ISO7741 (16DBQ pkg), ISO1228, ISO7721FS (8D pkg), ISO7731 (16DBQ pkg), ISO7761 (16DBQ pkg)*, ISO7721 (8D pkg), ISO1500 (16DBQ pkg), ISO7741FS (16DBQ pkg), ISO7762 (16DBQ pkg), ISO7742 (16DBQ pkg), ISO7720 (8D pkg), ISO7742FS (16DBQ pkg) *May be followed by any suffix.*

Single protection, non-optical isolators at 3750 Vac isolation voltage

Model(s): ISOM8116, ISOM8610, ISOM8113, ISOM8115, ISOM8112, ISOM8110, ISOM8111, ISOM8117, ISOM8118 *May be followed by any suffix.*

Single protection, non-optical isolators at 5000 Vac isolation voltage

Model(s): ISO7742FT, ISO7742T, ISO7741T, ISO6163, ISO1410 (16DW pkg), ISO1430 (16DW pkg), ISO1432 (16DW pkg), ISO1412 (16DW pkg), ISO1042 (8DWV pkg), ISO1450 (16DW pkg), ISO1452 (16DW pkg), ISO7741FT, ISO1042 (16DW pkg) *May be followed by any suffix.*

Single protection, non-optical isolators at 5700 Vac isolation voltage

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



CERTIFICATE OF COMPLIANCE

Certificate number(s): UL-CA-L181974-24-32205102-7
Report reference: E181974-20150223
Issue Date: 2026-03-12

Model(s): ISO6742 (16DWW pkg), ISO7740 (16DBQ pkg), ISO7721 (8DWV pkg) *May be followed by any suffix.*

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact UL Solutions Customer Service at <https://www.ul.com/contact-us>.



IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you fully indemnify TI and its representatives against any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#), [TI's General Quality Guidelines](#), or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products. Unless TI explicitly designates a product as custom or customer-specified, TI products are standard, catalog, general purpose devices.

TI objects to and rejects any additional or different terms you may propose.

Copyright © 2026, Texas Instruments Incorporated

Last updated 10/2025