

TUSB522P Schematic Checklist

Malik Barton

ABSTRACT

This application report for TUSB522P, a single-lane USB 3.1 GEN1 redriver and signal conditioner supporting 5 Gbps. The device allows the dual-channel capability to enable a system to maintain signal integrity on both transmit and receive data paths. This schematic checklist provides a brief explanation of each device pin and the recommended configuration of the device pin for default operation. Use this information to check the connectivity for each TUSB522P on a system schematic.

This document aids the design at the system level for general applications. This document should not be the only resource used. In addition to this list, customers are advised to use the information in the TUSB522P datasheet, TUSB522P EVM User's Guide and associated documents to gain a full understanding of device functionality. Project collateral discussed in this application report can be downloaded from the following URL: www.ti.com/lit/zip/SLLA399.

Trademarks

All trademarks are the property of their respective owners.

1 TUSB522P Schematic Checklist

Table 1. Schematic Checklist

Pin Name	Pin Number(s)	Pin Description	Recommendation
Power Pins			
VCC	1,13	3.3 V Positive Power Supply	Parallel array of one 1 μ F and two 0.1 μ F capacitors to GND.
GND	10, 21, PAD	Ground	Connected to Ground.
Configuration Pins			
EQ1	2	Tri-level configuration input pins for CH 1 Equalization.	Use 47k Ω pull-down resistor for 3 dB of gain on CH 1. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
EQ2	17	Tri-level configuration input pins for CH 2 Equalization.	Use 47k Ω pull-down resistor for 3 dB of gain on CH 2. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
DE1	16	Tri-level configuration input pins for CH 1 De-emphasis.	Use 47k Ω pull-down resistor for 0 dB of de-emphasis on CH 1 output. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
DE2	3	Tri-level configuration input pins for CH 2 De-emphasis.	Use 47k Ω pull-down resistor for 0 dB of de-emphasis on CH 2 output. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
OS1	15	Tri-level configuration input pins for CH 1 Output Swing.	Use 47k Ω pull-down resistor for 0.9 x V _{pp} on CH 1 output. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
OS2	4	Tri-level configuration input pins for CH 2 Output Swing.	Use 47k Ω pull-down resistor for 0.9 x V _{pp} on CH 1 output. Refer to Table 1 in the datasheet for additional configurations. To avoid over equalizing data start at the lowest settings and increase until desired eye is achieved.
EN_RXD	5	Active high device enable, has an internal 660-k Ω pull-down resistor.	Add a 4.7K Ω Pull up to VCC for normal operation. Resets state machine when toggled.

Table 1. Schematic Checklist (continued)

Pin Name	Pin Number(s)	Pin Description	Recommendation
USB Data Lines			
TX1P	22	Differential output for 5 Gbps positive signal on CH1	Connect to the USB3.1 RXP/N terminals from an USB3 HOST, HUB or DEVICE using 0.1uF AC coupling capacitors or connect to the TXP/N terminals from an USB3 connector using 0.1uF AC coupling capacitors. These pins allow polarity swapping.
TX1N	23		
TX2P	12	Differential output for 5 Gbps positive signal on CH2	
TX2N	11		
RX1P	9	Differential output for 5 Gbps positive signal on CH1	Connect to the USB3.1 TXP/N terminals from an USB3 HOST, HUB or DEVICE using 0.1uF AC coupling capacitors or connect to the RXP/N terminals from an USB3 connector. NO AC coupling capacitors. These pins allow polarity swapping.
RX1N	8		
RX2P	19	Differential output for 5 Gbps positive signal on CH2	
RX2N	20		
Misc. Pins			
RSV	14	Reserved	Leave no-connected.
NC	6,7,18,24	No Connection	Leave no-connected.

2 References

- [TUSB522P 3.3 V Dual-Channel USB 3.1 GEN 1 Redriver, Equalizer Datasheet](#)
- [TUSB522PEVM Users Guide](#)
- [Strengthening the USB Type-C signal chain through redrivers](#)

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2019, Texas Instruments Incorporated