



A myTI account is required to access the content links

Links to white papers and recordings will be added to this document link soon. Please visit this [link](#) for updates.

English content

| Session title | Presentation | White paper | Recording |
|---|--------------------------|--------------------------|-----------------------|
| Tips, tricks and advanced applications of linear regulators | Download | Download | Watch |
| Demystifying clearance and creepage distance for high-voltage end equipment | Download | Download | Watch |
| Introduction to the trans-inductor voltage regulator (TLVR) | Download | Download | Watch |
| Creating a primary-side regulation flyback converter using a conventional boost controller | Download | Coming soon | Watch |
| Phase-shifted full-bridge converter fundamentals | Download | Download | Watch |
| GaN-optimized transition-mode power factor correction | Download | Download | Watch |
| Comparing AC/DC power-conversion topologies for three-phase industrial systems | Download | Coming soon | Watch |

Simplified Chinese content

| Session title | Presentation | White paper |
|---|--------------------------|-------------|
| Tips, tricks and advanced applications of linear regulators | Download | Coming soon |
| Demystifying clearance and creepage distance for high-voltage end equipment | Download | Coming soon |
| Introduction to the trans-inductor voltage regulator (TLVR) | Download | Coming soon |
| Creating a primary-side regulation flyback converter using a conventional boost controller | Download | Coming soon |
| Phase-shifted full-bridge converter fundamentals | Download | Coming soon |
| GaN-optimized transition-mode power factor correction | Download | Coming soon |
| Comparing AC/DC power-conversion topologies for three-phase industrial systems | Download | Coming soon |

Japanese content

| Session title | Presentation | White paper |
|--|--------------------------|-------------|
| Tips, tricks and advanced applications of linear regulators | Download | Coming soon |
| Demystifying clearance and creepage distance for high-voltage end equipment | Download | Coming soon |
| Introduction to the trans-inductor voltage regulator (TLVR) | Download | Coming soon |
| Creating a primary-side regulation flyback converter using a conventional boost controller | Download | Coming soon |
| Phase-shifted full-bridge converter fundamentals | Download | Coming soon |
| GaN-optimized transition-mode power factor correction | Download | Coming soon |
| Comparing AC/DC power-conversion topologies for three-phase industrial systems | Download | Coming soon |

Traditional Chinese content

| Session title | Presentation | White paper |
|--|--------------------------|-------------|
| Tips, tricks and advanced applications of linear regulators | Download | Coming soon |
| Demystifying clearance and creepage distance for high-voltage end equipment | Download | Coming soon |
| Introduction to the trans-inductor voltage regulator (TLVR) | Download | Coming soon |
| Creating a primary-side regulation flyback converter using a conventional boost controller | Download | Coming soon |
| Phase-shifted full-bridge converter fundamentals | Download | Coming soon |
| GaN-optimized transition-mode power factor correction | Download | Coming soon |
| Comparing AC/DC power-conversion topologies for three-phase industrial systems | Download | Coming soon |

Korean content

| Session title | Presentation | White paper |
|--|--------------------------|-------------|
| Tips, tricks and advanced applications of linear regulators | Download | Coming soon |
| Demystifying clearance and creepage distance for high-voltage end equipment | Download | Coming soon |
| Introduction to the trans-inductor voltage regulator (TLVR) | Download | Coming soon |
| Creating a primary-side regulation flyback converter using a conventional boost controller | Download | Coming soon |
| Phase-shifted full-bridge converter fundamentals | Download | Coming soon |
| GaN-optimized transition-mode power factor correction | Download | Coming soon |
| Comparing AC/DC power-conversion topologies for three-phase industrial systems | Download | Coming soon |

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATA SHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, regulatory or other requirements.

These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to [TI's Terms of Sale](#) or other applicable terms available either on [ti.com](#) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

TI objects to and rejects any additional or different terms you may have proposed.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2024, Texas Instruments Incorporated