

PGA280 Communication via SPI™

Juergen Metzger, Laura Groskie
High-Performance Linear Products

ABSTRACT

The [PGA280](#) is a high-precision analog instrumentation amplifier that uses a serial peripheral interface (SPI) to control gain, the input multiplexer (MUX), several signal switches, the general-purpose input/output (GPIO) port, and a number of additional features. The [PGA280 product data sheet](#) provides a general description of the device register map and related functions. This application report offers additional descriptions and examples to explain how the PGA280 uses SPI communication protocols. For additional information about the PGA280, see the device data sheet (available for download at www.ti.com).

Contents

1	Introduction	1
2	Conditions	2
3	Internal Switches	5
4	Send Data to GPIO	6
5	Chip Select Mode for GPIO (ECS)	8
6	MUX Control from Register 0	11
7	General Note	12


List of Figures

1	Set Gain to 1V/V	3
2	Set Gain to 1V/V with BUF Activation	4
3	Test 3-State for SDO	5
4	GPIO Output	7
5	ECS on GPIO0	9
6	ECS on GPIO0 in Checksum Mode.....	10

1 Introduction

The PGA280 is a high-precision instrumentation amplifier with digitally-controllable gain and signal integrity test capability. This device offers low offset voltage, near-zero offset and gain drift, excellent linearity, and nearly no 1/f noise with superior common-mode and supply rejection to support high-resolution precision measurement. The 36V supply capability and wide, high-impedance input range comply with requirements for universal signal measurement. Special circuitry prevents inrush currents from MUX switching. In addition, the input switch matrix enables easy reconfiguration and system-level diagnostics—overload conditions are indicated. The configurable GPIO offers several control and communication features. The serial peripheral interface, or SPI™, can be expanded to communicate with more devices, supporting isolation with only four ISO couplers.

Figure 1 shows a plot of the SPI waveforms that set a gain of 1. The PGA280 uses the falling edge of SCLK to detect the state of SDI.



- CH4: \overline{CS}
- CH1: SCLK
- CH3: SDI

Figure 1. Set Gain to 1V/V


Gain is set to 1/8V/V (attenuation) after device reset. Changing the gain potentially overloads the input amplifier with a fast dynamic signal, especially with low gains and large signals. Therefore, it may be beneficial to activate the buffer (BUF) for approximately 36µs.

Changing the Gain to 1V/V with BUF

L 63 09 00 40 18 H ;

BUFTIM is set to approximately 36µs (0x09) together with the activation of BUF and the gain of 1V/V is set. The BUFTIM timeout (that is, the 36µs) starts **after** \overline{CS} asserts H

Figure 2 shows how the `0x6309` instruction sets BUFTIM3 and BUFTIM0, and activates the BUF with the falling edge of the 16th clock pulse. Eight clock pulses follow as a dummy checksum byte. The `0x4018` writes to Register 0 and sets a gain of 1V/V.



- CH4: \overline{CS}
- CH1: SCLK
- CH2: BUFA
- CH3: SDI

Figure 2. Set Gain to 1V/V with BUF Activation

The BUFA signal returns to low after \overline{CS} is asserted high, followed by the timeout of approximately 36µs.

Activate BUFA_{OUT} to GPIO5

Figure 2 shows BUFA connected to GPIO5 in order to visualize the buffer timing. During design and timing evaluation, it is helpful to observe the buffer active timing cycle. In addition, this output could be used to trigger the analog-to-digital conversion.

- L 48 7F H ; Configure all GPIOs to output, or alternatively, use L 48 20 H
 L 4C 20 H ; Activate BUFA_{OUT} to GPIO5; the buffer is active H by default

The *BUFA Timing* figure in the data sheet (Figure 55) and Figure 2 make use of this configuration. The bit BUFA Pol in Register 10 allows an inversion of the buffer active signal at GPIO5.


Read Register 3 (Test Read Operation)

Register 3 is set to `0x19` after a device reset. This command reads this value.

- L 83 00 H ; Send a read command to Register 3 and add eight extra cycles of SCLK

During these additional eight cycles of SCLK, the SDO pin sends `0x19` (it exits the 3-state mode during a sending data operation, and thereafter SDO returns to a 3-state condition). It would also send the CHKsum bit if 16 SCLK cycles are provided. Terminate the SDO to high or low, according to the specific system requirements.

As Figure 3 shows, SDO leaves the 3-state mode after the read command is decoded, and sends data during the following clock cycles. For a simple demonstration in this graph, SDO was terminated to the mid-supply of DVDD (3.3V) with 750Ω. Therefore, while in 3-state mode, the scope trace shows this mid-supply voltage. Asserting CS high terminates the transmission and sets SDO to 3-state mode again.



- CH4: CS
- CH1: SCLK
- CH2: BUFA
- CH3: SDO

Figure 3. Test 3-State for SDO

SDO would transmit the checksum with eight additional clock pulses and then go to a 3-state mode automatically, even if CS is held low.

In general, SPI reads are very sensitive to data skew. The master detects the received data with its own clock. The slave device, however, may receive this clock as delayed, and as a result its data output (the SDO of the PGA280, also called *Slave Out Master In*, or *SOMI*) may even be delayed further. The reasons for this delay are logic gates or buffers and long wires. Isolation couplers, in particular, add a significant delay or data skew. Such delays or skew are often the reason for unstable communications; therefore, test the data patterns with a scope.

3 Internal Switches

The internal switches of the PGA280 are shown in the *Input Switch Diagram* (Figure 44) in the [data sheet](#). After a device reset occurs, switches A1 and A2 (SW-A1 and SW-A2, respectively) are closed, routing the input signal from INP1 and INN1 to the amplifier input.

For using Channel 2, INP2 and INN2, send this instruction:

L 66 18 H ;

This command activates the BUF stage and connects INP2 and INN2 to the amplifier.

The fast switching from one input signal to the other would potentially generate a fast transient and dynamically overload the amplifier, but with the BUF already activated, the input clamp cannot draw current. Therefore, the input remains high impedance while the amplifier settles to the new value. The BUF turns off after a timeout according to register 3 (the default setting is approximately 100µs). This time can be reduced to approximately 39µs (that 4µs × 9 + delay) by writing:

```
L 43 09 H
```

4 Send Data to GPIO

The GPIO port can be initialized for either input or output for each individual port pin. After a device reset, all pins are configured as inputs. Reading Register 5 returns the momentary state at the pin. Open, unconnected pins return unpredictable information; therefore, terminate the device pins with resistors.

For output data to the pins, they must be assigned as *outputs*.

Each GPIO pin can be assigned as an output or input individually.

```
L 45 03 H ;
```

Load Register 5 (data) with 0x03

```
L 48 7E H ;
```

GPIO pins are set to output; only GPIO0 is an input. GPIO1 is set to H. GPIO0 ignores the Register 5 setting because it is configured as an input.

```
L 85 00 H ;
```

Read Register 5. SDO returns a byte with bit B1 = H and B0 indicating the state of the GPIO0 pin (external termination to H or L required).

When Register 5 is set before the GPIO direction is assigned, the state changes directly with assigning the role of *output* according to the contents of Register 5. Once configured as an output, data can be changed in Register 5 as required.

NOTE: GPIO pins are configured as *input* after a device reset; therefore, terminate all unused inputs or configure them as *output*.

WARNING


If GPIO outputs drive into a short, the current could be high enough to lower the digital supply voltage and consequently, disrupt communication; a locked condition may occur. Therefore, use resistors for termination.

GPIO pins can be toggled while \overline{CS} low, but in this case the duration of the state directly depends on the SPI speed. The GPIO pin changes state directly with decoding of the command.

Figure 4 shows the sequence:

```
L 45 20 00 45 10 H ;
```

This sequence toggles the GPIO pins as indicated.



- CH4: \overline{CS}
- CH1: SCLK
- CH2: GPIO5
- CH3: GPIO4

Figure 4. GPIO Output

Read Error Status Register

The Error Status Register contains the individual flags being stored. Read Register 4 to detect the error flags. The bit B3, EF always turns on with any of the error flags. This bit is the OR combination of the individual errors and can be routed to GPIO3.

```
L 84 00 H ;
```

Read Register 4. SDO returns the contents of register 4.

Clear Error Flags in Error Status Register

After device power-on, depending on the power sequence and the state of the inputs, several error flags may be set. Therefore, clear this register after power-on occurs. After a readout of the register, it may be cleared. Furthermore, after setting up a new channel or gain, it may be useful to clear any existing errors.

```
L 44 FF H ;
```

Clear all error flags.

Individual error bits can be cleared by writing a '1' to the respective bit. Example:

```
L 44 04 H ;
```

Clear OUTerr (only)

Connect the OR Combination of the Error Flags to the GPIO3 Pin

GPIO3 can be assigned to the EF bit in Register 4 that allows a hardware indication of an error.

```

L 45 00 H ;           Sets all GPIOs to L state
L 44 FF H ;           Clear all error flags in Register 4
L 48 7F H ;           Assign all GPIOs to be outputs; all GPIO pins are low
L 4C 08 H ;           Assign GPIO3 to special function status, connecting the port pin to
                       EFout in Register C
  
```

Now, GPIO3 would assert high as soon as an error appears. It remains high until the error is cleared in the Error Status Register (Register 4).

The latch condition for the errors can be disabled by writing:

```
L 4B 90 H (set LTD: Register 11, bit B7); see Testing the Signal Path with a Scope Using the Error Flag (EFout) Output.
```

With the latch disabled, the error duration can be observed at GPIO3 with a scope. The datasheet shows several examples: dynamic overload and signal overload.

Testing the Signal Path with a Scope Using the Error Flag (EFout) Output

```

L 48 7F H ;           Sets all GPIOs to output
L 4C 08 H ;           Activates EFout for GPIO3
L 4B 90 H ;           Sets LTD; error flags are not stored
L 44 FF H ;           Clears all error flags
  
```

Alternatively, use the combined string:

```
L 48 7F 00 4C 08 00 4B 90 00 44 FF 00 H
```

After this setup the error flag is only active while the error is present. This condition is indicated with the state of GPIO3 and can be observed with a scope.

In addition, Register 10 allows special settings. For example, writing $0x08$ disables the error suppression while BUF is active; therefore, error conditions during a BUF active period can be observed.

A selection of errors can also be OR-combined to EF by using Register 10. Write a '1' to all errors that are to be suppressed.

5 Chip Select Mode for GPIO (\overline{ECS})

The GPIO port can be used to generate \overline{CS} for external devices. This \overline{ECS} (that is, extended \overline{CS}) allows communication to additional devices by only using one SPI bus. The port activates the \overline{ECS} after a one-byte command, and then ignores further communication until the \overline{CS} to the PGA28 returns high.

To initialize \overline{ECS} :

```

L 45 FF H ;           Set GPIO output data to H to avoid any glitches before  $\overline{ECS}$  is
                       assigned
L 48 7F H ;           Configure all GPIOs as outputs. Alternatively, configure only GPIO0
                       and GPIO1; send:
                       L 48 03 H
L 49 03 H ;           Configure ECS0 and ECS1 as enabled in Register 9
  
```

Activate \overline{ECS} (\overline{ECS} is cleared when \overline{CS} asserts H):

```
L C0 00 H ;           0xC0 activates  $\overline{ECS}$  to GPIO0
```



Activate:

```
L C0 5B 00 H ;
```

0xC0 activates $\overline{\text{ECS}}$ for GPIO0

Just one byte (0x00) is sent for demonstration purposes; it can be many bytes (that is, there are no physical restrictions, only practical constraints).

With CHKsum activated, the command for $\overline{\text{ECS}}$ is extended by the checksum byte, as Figure 6 shows. Therefore, ECS asserts low after the checksum is proven correct.



- CH1: SCLK
- CH2: SDO (not used)
- CH4: $\overline{\text{CS}}$ to PGA280
- CH3: $\overline{\text{ECS}}$ on GPIO0

Figure 6. ECS on GPIO0 in Checksum Mode

Checksum Incorrect or Missing

```
L 4B 01 H ;
```

Checksum is missing in this command

```
L 8B 26 00 00 ;
```

The reply from Register 11 is 0x0026xx.

The device has not entered checksum mode, because a proper CHKsum was missing. However, the register is set to 00, and thus FLAGTIM is set to 0x00. Note also that the last byte xx represents the state of SDO in 3-state mode; in non-checksum mode, the checksum byte of the command is ignored, and SDO starts sending data and default checksum with the 16 clock pulses after the command byte.

Write and Read Register 0 with CHKsum

```
L 40 18 F3 H ;
```

Set the gain to be 1V/V; therefore, write 0x18 to Register 0

```
L 80 1B H ;
```

Read Register 0:

```
0x1833 ;
```

18 was stored for gain 1 (0x33 is checksum)

Exit Checksum Mode

Setting bit B0 = 0 in Register 11 (CHKsumE) returns the SPI communication to non-checksum mode without changing or resetting the other register contents.

```
L 8B 26 H ;           Read Register 11 contents, AND content with 0xFE (assumes a result
                        of 0x10, or default content).
L 4B 10 F6 H ;       Sends data to Register 11; Bit B0 = 0 = CHKsumE. From this point
                        forward, checksum is no longer needed in communication.
```

6 MUX Control from Register 0

Register 0 is used to set the gain for the PGA280. But the last three bits also allow channel control for an external multiplexer. Therefore, writing to this one byte can switch the MUX channel and set the corresponding gain.

Multiplexed data acquisition must account for the fast signal transients that result from switching between channels. The PGA280 allows activation of the BUF with the command byte, and so the switching transient does not dynamically overload the amplifier nor reflect a current pulse into the signal source and signal filter.

These GPIO pins for MUX addressing change state according to the MUX2 to MUX0 bits *after* \overline{CS} is asserted high. This combination, with the positive edge of \overline{CS} , ensures that the BUF can be active well before the transient appears, especially with fast SCLK rates. The BUFTIM setting also starts with \overline{CS} high, and therefore its timeout covers the changes of the multiplexed signal until settled. The buffer timeout is set in Register 3.

Activate MUX Control from Bits B1 and B0 of Register 0 (CHKsum Not Active)

```
L 48 FF 00 4C 07 H ;   Set up GPIOs to all output mode and enable MUX0, MUX1, and
                        MUX3
```

Set Gain and MUX Channel and Activate BUF

Example for MUX Channel 3 and gain 1V/V:

```
L 60 1B 00 64 FF 00 80 00 H Set the gain to be 1V/V, activate BUF, and set MUX0 and MUX1
;                               (MUX address 0x03)
;                               Clear all error flags.
;                               Read back Register 0
```

This is a typical command structure when scanning channels.

6.1 External BUF Control by GPIO4

The buffer (BUF) can be externally controlled using BUFTin. The BUF remains active with the external signal being high and times out after the external signal goes low. Using external BUF control requires a proper timing reference to switching transients. It may be used in systems that are controlled from microprocessors, where the BUFTIM delay setting is not sufficient because of unpredictable timing. It was originally intended for test purposes.

```
L 48 6F 00 4C 30 H ;   Sets all GPIOs to output except GPIO4, which is set to input. Register
                        12 activates BUFAout and BUFTin
```

This mnemonic activates BUFAout on GPIO5 and GPIO4 becomes the input-controlling BUF.

NOTE: Avoid overshoot of the control signal to achieve minimal distortion (that is, use series termination). The BUF active time can be tested at GPIO5 (BUFAout).

7 General Note

The PGA280 is a high-precision analog amplifier. The serial peripheral interface is a minimal communication bus to communicate to the register-controlled functions. It is recommended to avoid communication during a precise measurement in order to avoid coupled noise. The impact of such noise is difficult to predict, because it depends on layout, wave shape, and currents. Avoid large current loads to the GPIO and to the SDO.

The serial interface, in general, is sensitive to both data skew and delays; therefore, test signals for proper timing with a scope. Use the scope plots in this application report and in the product data sheet for reference.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009, Texas Instruments Incorporated