

LVDS: The ribbon cable connection

By E.D. Cole, P.E.

Application Engineer, Data Transmission

Introduction

As LVDS gains popularity, multi-channel applications are becoming common. In systems where cables are used to connect drivers to receivers, CAT5-type cable, usually containing unshielded twisted pairs (UTPs), has worked well. Now that 8-channel and 16-channel LVDS drivers and LVDS receivers are available in single packages, ribbon cable is being used successfully in these "wide-bus" applications. It has become much easier to implement 16-, 32-, or 64-channel-wide LVDS systems. But what happens to the performance? The most common cable used in LVDS applications is 4-pair CAT5 cable. When 16 or 32 twisted pairs are needed, can ribbon cable be used?

Test set-up

A customer requested our assistance to determine the feasibility of using ribbon cable for a 16-channel-wide point-to-point LVDS system. The customer, using a single LVDS387 driver connected to a single LVDS386 receiver,

requested jitter and crosstalk data at 50 Mbps and 100 Mbps using 0.5-m and 3-m lengths of twisted ribbon cable.


For these tests, a generic evaluation module (EVM) was developed (one PWB that can be used for the LVDS387 or LVDS386). BergSticks™ were used for the signal I/O and ribbon cable connections. Amphenol Cable Type 843-132-2801-064 twisted ribbon cable was used. Figure 1 shows the bench test set-up with the EVMs connected using a 3-m length of ribbon cable. The inputs to the LVDS387 driver were provided by a Tektronix HFS-9009 Pattern Generator Mainframe configured with four HFS 9DG1 plug-ins cards.

For these measurements, all 16 channels were supplied with NRZ data. The pattern generator was set up with 16 channels supplying pseudo-random binary data to the '387 driver.

The programmable delays between source channels in the pattern generator were set to zero, so all channels would be switching at the same time.

Continued on next page

Figure 1. Bench test set-up



Continued from previous page

Test results

Jitter was measured on the eye pattern at four points along the transmission path:

- Point 1. Output of the receiver
- Point 2. Input to the receiver
- Point 3. Output of the driver
- Point 4. Input to the driver

By collecting the jitter values at these four points, jitter added by each component could quickly be determined. For example, the jitter added by the receiver is simply the jitter measured at Point 2 minus the jitter measured

at Point 1. Jitter added by the ribbon cable is Point 3 minus Point 2, and so on. Data was collected and loaded into a spreadsheet, and the jitter contribution was plotted for each of the four tests that were run (see Figures 2, 3, 4, and 5).

During the first test, the output jitter from Channel C2 was much higher than from any other channel. Similar problems were also observed on Channel C4. The problem was determined to be a short circuit between input pins on the driver EVM. This was caused by the author's soldering ability.

Data for Channels C2 and C4 were not collected for the remaining tests.

Figure 2. Jitter contributions using 0.5-m ribbon cable at 50 Mbps





Figure 3. Jitter contributions using 3-m ribbon cable at 50 Mbps



Conclusion

The results show that short lengths of ribbon cable can be used successfully for interconnecting LVDS drivers and receivers. They suggest, however, that the length be kept short, as the increase in cable-generated crosstalk increased significantly between 0.5-m and 3-m lengths tested at 100 Mbps. It should also be noted that there is no significant increase associated with channels running in the middle of the ribbon cable compared to the channels along the edge of the cable.

Related Web sites

www.ti.com/sc/docs/products/msp/intrface/index.htm

www.ti.com/sc/docs/tools/analog/interfacedevelopmentboards.html

Get product data sheets at:

www.ti.com/sc/docs/products/analog/device.html

Replace *device* with sn65lvds386 or sn65lvds387

Figure 4. Jitter contributions using 0.5-m ribbon cable at 100 Mbps





Figure 5. Jitter contributions using 3-m ribbon cable at 100 Mbps



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DSP	dsp.ti.com
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital control	www.ti.com/digitalcontrol
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

TI Worldwide Technical Support

Internet

TI Semiconductor Product Information Center Home Page
support.ti.com

TI Semiconductor KnowledgeBase Home Page
support.ti.com/sc/knowledgebase

Product Information Centers

Americas

Phone	+1(972) 644-5580	Fax	+1(972) 927-6377
Internet/Email	support.ti.com/sc/pic/americas.htm		

Europe, Middle East, and Africa

Phone			
Belgium (English)	+32 (0) 27 45 54 32	Netherlands (English)	+31 (0) 546 87 95 45
Finland (English)	+358 (0) 9 25173948	Russia	+7 (0) 95 7850415
France	+33 (0) 1 30 70 11 64	Spain	+34 902 35 40 28
Germany	+49 (0) 8161 80 33 11	Sweden (English)	+46 (0) 8587 555 22
Israel (English)	1800 949 0107	United Kingdom	+44 (0) 1604 66 33 99
Italy	800 79 11 37		
Fax	+(49) (0) 8161 80 2045		
Internet	support.ti.com/sc/pic/euro.htm		

Japan

Fax			
International	+81-3-3344-5317	Domestic	0120-81-0036
Internet/Email			
International	support.ti.com/sc/pic/japan.htm		
Domestic	www.tij.co.jp/pic		

Asia

Phone			
International	+886-2-23786800		
Domestic	Toll-Free Number		
Australia	1-800-999-084	New Zealand	0800-446-934
China	800-820-8682	Philippines	1-800-765-7404
Hong Kong	800-96-5941	Singapore	800-886-1028
Indonesia	001-803-8861-1006	Taiwan	0800-006800
Korea	080-551-2804	Thailand	001-800-886-0010
Malaysia	1-800-80-3973		
Fax	886-2-2378-6808	Email	tiasia@ti.com
Internet	support.ti.com/sc/pic/asia.htm		ti-china@ti.com

C011905

Safe Harbor Statement: This publication may contain forward-looking statements that involve a number of risks and uncertainties. These "forward-looking statements" are intended to qualify for the safe harbor from liability established by the Private Securities Litigation Reform Act of 1995. These forward-looking statements generally can be identified by phrases such as "TI or its management believes," "expects," "anticipates," "foresees," "forecasts," "estimates" or other words or phrases of similar import. Similarly, such statements herein that describe the company's products, business strategy, outlook, objectives, plans, intentions or goals also are forward-looking statements. All such forward-looking statements are subject to certain risks and uncertainties that could cause actual results to differ materially from those in forward-looking statements. Please refer to TI's most recent Form 10-K for more information on the risks and uncertainties that could materially affect future results of operations. We disclaim any intention or obligation to update any forward-looking statements as a result of developments occurring after the date of this publication.

Trademarks: BergSticks is a trademark of Berg Electronics. All other trademarks are the property of their respective owners.

Mailing Address: Texas Instruments
Post Office Box 655303
Dallas, Texas 75265

© 2005 Texas Instruments Incorporated