


Enable or Disable a Digital Signal



See more about this use case in the *Logic Minute* video [Enable or Disable a Digital Signal](#).

Design Considerations

- Refer to the table below to select the right function to meet system requirements
- Select the right family based on device parameters desired (for example, low power, strong drive, and high speed)
- [\[FAQ\] What is the default output of a latched device? \(Flip-Flop, latch, register\)](#)
- [\[FAQ\] What's the difference between logic output types \(push-pull, open-drain, 3-state\)?](#)
- [\[FAQ\] How do I size pull-up or pull-down resistors?](#)
- [\[FAQ\] What is a floating input or floating node?](#)
- Ask a question on our [Engineer-to-Engineer forum](#)

Recommended Parts

Part Number	AEC-Q100	Input Type	Behavior When Disabled	Features
SN74LVC1G08		Enable	LOW	<ul style="list-style-type: none"> • Wide operating supply range (1.65 V – 5.5 V) • High drive strength (32 mA) • Over-voltage tolerant inputs • Back-drive protection
SN74LVC1G08-Q1	✓	Enable	LOW	
SN74LVC1G32		Disable	HIGH	
SN74LVC1G32-Q1	✓	Disable	HIGH	
SN74LVC1G126		Enable	3-state	
SN74LVC1G126-Q1	✓	Enable	3-state	
SN74LVC1G373		Enable	Last known state	

For more devices, browse through the [online parametric tool](#) where you can sort by desired voltage, channel numbers, and other features.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated