

Compatibility Considerations: Migrating From TMS570LS31x/21x or TMS570LS12x/11x to TMS570LS0914/0714 Safety Microcontrollers

David Livingston

ABSTRACT

This application report provides a summary of the differences between the TMS570LS0914/0714 versus the TMS570LS31x/21x and TMS570LS12x/11x series of microcontrollers.

Contents

1	Introduction	2
2	Memory Configuration Differences	2
3	Package Compatibility Considerations	2
4	Input/Output Considerations	6
5	Module Compatibility Considerations	6
6	References	7

List of Tables

1	Memory Configuration Differences	2
2	Functional Pin Compatibility Mapping	3
3	Low-EMI Differences Between LS0914/0714 vs LS31x/21x and LS12x/11x	6

1 Introduction

The LS0914/0714 series incorporates a subset of the functionality incorporated on the LS31x/21x and LS12x/11x series. There are some enhancements implemented on the LS0914/0714 similar to the enhancements implemented on the TMS570LS12x/11x series vs the overall superset LS31x/21x series, while still maintaining application code compatibility to the overall superset series when the code is targeted to the subset functionality. An application written for the LS31x/21x or LS12x/11x series runs correctly on the LS0914/0714 series as long as only the common functions and features are exercised.

A product overview can be found in the [Hercules Product Brochure](#) that outlines content differences between all three series of devices.

2 Memory Configuration Differences

The memory configurations of each of the three series of microcontrollers are different. In each series, the memories are sized according to the targeted applications. [Table 1](#) shows the primary memory spaces within each series of microcontrollers in order to highlight the differences.

Table 1. Memory Configuration Differences

Memory Type	TMS570LS31x/21x	TMS570LS12x/11x	TMS570LS0914/0714
Flash: Program Memory	3MB/2MB	1.25MB/1MB	1MB/768MB
Flash: Boot Sector	1 X 32kB Sector	Up to 2 X 16kB Sectors	Up to 2 X 16kB Sectors
Flash: EEPROM Emulation	4 X 16kB Sectors	4 X 16kB Sectors	16 X 4kB Sectors
CPU Data RAM	Up to 256kB	Up to 192kB	Up to 128kB
MibADC1 RAM	64 Result Buffers	64 Result Buffers	64 Result Buffers
MibADC2 RAM	64 Result Buffers	64 Result Buffers	64 Result Buffers
N2HET1 RAM	160 Instruction RAM	160 Instruction RAM	160 Instruction RAM
N2HET RAM	160 Instruction RAM	160 Instruction RAM	160 Instruction RAM
DCAN1 RAM	64 Mailboxes	64 Mailboxes	64 Mailboxes
DCAN2 RAM	64 Mailboxes	64 Mailboxes	64 Mailboxes
DCAN3 RAM	64 Mailboxes	64 Mailboxes	64 Mailboxes
MibSPI1 RAM	128 Words	128 Words	128 Words
MibSPI3 RAM	128 Words	128 Words	128 Words
MibSPI5 RAM	128 Words	128 Words	128 Words
FlexRay RAM	8kB Message RAM	8kB Message RAM	N/A

3 Package Compatibility Considerations

Both the LS31x/21x and LS12x/11x series of microcontrollers are supported in either a 337 ball grid array (337 BGA) or a 144-pin quad flat pack (144 QFP) package. The LS0914/0714 series of devices is available in pin compatible versions of the previously listed packages as well as the 100-pin quad flat pack (100 QFP) package compatible with the LS04x/03x series of devices.

3.1 Pin-Out Compatibility

Table 2 demonstrates how the default functional pins of the 100QFP package for the LS0914/0714 series map to the subset of default functional pins of the 144QFP on the LS31x/21x and LS12x/11x series of microcontrollers.

Table 2. Functional Pin Compatibility Mapping

LS0914/0714 100PZ		LS31x/21x and LS12x/11x 144PGE		Comments
Pin Number	Pin Name/Function	Pin Number	Pin Name/Function	
1	GIOA[0]/INT[0]	2	GIOA[0]/INT[0]	
2	GIOA[1]/INT[1]	5	GIOA[1]/INT[1]	
3	FLTP1	7	FLTP1	
4	FLTP2	8	FLTP2	
5	GIOA[2]/INT[2]	9	GIOA[2]/INT[2]	
6	VCCIO	10	VCCIO	
7	VSS	11	VSS	
8	GIOA[3]/INT[3]	12	CAN3TX	GIOA[3:4]/INT[3:4] are not available in the 144PGE package of the superset devices. CAN3TX and CAN3RX used in GIO mode will allow functional compatibility.
9	GIOA[4]/INT[4]	13	CAN3RX	
10	GIOA[5]/INT[5]	14	GIOA[5]/INT[5]	
11	N2HET[22]	15	N2HET[22]	
12	GIOA[6]/INT[6]	16	GIOA[6]/INT[6]	
13	VCC	17	VCC	
14	OSCIN	18	OSCIN	
15	KELVIN_GND	19	KELVIN_GND	
16	OSCOUT	20	OSCOUT	
17	VSS	21	VSS	
18	GIOA[7]/INT[7]	22	GIOA[7]/INT[7]	
19	N2HET[0]	25	N2HET[0]	
20	VSS	27	VSS	
21	VCC	29	VCC	
22	N2HET[2]	30	N2HET[2]	
23	SPI2nCS[0]	32	MibSPI5nCS[0]	SPI2 is not available in the 144 PGE package for the superset devices. With an offset change and configuration of the MibSPI5 module in compatibility mode, pin functional compatibility can be realized.
24	TEST	34	TEST	
25	N2HET[4]	36	N2HET[4]	
26	N2HET[6]	38	N2HET[6]	
27	MibSPI1nCS[2]	40	MibSPI1nCS[2]	
28	VCCIO	42	VCCIO	
29	VSS	44	VSS	
30	VCC	45	VCC	
31	nPORRST	46	nPORRST	
32	VCC	49	VCC	
33	VSS	50	VSS	

Table 2. Functional Pin Compatibility Mapping (continued)

LS0914/0714 100PZ		LS31x/21x and LS12x/11x 144PGE		Comments
Pin Number	Pin Name/Function	Pin Number	Pin Name/Function	
34	MibSPI3SOMI	51	MibSPI3SOMI	
35	MibSPI3SIMO	52	MibSPI3SIMO	
36	MibSPI3CLK	53	MibSPI3CLK	
37	MibSPI3nENA	54	MibSPI3nENA	
38	MibSPI3nCS[0]	55	MibSPI3nCS[0]	
39	MibSPI1nCS[3]	3	MibSPI1nCS[3]	
40	ADIN[16]	58	ADIN[16]	
41	ADIN[17]	59	ADIN[17]	
42	ADIN[0]	60	ADIN[0]	
43	ADIN[7]	61	ADIN[7]	
44	ADIN[20]	64	ADIN[20]	
45	ADIN[21]	65	ADIN[21]	
46	VCCAD/ADREFHI	66	ADREFHI	VCCAD and REFHI are combined on the subset package. REFHI limited to a range of 3-3.6V
		69	VCCAD	
47	VSSAD/ADREFLO	67	ADREFHI	VSSAD and REFLO are combined on the subset package. REFLO limited to GND.
		68	VSS	
48	ADIN[9]	70	ADIN[9]	
49	ADIN[1]	71	ADIN[1]	
50	ADIN[10]	72	ADIN[10]	
51	ADIN[2]	73	ADIN[2]	
52	ADIN[3]	74	ADIN[3]	
53	ADIN[11]	75	ADIN[11]	
54	ADIN[4]	76	ADIN[4]	
55	ADIN[5]	78	ADIN[5]	
56	ADIN[6]	80	ADIN[6]	
57	ADIN[8]	83	ADIN[8]	
58	ADEVT	86	ADEVT	
59	VSS	-	-	This subset pin has no direct matching pin in the 144QFE but can be connected directly to the common ground for the MCU
60	VCCIO	-	-	This subset pin has no direct matching pin in the 144QFE but can be connected directly to the common 3.3 V rail for the MCU.
61	VCC	87	VCC	
62	CAN1TX	89	CAN1TX	
63	CAN1RX	90	CAN1RX	
64	N2HET[24]	91	N2HET[24]	
65	MibSPI1SIMO	93	MibSPI1SIMO	
66	MibSPI1SOMI	94	MibSPI1SOMI	
67	MibSPI1CLK	95	MibSPI1CLK	
68	MibSPI1nENA	96	MibSPI1nENA	

Table 2. Functional Pin Compatibility Mapping (continued)

LS0914/0714 100PZ		LS31x/21x and LS12x/11x 144PGE		Comments
Pin Number	Pin Name/Function	Pin Number	Pin Name/Function	
69	SPI2SOMI	98	MibSPI5SOMI	There is no SPI2 or MibSPI2 available in the 144QFP superset package; therefore, the subset pins map to the MibSPI5 functionally equivalent pins. The SPI2 module on the subset device is limited to non-buffered 4-pin mode only.
70	SPI2SIMO	99	MibSPI5SIMO	
71	SPI2CLK	100	MibSPI5CLK	
72	VSS	102	VSS	
73	MibSPI1nCS[0]	105	MibSPI1nCS[0]	
74	N2HET[8]	106	N2HET[8]	
75	TMS	108	TMS	
76	nTRST	109	nTRST	
77	TDI	110	TDI	
78	TDO	111	TDO	
79	TCK	112	TCK	
80	RTCK	113	RTCK	
81	nRST	116	nRST	
82	nERROR	117	nERROR	
83	N2HET[10]	118	N2HET[10]	
84	ECLK	119	ECLK	
85	VCCIO	120	VCCIO	
86	VSS	121	VSS	
87	VSS	122	VSS	
88	VCC	123	VCC	
89	N2HET[12]	124	N2HET[12]	
90	N2HET[14]	125	N2HET[14]	
91	CAN2TX	128	CAN2TX	
92	CAN2RX	129	CAN2RX	
93	MibSPI1nCS[1]	130	MibSPI1nCS[1]	
94	LINRX (UARTRX)	131	LINRX (UARTRX)	
95	LINTX (UARTTX)	132	LINTX (UARTTX)	
96	VCCP	134	VCCP	
97	N2HET[16]	139	N2HET[16]	
98	N2HET[18]	140	N2HET[18]	
99	VCC	143	VCC	
100	VSS	144	VSS	

4 Input/Output Considerations

There are some low-EMI differences for output signals between the LS0914/0714 series vs the LS31x/21x and LS12x/11x series of microcontrollers. These are listed in [Table 3](#).

Table 3. Low-EMI Differences Between LS0914/0714 vs LS31x/21x and LS12x/11x

Low-EMI Name LS0914/0714	Low-EMI Output Buffer Signal Hookup LS0914/0714	Low-EMI Name LS31x/21x and LS12x/11x	Low-EMI Output Buffer Signal Hookup LS31x/21x and LS12x/11x
SPI2	N/A	SPI2	GPREG1.1
TDI	N/A	TDI	GPREG1.9
TEST	N/A	TEST	GPREG1.12
AD1EVT	N/A	AD1EVT	GPREG1.14

5 Module Compatibility Considerations

The LS0914/0714 series of microcontrollers are a subset of the features/functionality available on the LS12x/11x and LS31x/21x series of microcontrollers. As such, the majority of the software written for the superset devices, LS12x/11x and LS31x/21x, will be compatible with the LS0914/0714 series of microcontrollers. However, in some cases, features that are utilized in the superset devices need to be considered either during development of the software or during the porting process to the subset device. In addition, the LS0914/0714 series of microcontrollers has similar enhancements to key peripherals as the LS12x/11x series of microcontrollers. Some key feature differences and brief description of the peripheral enhancements are listed below.

5.1 Feature differences on LS0914/0714 Series

The LS0914/0714 series of microcontrollers is a subset of the LS31x/21x and LS12x/11x series of microcontrollers. Some features are not included as a result of the simpler implementation.

5.1.1 Feature Implementation Differences for the LS0914/0714 Series

- Flash EEPROM emulation bank

The module IP used for the Flash EEPROM emulation is the same as the LS04x/03x series. This new bank is a 72-bit wide bank with slower access times than the bank used on super set series.

- Wait States

The EWAIT parameter within the Flash Wrapper register set will need to be programmed according to the waitstates defines in the data sheet for LS0914/0714 series of microcontrollers.

- Flash Topology

The number and size of each sector in bank 7 has changed from 4, 16kB sector to 16, 4kB, see the *OTP Memory* section in the *TMS570LS0914/0714 16/32-Bit RISC Flash Microcontroller Technical Reference Manual* ([SPNU607](#)).

- Pin muxing/IOMM configuration
The PINMMR register assignments are mostly the same as the LS31x/21x and LS12x/11x series although there are some differences where modules were removed.
- eQEP VIM interrupt mappings are different
The default eQEP VIM interrupt request is 110 on LS0914/0714 devices and 84 on LS04x/03x. Since the EQEP interrupt configuration is different, it results in software incompatibility. Also, in the LS0914/0714 devices, the eQEP module is present on SCR5 (similar to LS12x/11x), whereas, in LS04x/03x, it is present on the PCR. On LS04x/03x, there is a peripheral select bit that needs to be enabled before the eQEP can be used.
- Power Domain States
In the LS0914/0714 devices, the Off state is equivalent to the Idle state in terms of power saving. From a programmer model perspective, users can still put a power domain into the Off state as if the power domain can be physically turned off.

NOTE: This device does not implement power switches to physically isolate the power domain from its power supply. Putting a power domain into the Off state has no effect to remove leakage power. For more details, see the *Power Domains* section in the *TMS570LS0914/0714 16/32-Bit RISC Flash Microcontroller Technical Reference Manual (SPNU607)*.

- Max Clock Speeds
LS0914/0714 devices performance will be similar to the LS12x/11x devices and faster than LS04x/03x. When migrating between series, see the device-specific data sheets.

6 References

- *TMS570LS0914/0714 16/32-Bit RISC Flash Microcontroller Technical Reference Manual (SPNU607)*
- *TMS570LS1227 16- and 32-Bit RISC Flash Microcontroller Data Manual (SPNS192)*
- *TMS570LS0432/0332 16- and 32-Bit RISC Flash Microcontroller Data Manual (SPNS186)*
- *TMS570LS0914 16- and 32-Bit RISC Flash Microcontroller Data Manual (SPNS225)*
- *TMS570LS0714 16- and 32-Bit RISC Flash Microcontroller Data Manual (SPNS226)*

Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Changes from Original (November 2014) to A Revision	Page
• Removed ZWT package as this is no longer supported.	2

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com