

Non-Isolated DC/DC Solutions for Alder Lake in Notebook Computing Applications



Richard Nowakowski

ABSTRACT

Notebook, desktop, and industrial computers serve to improve business continuity, enhance consumer entertainment, and streamline industrial process control. Texas Instruments provides performance power-management solutions for these applications to improve performance and extend battery life. Advanced processors and platforms, such as the Intel® Alder Lake micro-architecture, need point-of-load (POL) solutions for memory, low-power CPU rails, and 3.3 V and 5 V rail requirements from an array of rechargeable batteries, or a 12 V input bus. This document intends to highlight DC/DC converters and describe their features addressing general Alder Lake power requirements. For specific information about Intel processors and their power requirements, log on to the Intel Resource and Design Center. Contact TI for information about multiphase controllers and power stages designed specifically for the Intel Mobile Voltage Positioning (IMVP) requirements.

Table of Contents

1 Suggested Point-of-Load Solutions.....	2
2 Light Load Efficiency (Eco-Mode™) and Low Quiescent Current (ULQ™).....	3
3 Voltage Identification (VID) Capability with TPS51215A.....	4
4 Fast Load Transient Response with D-CAP3™ and D-CAP2™ Control.....	4
5 Small IC Packaging.....	6
6 Conclusion.....	6
7 Resources.....	7

List of Figures

Figure 2-1. TPS51285A Efficiency Plot.....	3
Figure 4-1. TPS51395 Transient Waveform.....	4
Figure 4-2. TPS51215A Load Transient Waveform.....	5
Figure 5-1. TPS566335 in 2x3mm QFN Package.....	6

List of Tables

Table 1-1. Suggested DC/DC Controllers and Converters for Alder Lake.....	2
Table 4-1. TPS51215A Load Transient Test Results.....	5

Trademarks

D-CAP3™ and D-CAP2™ are trademarks of Texas Instruments.
All trademarks are the property of their respective owners.

1 Suggested Point-of-Load Solutions

Table 1-1 highlights the latest POL DC/DC converters with integrated MOSFETs and controllers suitable for Alder Lake applications. The suggested devices are selected to accommodate different input voltage and control mode requirements over a wide range of output current. The featured devices in the left column accommodate a maximum input voltage of 22 V or greater, and are designed to achieve fast load-transient response with an adaptive on-time control mode, high light and full-load efficiency, and low quiescent current.

Several devices include an integrated programmable voltage identification (VID) supporting the processor's adaptive voltage requirements. The alternate devices in the right column employ fixed-frequency current-mode control with frequency synchronization useful in noise-sensitive industrial applications, and operate up to a 17 V input. If VID is required with alternative devices, consider the LM10011 VID voltage programmer in addition to the converter's resistor divider network.

Table 1-1. Suggested DC/DC Controllers and Converters for Alder Lake

Featured P/N ⁽¹⁾	Rail	Current Capability	Type	Note	Alternate P/N ⁽²⁾
TPS51285A	V5A	≤20A + 100mA LDO each rail	Dual Controller & 2 LDOs	System Power	TPS51220A
	V3P3				
TPS51395	V5A	≤8A + 100mA LDO	Converter & LDO	System Power	TPS54A24
TPS51393	V3P3				
TPS51215A	V _{CCIN_AUX}	≤32A	Controller	I/O power, 2-bit VID (0V support)	-
TPS566335	V1P8A	≤6A	Converter		TPS543620
TPS51372	Optional Bypass	≤6.5A	Converter	2-bit VID	-
General Purpose DC/DC Converters					
TPS51367	Various	12A	Converter	General	TPS54A24
TPS51397A	Various	10A	Converter	General	TPS54A24
TPS51396A	Various	8A	Converter	General	TPS543820
TPS566335	Various	6A	Converter	General	TPS543620
TPS56339	Various	3A	Converter	General	TPS543320
DDR Memory Power Solutions					
TPS51486A	V _{DDQ}	≤8A	Multi-Channel Converter	DDR4 Memory	TPS65295
	V _{PP}	≤1A			
	V _{TT}	±1A			
	V _{TT_REF}	10mA			
TPS51487XA	V _{DD1}	≤8A	Multi-Channel Converter	LPDDR4/X Memory	TPS65296
	V _{DD2}	≤1A			
	V _{DDQ_TX}	≤1.5A			
TPS51397A	V _{DD2H/L}	≤10A	Converter	LPDDR5 Memory	Consider general device for more/less current
TLV62084A	V _{DD1}	≤2A	Converter		TPS543320
TLV62084A	V _{DDQ}	≤2A	Converter		TPS543320

- Some featured 24-V devices require Mysecure access to download the data sheet. Click the device link to request access. Users will require their my.ti.com account information.
- Alternate converters operate up to 17 V input with a fixed-frequency control mode

2 Light Load Efficiency (Eco-Mode™) and Low Quiescent Current (ULQ™)

The POL regulators generating low voltages from an array of batteries must employ an energy-saving pulse-skipping technique now referred to as Eco-Mode. The inductor current in a synchronous-buck converter is a triangle wave. As the output current decreases from a heavy-load condition, the inductor current is reduced and the rippled valley of the triangle wave eventually touches the zero level at the boundary between continuous conduction-mode (CCM) and discontinuous conduction mode (DCM).

With Eco-Mode, the rectifying MOSFET is turned off when the converter detects zero current in the inductor. As the load current further decreases, the on-time is held nearly constant so that the off-time is extended, and the switching frequency is reduced to maintain regulation. As a result, the power MOSFETs and inductor are idle for longer time periods and conduction losses are greatly reduced. DC/DC converters and controllers with low quiescent current will have improved light-load efficiency performance and extended battery run-time, since less power is dissipated within the IC. The TPS51825A features Ultra Low Quiescent current (ULQ) of 25- μ A for longer battery life in system stand-by mode.

Figure 2-1 shows 90% efficiency with 7.4-V input and 5-V output at 1-mA, illustrating the combined affects of Eco-Mode and ULQ.




Figure 2-1. TPS51825A Efficiency Plot

3 Voltage Identification (VID) Capability with TPS51215A

The TPS51215A supports a 2-bit VID and Low Power Mode (LPM) to dynamically change the output voltage to satisfy Intel IMVP8/9 applications for VCCIN_AUX, VCCIO_0, and VCCIO_1_2 rails. A fixed 0V output voltage and up to three voltage levels can be programmed externally with a voltage divider circuit. The device can also be configured to provide a 1-bit VID output voltage. Please see the [TPS51215A Single Phase, D-CAP2™ Controller with 2-Bit VID Control and Low Power Mode](#) data sheet for more information.

4 Fast Load Transient Response with D-CAP3™ and D-CAP2™ Control

Since the load profile can change dramatically in Notebook and Desktop PC applications, it is important to consider AC transient performance. Choosing a DC/DC converter with a fast transient response using non-linear control techniques, such as constant on-time or D-CAP3™, allows a fast transient response with minimal output capacitance. A converter using D-CAP3 control mode has three primary considerations for deciding the value of the output capacitance: transient (which includes load step and slew rate of the load step) output ripple, and stability.

In applications where the load transient is stringent, the output capacitance is predominantly driven by the transient requirement. For a D-CAP3 based design, there is a minimum capacitance requirement in terms of small signal stability. This requirement prevents subharmonic, multiple-pulsing behavior in the modulator.

Figure 4-1 shows the transient performance of the 8-A TPS51395 with a 5-V output, less than 100mV overshoot, and less than a 30µs recovery with output capacitance of 0.1 µF and 4x22 µF. The 0.8-A to 7.2-A load step has a slew rate of 2.5-A/µs.




Figure 4-1. TPS51395 Transient Waveform

The TPS51215A supplying VCCIN_AUX features adaptive on-time D-CAP2™ control allowing ceramic output capacitors and achieves a fast load transient response shown in Figure 4-2 under the noted conditions below the waveform. The over-voltage and under-voltage test results also meet the target design specification, and the results are shown in Table 4-1 under the same conditions as the TPS51215A load transient waveform. The TPS51215A waveform conditions are $V_{IN}=12.6V$, slew rate=12A/µs, $F_{SW}=600k\Omega$, $L=0.22\mu H$, and $C_{OUT}=220\mu F + 22*12\mu F$.




Figure 4-2. TPS51215A Load Transient Waveform

Table 4-1. TPS51215A Load Transient Test Results

Voltage Rail	Type	Load Transient	Validation Result (V)	Target (V)
0.8 V	Undershoot	0 A to 16 A	1.67	1.62
	Overshoot	16 A to 0 A	1.858	1.89
1.8 V	Undershoot	17 A to 29 A	1.678	1.62
	Overshoot	29 A to 17 A	1.882	1.89

5 Small IC Packaging

Integrated circuit packaging technology must keep pace with semiconductor wafer fabrication as process technology advances. TI released flip-chip on leadframe packaging that reduce package footprint, power loss, and parasitic effects. Traditional bond wires are replaced with copper posts attached directly to the leadframe which shortens current path from the IC to the lead frame, which allows a larger die in the small package cavity, reduced package resistance, and reduced parasitic package inductance loops. Consider the 6-A TPS566335, housed in a small 2x3mm QFN package.

Figure 5-1 shows ample pins for power conversion and I/O features while maintaining a 0.5mm pin pitch, allowing simplified circuit board manufacturing.




Figure 5-1. TPS566335 in 2x3mm QFN Package

6 Conclusion

Performance processors, such as the Alder Lake platform in Notebook and Industrial PCs, need DC/DC converters that offer fast transient response, small packaging, low quiescent current, and high light and full-load efficiency. TI offers high performance point-of-load solutions to address these requirements while lowering the total system cost.

7 Resources

- Texas Instruments, [LM10011 VID Programmer](#) data sheet.
- Texas Instruments, [Accuracy-Enhanced Ramp-Generation Design for D-CAP3 Modulation](#) application report.
- Texas Instruments, [Power tips: Iq \(quiescent current\) and Light Load Efficiency](#) training video.
- Texas Instruments, [HotRod QFN Package PCB Attachment](#) application note.

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (<https://www.ti.com/legal/termsofsale.html>) or other applicable terms available either on [ti.com](https://www.ti.com) or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2021, Texas Instruments Incorporated