

TPS386000-Q1 Pin FMEA

Toshimi Satoh

ABSTRACT

The TPS386000-Q1 family of voltage supervisors monitors four power rails that are greater than 0.4 V and one power rail that is less than 0.4 V (including negative voltage) with a 0.25% (typical) threshold accuracy. Each of the four supervisory circuits (SVS-*n*) asserts a $\overline{\text{RESET}}n$ or $\text{RESET}n$ output signal when the $\text{SENSE}m$ input voltage drops below the programmed threshold. With external resistors, the threshold of each SVS-*n* can be programmed (where $n = 1, 2, 3, 4$ and $m = 1, 2, 3, 4L, 4H$).

Each SVS-*n* has a programmable delay before releasing $\overline{\text{RESET}}n$ or $\text{RESET}n$. The delay time can be set from 1.4 ms to 10 seconds through the $\text{CT}n$ pin connection. Only SVS-1 has an active-low manual reset (MR) input which is a logic-low input to MR that asserts $\overline{\text{RESET}}1$ or $\text{RESET}1$.

SVS-4 monitors the threshold window using two comparators. The extra comparator can be configured as a fifth SVS to monitor negative voltage with the voltage-reference output, VREF.

The TPS386000-Q1 device has a very-low quiescent current of 12 mA (typical) and is available in a small, 4-mm x 4-mm, QFN-20 package.

Contents

List of Tables

1	Classification of Failure Effects	2
2	Pin FMEA Analysis for Pin Short-Circuit to GND	2
3	Pin FMEA Analysis for Pin Left Open	3
4	Pin FMEA Analysis for Pin Short-Circuit to VCC	4
5	Pin FMEA Analysis for Pin Short-Circuit to Neighboring Pin	5

Pin FMEA

This application note provides a **Failure Modes and Effects Analysis (FMEA)** for the device pins of the TPS386000-Q1 quad-supply voltage-supervisor device with programmable delay and watchdog timer. The failure conditions covered in this document include typical failure scenarios such as short-circuit to GND, short-circuit to VCC, short-circuit to a neighboring pin, and if the pin is left open. The following tables list how these conditions affect the device. The first effect considered is whether the condition damages the pin in question or the device itself. The second effect considered is whether the device is functional under the condition. Lastly, the analysis includes a comments section that discusses how the particular condition affects the device operation.

NOTE: The first letter, X, of the pin name is expressed with the active-low bar.

Table 1. Classification of Failure Effects

Class	Failure Effects
A	Damage to device affects application functionality
B	No damage to device but thermal damage must be considered
C	No damage to device but can affect application functionality
D	No damage to device and no affect to application functionality

Table 2. Pin FMEA Analysis for Pin Short-Circuit to GND

Pin		Short to GND			
No.	Name	Damage	Functionality	Comments	Class
1	\overline{MR}	NO	YES	Can affect functionality of the sub-CPU circuit that drives \overline{MR} pin.	D
2	CT4	NO	YES	A pulldown transistor is located on each pin. If these pins are shorted to GND, the programmable delay circuit does not function correctly.	D
3	CT3				
4	CT2				
5	CT1				
6	SENSE4H	NO	YES		D
7	SENSE4L	NO	YES	The corresponding \overline{RESETn} output is always asserted if the SENSEn input is shorted to GND.	D
8	SENSE3				
9	SENSE2				
10	SENSE1				
11	NC	NO	YES	This pin has no electrical connection.	D
12	GND	NO	YES	Normal operating condition	D
13	VREF	NO	YES	1.2 V at 5 mA (max)	B
14	VCC	NO	Can affect functionality	No damage to device, can affect application functionality. Increases leakage.	C
15	$\overline{RESET1}$	NO	YES	Whichever device is connected to the \overline{RESETn} the output is always in reset if these pins are shorted to GND.	D
16	$\overline{RESET2}$				
17	$\overline{RESET3}$				
18	$\overline{RESET4}$				
19	\overline{WDO}	NO	Can affect functionality	User does not have any watchdog functionality.	C
20	WDI	NO	Can affect functionality	User does not have any watchdog functionality.	C

Table 3. Pin FMEA Analysis for Pin Left Open

Pin		Short to GND			
No.	Name	Damage	Functionality	Comments	Class
1	MR	NO	Can affect functionality	Undefined operating condition, no damage, increases leakage	C
2	CT4	NO	YES	Leaving these pins open results in a 20-ms (typical) delay.	D
3	CT3				
4	CT2				
5	CT1				
6	SENSE4H	NO	YES	Undefined operating condition ($\overline{\text{RESET4}}$ tends to become High)	D
7	SENSE4L	NO	YES	Undefined operating condition ($\overline{\text{RESET4}}$ tends to become Low)	D
8	SENSE3	NO	YES	Undefined operating condition ($\overline{\text{RESET3}}$ tends to become Low)	D
9	SENSE2	NO	YES	Undefined operating condition ($\overline{\text{RESET2}}$ tends to become Low)	D
10	SENSE1	NO	YES	Undefined operating condition ($\overline{\text{RESET1}}$ tends to become Low)	D
11	NC	NO	YES	This pin has no electrical connection.	D
12	GND	NO	NO	Undefined operating condition, no damage, increases leakage	C
13	VREF	NO	YES	Normal operating condition	D
14	VCC	NO	NO	Undefined operating condition, no damage, increases leakage	C
15	$\overline{\text{RESET1}}$	NO	YES	Normal operating condition, this pin is an open-drain output.	D
16	$\overline{\text{RESET2}}$				
17	$\overline{\text{RESET3}}$				
18	$\overline{\text{RESET4}}$				
19	$\overline{\text{WDO}}$				
20	WDI	NO	Can affect functionality	User does not have any watchdog functionality.	C

Table 4. Pin FMEA Analysis for Pin Short-Circuit to VCC

Pin		Short to GND			
No.	Name	Damage	Functionality	Comments	Class
1	\overline{MR}	NO	YES	Can affect functionality of the sub-CPU circuit that drives \overline{MR} pin.	D
2	CT4	NO	YES	A large current flows during wakeup, but it can be low power. TI recommends to pull these pins up to VCC with a 40k to 200k resistor.	D
3	CT3				
4	CT2				
5	CT1				
6	SENSE4H	NO	YES	The $\overline{RESET4}$ output is always be asserted if the SENSE4H input is shorted to VCC. The DC-DC or LDO that is monitored is affected.	D
7	SENSE4L	NO	YES	The DC-DC or LDO that is monitored is affected.	D
8	SENSE3				
9	SENSE2				
10	SENSE1				
11	NC	NO	YES	This pin has no electrical connection.	D
12	GND	NO	NO	No damage to device, can affect application functionality. Increases leakage.	C
13	VREF	NO	YES	1.2 V at 5 mA (max)	B
14	VCC	NO	YES	Normal operating condition	D
15	$\overline{RESET1}$	YES	NO	$I_{RESET} < 5 \text{ mA (absolute)}$	A
16	$\overline{RESET2}$				
17	$\overline{RESET3}$				
18	$\overline{RESET4}$				
19	\overline{WDO}	YES	NO	$I_{WDO} < 5 \text{ mA (absolute)}$	A
20	WDI	NO	YES	Functionality of FPGA connected to this pin can be affected.	D

Table 5. Pin FMEA Analysis for Pin Short-Circuit to Neighboring Pin

Pin		Short to GND			
No.	Name	Damage	Functionality	Comments	Class
1	\overline{MR} to CT4	NO	Can affect functionality	No electric damage, increases leakage at \overline{MR} . The desired delay is not achieved if these pins are shorted together.	B
2	CT4 to CT3	NO	YES	The desired delay is not achieved if these pins are shorted together.	D
3	CT3 to CT2				
4	CT2 to CT1				
5	CT1 to SENSE4H	NO	YES	The desired delay is not achieved if these pins are shorted together. The respective \overline{RESETn} outputs do not function as desired.	D
6	SENSE4H to SENSE4L	NO	YES	The respective \overline{RESETn} outputs do not function as desired.	D
7	SENSE4L to SENSE3				
8	SENSE3 to SENSE2				
9	SENSE2 to SENSE1				
10	SENSE1 to NC	NO	YES		D
11	NC to GND	NO	YES		D
12	GND to VREF	NO	YES	1.2 V at 5 mA (max)	B
13	VREF to VCC	NO	YES	1.2 V at 5 mA (max)	B
14	VCC to $\overline{RESET1}$	YES	NO	$I_{\overline{RESET}} < 5 \text{ mA}$ (absolute)	A
15	$\overline{RESET1}$ to $\overline{RESET2}$	NO	YES		C
16	$\overline{RESET2}$ to $\overline{RESET3}$				
17	$\overline{RESET3}$ to $\overline{RESET4}$				
18	$\overline{RESET4}$ to \overline{WDO}				
19	\overline{WDO} to WDI	NO	Can affect functionality	Functionality of FPGA connected to this pin can be affected.	B
20	WDI to \overline{MR}	NO	Can affect functionality	Undefined operating condition, no damage, increases leakage	C

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com