

TPS6208x and TLV6208x Device Comparison

Michael Helmlinger, Felix Risch

Low Power DC/DC

ABSTRACT

This application report presents an overview of the differences among the TPS62080, TPS62081, TPS62082, TPS62080A, TLV62080, TLV62084, and TLV62084A power management integrated circuits (IC). It can assist design engineers in selecting the most suitable IC for their applications. The devices are a family of high frequency synchronous step-down converters, available in a 2-mm x 2-mm QFN package. All devices are pin-to-pin compatible, unless the *Snooze Mode* is used.

Contents

1	Family Members	1
2	Feature Explanations.....	2
	2.1 Power -Good Behavior	2
	2.2 Output Discharge	3
	2.3 Snooze Mode.....	3
3	Conclusion	3

List of Figures

1	TLV62084 PG Behavior (PG Pulled up to V_{OUT})	2
2	TLV62084A PG Behavior (PG Pulled up to V_{OUT})	2
3	TLV62084 PG Behavior (PG Pulled up to V_{sys})	2
4	TLV62084A PG Behavior (PG Pulled up to V_{sys})	2
5	TPS62080 Output Discharge.....	3
6	TPS62080A Output Discharge.....	3

List of Tables

1	TPS6208x and TLV6208x Family Members	1
---	--	---

1 Family Members

Table 1. TPS6208x and TLV6208x Family Members

Device	TPS62080	TPS62080A	TLV62080	TLV62084	TLV62084A
Input Voltage Range	2.3 V–6 V	2.3 V–6 V	2.5 V–6 V	2.7 V–6 V	2.7 V–6 V
Output Voltage Range	0.5 V - 4 V	0.5 V–4 V	0.5 V–4 V	0.5 V–4 V	0.5 V–4 V
	TPS62081 fixed 1.8V				
	TPS62082 fixed 3.3V				
Max Output Current	1.2 A	1.2 A	1.2 A	2 A	2 A
Power Good Logic Level (EN = Low)	High Impedance	High Impedance	High Impedance	High Impedance	Low
Output Discharge Resistor	1 k Ω	40 Ω	1 k Ω	1 k Ω	1 k Ω
Power Save Mode	√	√	√	√	√
Snooze Mode	√	√			

2 Feature Explanations


2.1 Power -Good Behavior

All devices from [Table 1](#) have a power-good (PG) output to indicate whether the output voltage has reached its appropriate level or not. The power good goes high impedance once the output is above 95% of the regulated voltage, and is driven low once the output voltage falls below typically 90% of the regulated voltage. The PG pin is an open-drain output and is specified to sink up to 0.5 mA. The power good output requires a pull-up resistor which is recommended to connect to the output voltage of the device. V_{IN} must remain present for the PG pin to stay Low. If not used, the PG pin should be connected to GND but may be left floating.

The TLV62084A device differs from the other devices in how the PG (power good) pin is controlled when the device is disabled, in UVLO, or in thermal shutdown. The TLV62084A holds the PG pin low during these conditions, while the other devices of this family set the PG pin high impedance (floating). This is typically only important in a system that uses multiple voltage rails.



Configuration 1: PG Pin Pulled up to V_{OUT}

[Figure 1](#) and [Figure 2](#) show the difference in PG pin operation when the IC gets disabled without an output load. For these waveforms, the PG pin is connected to the 1.2-V output voltage through a pull-up resistor. In this configuration, there is only a difference in the time it takes for the PG pin to go low. The PG pin goes low in both cases. With an increasing output load, the PG pin goes low faster in the first case.





Configuration 2: PG Pin Pulled up to a System Rail

[Figure 3](#) and [Figure 4](#) show the difference in PG pin operation when the IC gets disabled without an output load. The PG pin is connected, through a pull-up resistor, to a 5-V system rail which is not the 1.2-V output voltage of the IC. In this configuration, there is an important difference between the performance of the device, as the PG pin goes low with the TLV62084A but remains high with the TLV62084.



2.2 Output Discharge

Figure 5 and Figure 6 show the difference in output discharge operation when the IC gets disabled without an output load. The TPS62080A has a smaller discharge resistor value and thus the output gets discharged faster compared to the TPS62080.



2.3 Snooze Mode

While all devices from Table 1 have a *Power Save Mode*, only the TPS62080, TPS62081, TPS62082, and TPS62080A implement an additional *Snooze Mode*. If *Snooze Mode* is enabled (by setting the MODE pin to HIGH), the quiescent current consumption of the device is reduced even further compared to the *Power Save Mode*. This results in higher efficiency at lowest output currents. See the TPS62080 data sheet (SLVSAE8) for more details.

3 Conclusion

The TLV62084A device provides easier integration into multi-rail systems due to its PG behavior. For this reason, the TLV62084A device is generally recommended over the TLV62084 since the devices are pin-to-pin compatible. If the *Snooze Mode* is desired, the TPS6208x device can be used.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com