

PMP5315_REVB BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
1	C1	220uF	Capacitor, Aluminum, 400V	30 x 30mm	ECOS2GP221DA	Panasonic
1	C12	100uF	Capacitor, Aluminum Electrolytic, 25V	0.248 inch	25V ZL 100uF 6.3 X 11	Rubycon
1	C13	1500pF	CAP, CERM DISC Y1, 250Vac, 20%	.500 X .310	ECKDNA152ME	Panasonic
1	C14	0.047uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H473K	TDK
2	C15, C18	100pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H101K	TDK
1	C16	0.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H103K	TDK
1	C17	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H104K	TDK
2	C2, C3	0.22 uF	Capacitor, Film, 250VAC, 20%	0.689 x 0.217	STD	STD
1	C4	0.01uF	Capacitor, Polyester Film, 250V, 10%	0.311 x 0.213 inch	ECQ-E2103KB	Panasonic
1	C5	DNP	Do Not Populate	0603	N/A	N/A
2	C6, C11	1uF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
4	C7, C8, C9, C10	2700uF	Capacitor, Aluminum Electrolytic, 25V, 3.45A rms ripple	0.571 inch	25V ZL 2700uF 16 X 25	Rubycon
1	D1	KBPO6G	Diode, Bridge Rectifier, 1.5A, 600V	0.580 x 0.145 inch	KBPO6G	Diodes
1	D2	MBRF30H100CT	Diode, Dual Schottky, 30A, 100V	TO-220	MBRF30H100CT	ON Semi
1	D3	MURA160T3	Diode, Rectifier, 1A, 600V	SMA	MURA160T3	ON Semiconductor
1	D4	MMSD914	Diode, Switching, 100-V, 200-mA, 225-mW	SOD-123	MMSD914T1	On Semi
1	F1	2.5A/250V	Fuse, TR5 Series, 2.5A, 250V	0.335	3701250041	Wickmann
1	HS1	HS350	Heatsink, Vertical-mount, Multipackages	25.4 x 42.0 mm	529802B02500G	Thermalloy
1	HS2	513201	HEATSINK TO-220 W/PINS 1inch TALL	0.5x1.38in.	531002B02500G	Aavid
1	J1		Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25"	ED1514	OST
1	L1	450uH	Inductor, Power Choke, 1.5A	C CODE	I01-0450-01-00	ICE
1	L2	10 uH	Inductor, Common Mode Cok	12.70 x 18.16 mm	ICA 1069	ICE Components
1	L3	9.5 mH	Inductor, Line Filter	18.5 x 25.5 mm	LF24012-0095-V	ICE Components
1	L4	2.2uH	Inductor, Power,	0.350 x 0.300 inch	RFB0807-2R2L	Coilcraft
1	Q1	SPP11N60C3	Trans, Cool MOS Power Nchan, 650V, 11A, 380 millohm	TO-220AB	SPP11N60C3	Infineon
4	R1, R2, R3, R4	30.1k	Resistor, Chip, 1-W, 5%	2512	Std	Std
1	R11	10	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R12, R15	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R13, R21	DNP	Do Not Populate	0603	N/A	N/A
1	R14	150k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R16	698	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R17, R20	4.99k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R18	100k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R19	27.4k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R22	1.21k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R23	21.5k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
5	R24, R25, R26, R27, R28	1	Resistor, Chip, 1/16W, x%	0805	Std	Std
1	R5	DNP	Do Not Populate	1206	N/A	N/A
3	R6, R7, R9	332k	Resistor, Chip, 1/16W, x%	0805	Std	Std
2	R8, R10	499k	Resistor, 1/4 watt, 5%	1206	Std	Std
1	RT1	S10K320	MOV, 50W	0.472 x 0.157 inch	B72210S03321K101	Epcos

Filename: PMP5315_REVB_bom.xls

Date: 04/22/2010

PMP5315_REVB BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
1	T1	240 uH	XFMR, Flyback, Custom	34.5 x 36.00 mm	TT10050-3	
3	TP1, TP2, TP3	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	TP4	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
1	TP6	5002	Test Point, White, Thru Hole Color Keyed	0.100 x 0.100 inch	5002	Keystone
1	U1	UCC28600D	IC, Quasi-Resonant Flyback Green Mode Controller	SO8	UCC28600D	Texas Instruments
1	U2	H11A817A	IC, Optocoupler, 5300-V, 80-160% CTR	0.380 x 0.180 inch	H11A817A	Fairchild
1	U3	TL431AILP	IC, Adj Shunt Regulator	T0-92	TL431AILP	TI

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated