

*TMS320 DSP
DESIGNER'S NOTEBOOK*

'C5x EVM Provides for Audio Processing

APPLICATION BRIEF: SPRA202

*Joe George
Digital Signal Processing Products
Semiconductor Group*

*Texas Instruments
December 1992*



IMPORTANT NOTICE

Texas Instruments (TI) reserves the right to make changes to its products or to discontinue any semiconductor product or service without notice, and advises its customers to obtain the latest version of relevant information to verify, before placing orders, that the information being relied on is current.

TI warrants performance of its semiconductor products and related software to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

Certain application using semiconductor products may involve potential risks of death, personal injury, or severe property or environmental damage ("Critical Applications").

TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, INTENDED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT APPLICATIONS, DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS.

Inclusion of TI products in such applications is understood to be fully at the risk of the customer. Use of TI products in such applications requires the written approval of an appropriate TI officer. Questions concerning potential risk applications should be directed to TI through a local SC sales office.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards should be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or services described herein. Nor does TI warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used.

TRADEMARKS

TI is a trademark of Texas Instruments Incorporated.

Other brands and names are the property of their respective owners.

CONTACT INFORMATION

US TMS320 HOTLINE	(281) 274-2320
US TMS320 FAX	(281) 274-2324
US TMS320 BBS	(281) 274-2323
US TMS320 email	dsph@ti.com

Contents

Abstract.....	7
Design Problem.....	8
Solution.....	8

Figures

Figure 1. 32K-word 'C5x Circular Buffer For Reverberation.....	8
---	----------

Examples

Example 1. Serial Port Receive Interrupt Service Routine	9
---	----------

'C5x EVM Provides for Audio Processing



Abstract

The TMS320C5x evaluation module (EVM) has RCA input/output jacks and a TLC32046 Analog Interface Chip (AIC). It offers an easy-to-configure system for audio processing applications. Whether implementing simple delays and echoes, or complex multi-filter digital reverberation, TMS320C5x EVM features make it easy.




Design Problem

How do I interface a 'C5x to analog signals?

Solution

The TMS320C5x EVM, with its input/output RCA jacks and TLC32046 Analog Interface Chip (AIC), offers an easy-to-configure system for audio processing. Whether implementing simple delays and echoes or complex multi-filter digital reverberation, 'C5x features make it easy. Some simple artificial digital reverberation code with absolute delay that simulates four echoes in a room is available on the TMS320 BBS in the file C5XEVAUD.EXE. The code first initializes the AIC and then sets up the 'C5x's two circular buffer pointers to point at different places in a single 32K word buffer (see Figure 1). This configuration corresponds to a receive pointer and a transmit pointer. In the serial port receive Interrupt Service Routine (ISR) (see Example 1), the 'C5x receives and stores data (at sample n) in the single buffer, but manipulates and transmits data stored earlier ($n - \text{absdelay}$) in the buffer. This permits a programmable absolute delay, which makes any processing effects more obvious. The manipulation in the ISR shows the scaling of four echoes at 1 (at $n - \text{absdelay}$), $1/2$ (at $n - \text{absdelay} - 1 * \text{INDX}$), $1/4$ (at $n - \text{absdelay} - 2 * \text{INDX}$), and $1/8$ (at $n - \text{absdelay} - 3 * \text{INDX}$). The echoes are then summed.

Figure 1. 32K-word 'C5x Circular Buffer For Reverberation





The delay between the echoes is previously stored in the index register. This index may be varied in code to hear the effects of various inter-echo delays. To prevent the circular addressing from indexing an invalid address, write a 1 to the Most Significant Bit (MSB) of the indirect address since the buffer from 8000h to FFFFh is always 1. This is done using the Parallel Logic Unit. A NOP is inserted for pipeline considerations as explained in Section 3.6.2 in the TMS320C5x User's Guide. Be sure to mask off the lowest two bits as zeroes at the end of the ISR since they are command bits for the AIC.

Example 1. Serial Port Receive Interrupt Service Routine

```
receive:
    MAR    *,AR7                ; Receive Pointer
    LACC   DRR                  ; Read sample from AIC
    SACL   *+                   ; Store to buffer (at n)
    MAR    *,AR6                ; Transmit Pointer
    SAR    AR6, 60h             ; Store Temp
    LACC   *0-, 16              ; Load previous value
                                        ; (at n-absdelay)
                                        ; (Divide by 1)
    OPL    #8000h, AR6          ; Write 1 for addressing
    NOP
    ADD    *0-, 15              ; Add previous value
                                        ; (at n-absdelay-INDX)
                                        ; (Divide by 1/2)
    OPL    #8000h, AR6          ; Write 1 for addressing
    NOP
    ADD    *0-, 14              ; Add previous value
                                        ; (at n-absdelay-2*INDX)
                                        ; (Divide by 1/4)
    OPL    #8000h, AR6
    NOP
    ADD    *0-, 13              ; Add previous value
                                        ; (n-absdelay-3*INDX)
    AND    #0FFFCh, 16          ; Mask off lowest 2 bits
    SACH   DXR                  ; Transmit to AIC
    LAR    AR6, 60h             ; Load back temp
    MAR    *+, AR6              ; Increment by one sample
    RETE
```