

Filename: PMP5536_REV_A_bom.xls

Date: 06/09/2010

PMP5536_REV_A BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
1	C1	47uF	Capacitor, Aluminum Electrolytic, 450V	0.571 inch	EKXJ451ESS470ML25S	Nippon Chemi-Con
1	C2	1000uF	Capacitor, Aluminum Electrolytic, 35V	0.492 inch	35V ZL 1000uF 12.5 X 25	Rubycon
1	C3	4.7uF	Capacitor, Ceramic, 50V, X7R, 20%	1210	GRM32ER71H475KA88L	Murata
2	C4	0.1uF	Capacitor, Film, MKP 338 X2, 275VAC, 20%	.470x.250 inch	2222 338 20104	BC Components
	C5	0.1uF	Capacitor, Film, MKP 338 X2, 275VAC, 20%	.470x.250 inch	2222 338 20104	BC Components
1	C6	0.01uF	Capacitor, Ceramic, 630V, C0G, 10%	1206	C3216CH2J103K	TDK
1	C7	22uF	Capacitor, Ceramic, 16V, X7R, 20%	1210	C3225X7R1C226MT	TDK
2	C9	27uF	Capacitor, Aluminum Electrolytic, 25V	0.200 * 0.435 inch	25V ZL 27uF 5 X 11	Rubycon
2	C10	1uF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
3	C11	100pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H101K	TDK
1	C12	0.047uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H473K	TDK
	C13	1uF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
	C14	100pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H101K	TDK
1	C15	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H104K	TDK
1	C16	0.01uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H103K	TDK
	C17	100pF	Capacitor, Ceramic, 50V, X7R, 10%	0603	C1608X7R1H101K	TDK
1	C18	0.01uF	CAP, CERM DISC, 250Vac, 20%	.500 X .310	ECKATS103MF6	Panasonic
	C19	27uF	Capacitor, Aluminum Electrolytic, 25V	0.200 * 0.435 inch	25V ZL 27uF 5 X 11	Panasonic
1	D1	ES3D	Diode, 3A, 200V	SMC	ES3D-13-F	Diodes Inc.
1	D2	RH06-T	Diode, Bridge, 0.5-A, 600-V	MiniDIP	RH06-T	Diodes
1	D3	US1K	Diode Ultrafast, 1-A, 800-V	SMA	US1K	Diodes Inc.
1	D4	B160-13	Diode, Schottky, 1-A, 60-V	SMA	B160-13	Diodes Inc.
1	D5	BAS20	Diode, Switching, 150V, 200mA	SOT23	BAS20LT1	On Semiconductor
2	D6	BAS16	Diode, Switching, 75V, 200mA	SOT23	BAS16LT1	On Semiconductor
	D7	BAS16	Diode, Switching, 75V, 200mA	SOT23	BAS16LT1	On Semiconductor
1	F1	1.6A/250V	Fuse, TR5 Series, 1.6A, 250V	0.335	3701160041	Wickmann
2	J1	ED1514	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	OST
	J2	ED1514	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	OST
1	L1	10mH	Inductor, Common-Mode, 0.25A	0.906 x 0.748 inch	UU9.8V-103	GCI
1	Q1	IRFBC30A	MOSFET, N-ch, 600-V, 3.6-A, 2.2-Ohms	TO-220V	IRFBC30A	International Rectifier
3	R1	10	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R2	499k	Resistor, Chip, 1/4W, 5%	1210	Std	Std
1	R3	100k	Resistor, Chip, 1W, 5%	2512	STD	STD
	R4	499k	Resistor, Chip, 1/4W, 5%	1210	Std	Std
	R5	10	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R6	499k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R7	210k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R8	49.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R9	4.99k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R10	4.99k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R11	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std

1	R12	41.2k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R13	15k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R14	10k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R15	1k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R16	0.36	Resistor, Chip, 1/4W, 5%	1210	Std	Std
1	R17	1.15k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R18	100k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R19	10	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R100	357k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R101	110k	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	RT1	20 Ohms	Thermistor, NTC, 20 Ohms	0.197 DIA.	ERT-D2FEL200S	Panasonic
1	T1	SRW2425EG-U05V015	Transformer, Custom, Flyback	1.004 x 1.181 inch	SRW2425EG-U05V015	TDK
5	TP1	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP2	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
2	TP3	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
	TP4	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP5	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
	TP6	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
	TP7	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	U1	UCC28600D	IC, Quasi-Resonant Flyback Green Mode Controller	SO8	UCC28600D	Texas Instruments
1	U2	H11A817AS	IC, Optocoupler, 5300-V, 50-160% CTR	0.435 x 0.210 inch	H11A817AS	Fairchild
1	U3	TL431AIDBZ	IC, Precision Adjustable Shunt Regulator	SOT23-3	TL431AIDBZ	Texas Instruments
1	U4	TPS77601D	IC, Fast Transient Response, 0.5-A LDO Voltage Regulator	SO8	TPS77601D	TI

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
 2. These assemblies must be clean and free from flux and all contaminants.
Use of no clean flux is not acceptable.
 3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
 4. Ref designators marked with an asterisk (***) cannot be substituted.
All other components can be substituted with equivalent MFG's components.

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated