

## PMP4908\_REVA BOM

COUNT	RefDes	Value	Description	Size	Part Number	Mfr
2	C1, C24	0.1uF	Capacitor, Ceramic, 100V, X7R, 10%	0805	Std	TDK
1	C10	560uF	Capacitor, Aluminum, 6.3V, 20%	0.315 inch	6.3V ZL 560uF 8 X 11	Rubycon
1	C11	47uF	Capacitor, Ceramic, 6.3V, X5R, 20%	1206	C3216X5R0J476M	TDK
1	C12	0.047uF	Capacitor, Ceramic, 250V, X7R, 10%	1206	Std	Std
1	C14	47pF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
2	C15, C23	1uF	Capacitor, Ceramic, 16V, X7R, 20%	0603	C1608X7R1C105M	TDK
1	C16	22uF	Capacitor, Ceramic, 16V, X7R, 20%	1206	C3216X7R1C226M	TDK
1	C17	1000pF	Capacitor, Ceramic, 2KV, X7R, 10%	1812	C4532X7R3D102K	TDK
1	C18	0.22uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std
1	C19	0.022uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	C2	47uF	Capacitor, Aluminum, 63V, ±20%	8x10.2mm	EEEFK1J470P	Panasonic
1	C20	DNP	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	C21	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	Std	Std
1	C22	4.7uF	Capacitor, Ceramic, 6.3V, X5R, 20%	0603	C1608X5R0J475M	TDK
2	C3, C4	2.2uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	C3225X7R2A225K	TDK
6	D3, D4, D8, D10, D11, D12	MMSD914	Diode, Switching, 100-V, 200-mA, 225-mW	SOD-123	MMSD914T1	On Semi
1	D9	BAV99	Diode, Dual Ultra Fast, Series, 200-mA, 70-V	SOT23	BAV99	Fairchild
2	J1, J3	ED555/2DS	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25 inch	ED555/2DS	OST
1	J2	ED120/2DS	Terminal Block, 2-pin, 15-A, 5.1mm	0.40 x 0.35 inch	ED120/2DS	OST
1	L1	3.3uH	Inductor, SMT, 1.53A, 32milliohm	5.1x5.1mm	MSS5131-332MX	Coilcraft
1	L2	6uH	Inductor, SMT, 7.1A, 6.05 milliohm	12.9x13.1mm	SER1360-602KL	Coilcraft
1	L3	1500uH	Inductor, SMT, 120mA, 4.6 Ohm	6x6mm	LPS6235-155ML	Coilcraft
1	Q2	Si2325DS	MOSFET,P-ch, -150 V, 690-mA, 1.2 Ohms	SOT-23	Si2325DS	Vishay
1	Q3	FDS2572	MOSFET, N-ch, 150V, 4.9A, 47 milliohm	SO8	FDS2572	Fairchild
1	Q4	MMBT3906	Bipolar, PNP, 40V, 200mA, 225mW	SOT23	MMBT3906LT1	On Semi
2	Q6, Q7	CSD16406Q3	MOSFET, NChan, 25V, 19A, 5.9 milliohm	QFN3.3X3.3mm	CSD16406Q3	TI
1	R10	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R11	1.5K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R13	499	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R14	301	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R16, R23	DNP	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R17	41.2K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R18	75K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R19	69.8K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R20	24.9K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R21	5.90K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R22	63.4	Resistor, Chip, 1/16W, 1%	0603	Std	Std
3	R3, R24, R25	10	Resistor, Chip, 1/16W, 5%	0603	Std	Std
3	R4, R12, R15	10K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R6	0.22	Resistor, Chip, 1/2W, 1%	2010	Std	Std
1	R8	1K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R9	2.2	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	T1	100 uH	Transformer, Forward, 25W	13.46 x 17.75 mm	JA4269-AL	Coilcraft
3	TP1, TP3, TP4	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
1	TP2	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
1	U1	TPS23754PWP-1	IC, IEEE 802.3at PoE Interface and Isolated Converter Controller	PWP20	TPS23754PWP-1	TI
1	U2	TCMT1107	IC, Photocoupler, 80-160% CTR	MF4	TCMT1107	Vishay
1	U3	TLV431ACDBVR	IC, Shunt Regulator, 1.24-V ref, 6-V, 10-mA, 1%	SOT23-5	TLV431ACDBVR	TI

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated