

PMP6797_REVC BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	C1	0.047uF	Capacitor, Ceramic, 100V, X7R, 15%	1206	STD	STD
1	C10	330pF	Capacitor, Ceramic, 3kV, NP0, COG, 10%	1808	Std	Std
1	C11	47uF	Capacitor, Aluminum, 16V, 20%	0.201 x 0.262 inch	EEVFK1C470UR	Panasonic
1	C14	1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	STD	STD
1	C15	100pF	Capacitor, Ceramic, 50V, COG, 10%	0603	STD	STD
1	C16	0.047uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	STD	STD
4	C18, C19, C20, C21	4.7uF	Capacitor, Ceramic, 50V, X7R, 15%	1210	STD	STD
3	C2, C3, C24	10uF	Capacitor, Ceramic, 25V, X5R, 15%	1210	STD	STD
1	C23	4.7uF	Capacitor, Ceramic, 25V, X7R, 15%	1206	STD	STD
1	C25	470uF	CAP ALUM 470UF 35V 20% SMD	0.543 x 0.543	EEV-FK1V471Q	Panasonic
1	C26	100uF	CAP ALUM 100UF 35V 20% SMD	0.328 x 0.390 inch	EEV-FK1V101XP	Panasonic
2	C4, C22	10pF	Capacitor, Ceramic, 100V, COG, 10%	0603	STD	STD
2	C5, C6	1000pF	Capacitor, Ceramic, 50V, X7R, 15%	0603	STD	STD
4	C7, C12, C13, C17	0.1uF	Capacitor, Ceramic, 50V, X7R, 10%	0603	STD	STD
2	D1, D2	12V	Diode, Zener, 12-V	SOT23	STD	STD
8	D3, D4, D5, D6, D7, D8, D9, D10	MMSD914T1	Diode, Switching, 100-V, 200-mA, 225-mW,	SOD-123	MMSD914T1	On Semi
2	J2, J3	ED555/2DS	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25 inch	ED555/2DS	OST
1	L1	36uH	Inductor, SMT, 6A, 18.8milliohms	0.750 x 0.875 inch	PA2050-363NL	Pulse
1	L3	1mH	INDUCT PWR 1MH SMD	0.244 x 0.244 inch	PG0087.105NLT	Pulse
1	L4	10uH	Inductor, SMTPower, 6A	0.492 x 0.492 inch	PF0553-103NL	Pulse
2	Q1, Q9	AO4444	MOSFET N-CH 80V 11A 8-SOIC	SO8	AO4444	Alpha & Omega Semiconductor Inc
1	Q10	MMBT2222A	TRANSISTOR, NPN, HIGH-PERFORMANCE, 500mA	SOT-23	MMBT2222A	Fairchild
1	Q11	MMBT2907A	Transistor, PNP, -60V, -600mA, 225-W	SOT23	MMBT2907ALT1	On Semi
1	Q2	FDC3535	MOSFET P-CH 80V 6-SSOT	SuperSOT-6	FDC3535	Fairchild
2	Q3, Q4	AO4452	MOSFET N-CH 100V 8-SOIC	SO8	AO4452	Alpha & Omega Semiconductor Inc
2	Q5, Q6	DZT853	TRANS NPN 6A 100V MED PWR SOT223	SOT223	DZT853-13	Diodes Inc.
1	R1	1k	Resistor, Chip, 1/16W, 5%	0805	Std	Std
1	R10	80.6k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R100	301k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R13	2k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R14	6.98k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R15	49.9k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
2	R16, R24	0	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R17	4.70k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R18	1.21k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
2	R2, R25	5.11k	Resistor, 1/4W, 5%	1210	Std	Std
1	R20	1	Resistor, Metal Film, 1/4 watt, 5%	1206	Std	Std
1	R21	2.4	Resistor, Chip, 1/16W, 5%	0805	Std	Std
3	R4, R5, R11	10k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
3	R6, R8, R23	1k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
3	R7, R12, R19	60.4k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	R9	100k	Resistor, Chip, 1/16W, 1%	0603	STD	STD
1	T1	40 uH	Transformer, ±20%	0.984x1339 inch	PA3507NL	Pulse
1	T2	PA1005.100NL	Transformer, Current Sense	0.284 x 0.330 inch	PA1005.100NL	Pulse
3	TP1, TP2, TP4	5000	Test Point, Red, Thru Hole Color Keyed	0.100 x 0.100 inch	5000	Keystone
2	TP3, TP5	5001	Test Point, Black, Thru Hole Color Keyed	0.100 x 0.100 inch	5001	Keystone
1	U1	UCC2897APW	IC, Current-Mode Active Clamp PWM Controller	PW20	UCC2897APW	TI
1	U3	TL431AIDBZ	IC, Precision Adjustable Shunt Regulator	SOT23-3	TL431AIDBZ	TI
1	U4	TCMT1107	IC, Photocoupler	MF4	TCMT1107	Vishay

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Mobile Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Transportation and Automotive	www.ti.com/automotive
Video and Imaging	www.ti.com/video

TI E2E Community Home Page

e2e.ti.com

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2011, Texas Instruments Incorporated