

PMP9002_PRI_REVA BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
2	C1, C2	6.8uF	CAP ALUM 6.8UF 400V 20% RADIAL	0.315 inch	UCS2G6R8MPD	Nichicon
1	C3	2200pF	CAP CER 2200PF 250VAC X1Y2 RAD	7.00 Dia mm	STD	STD
1	C4	0.22uF	Capacitor, Ceramic, 50V, X7R, 15%	0603	STD	STD
1	D1	SMAJ120A	Diode, Transient Voltage Suppressor, 120V	SMA	SMAJ120A	Bourns
1	D2	RH06-T	Diode, Bridge, 0.5-A, 600-V	MiniDIP	RH06-T	Diodes
1	D3	MRA4007	Diode, Rectifier, 1A, 1000V, SMA	SMA	STD	STD
1	D5	BAS20	Diode, Switching, 200 mA, 200V	SOD-323	BAS20HT1	On Semi
1	F2	0.5A	FUSE SLOW 250VAC 500MA RADIAL	4x8.35 mm	RST500	BEL Fuse
1	L1	100uH	Inductor, 240mA	0.126 x 0.098 inch	ME3220-104MX	Coilcraft
1	Q1	AOD3N60	MOSFET N-CH 600V 2.5A DPAK		AOD3N60	Alpha & Omega Semiconductor Inc
1	R1	10k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R5	115k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R2	49.9	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R3	49.9	Resistor, 1/4 watt, 5%	1206	STD	STD
1	R4	1	Resistor, Chip, 1/16W, 1%	0805	Std	Std
1	R6	3.01k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
2	R7, R9	10MEG	Resistor, 1/4 watt, 5%	1206	STD	STD
1	R8	21.0k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	T2	550 uH	Transformer, Discontinuous Mode Flyback, ±7%	0.650x0.720 inch	RLTI-1061	Renco
2	TP1, TP2	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
1	U1	UCC28700DBV	IC, Constant Voltage, Constant Current PWM With Primary Side Regulation		UCC28700DBV	

PMP9002_SEC_REVA BOM

COUNT	RefDes	Value	Description	Size	Part Number	MFR
1	A1	N/A	N/A	0.125 x 0.125 inch	N/A	N/A
1	B1	N/A	N/A	0.125 x 0.125 inch	N/A	N/A
1	C1	22uF	Capacitor, Ceramic Chip, 6.3V, X5R, 20%	0805	Std	Std
2	C2, C5	270uF	CAP ALUM 270UF 6.3V 20% RADIAL	0.197 inch	RF80J271MDN1PX	Nichicon
2	C3, C4	1uF	Capacitor, Ceramic, 16V, X7R, 15%	0402	STD	STD
1	D1	SBR10U45	DIODE 10A 45V POWERDI5	Power DI	SBR10U45SP5-13	Diodes
1	J1	292303	Connector, USB TH	14.0 x 14.0 mm	292303	STD
1	L1	1uH	Inductor, Power, 2.5 A, ±20%	0.120 x 0.120 inch	XFL3012-102ML	Coilcraft
1	P3	N/A	Do Not Populate	0.100 x 0.100 inch	N/A	N/A
1	R1	2.2k	Resistor, Chip, 1/16W, 5%	0402	Std	Std
5	R2, R3, R4, R5, R6	DNP	Do Not Populate	0402	N/A	N/A
1	R7	100k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	R8	16.9k	Resistor, Chip, 1/16W, 1%	0402	Std	Std
1	U1	TPS2511DGN	IC, INTELLIGENT USB CHARGING CONTROLLER WITH CURRENT LIMITING POWER SWITCH		TPS2511DGN	

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products

Audio	www.ti.com/audio
Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
OMAP Applications Processors	www.ti.com/omap
Wireless Connectivity	www.ti.com/wirelessconnectivity

Applications

Automotive and Transportation	www.ti.com/automotive
Communications and Telecom	www.ti.com/communications
Computers and Peripherals	www.ti.com/computers
Consumer Electronics	www.ti.com/consumer-apps
Energy and Lighting	www.ti.com/energy
Industrial	www.ti.com/industrial
Medical	www.ti.com/medical
Security	www.ti.com/security
Space, Avionics and Defense	www.ti.com/space-avionics-defense
Video and Imaging	www.ti.com/video

TI E2E Community

e2e.ti.com