UCC28730 5V/10A Flyback

Desimutan	O	Mahaa	Description	De also va Dafanana a	Deathleaster	M	Alternate Deathleasters	
PCB1	Quantity	Value	Description	PackageReference	PartNumber PMP10407	Manufacturer Anv	Alternate PartNumber	Alternate Manufacturer
C1	1	2200pF	Printed Circuit Board CAP, CERM, 2200 pF, 300 V, +/- 20%, E, TH, 2-	TH, 2- Leads, Body	DE6E3KJ222MN3A	Any MuRata		
CI		2200pr			DEGESKJ222IVINSA	MuRala		
			Leads, Body 9x7mm, Pin Spacing 7.5mm	9x7mm, Pin Spacing				
C2 C2 C4	3	690F	CAP ALUM 680UF 6.3V 20% RADIAL	7.5mm		Nichicon		-
C2, C3, C4	1	680uF		10x12.5mm	PLE0J681MDO1			
C5		470uF	CAP ALUM 470UF 6.3V 20% RADIAL	6.3x5.5mm	6.3YXJ470M6.3X11	Rubycon		
<u>C6</u>	1	1uF	CAP, CERM, 1 µF, 16 V, +/- 10%, X5R, 0603	0603	C0603C105K4PACTU	Kemet		
C7 C8	1	0.1uF 47uF	CAP, CERM, 0.1uF, 25V, +/-10%, X7R, 0805	0805	08053C104KAT2A	AVX		
C8	1	47uF	CAP ALUM 47UF 400V 20% RADIAL	18x20mm	EKXG401ELL470MM20	UCC		
		00 F		40.00	S	D 1		
C9	1	68uF	CAP ALUM 68UF 400V 20% RADIAL	18x20mm	400BXW68MEFC18X20	Rubycon		
C11, C14	2	220pF	CAP, CERM, 220 pF, 300 V, +/- 10%, B, TH, 2- Leads,	TH, 2- Leads, Body	DE6B3KJ221KN3A	MuRata		
			Body 8x7mm, Pin Spacing 7.5mm	8x7mm, Pin Spacing				
C12		0.33uF	CAP, Film, 0.33uF, 275V, +/-20%, TH	7.5mm RCAP,	ECQ-U2A334ML	Panasonic		
012	1	0.33UF	CAP, FIIII, 0.330F, 275V, +/-20%, TH	17.5x17.5x9.5mm	ECQ-02A334IVIL	Panasonic		
C13, C15,	4	4E	CAP, CERM, 1uF, 16V, +/-10%, X5R, 0603	0603	C0603C105K4PACTU	Komot	1	
	4	1uF	CAP, CERM, 10F, 16V, +/-10%, X5R, 0603	0603	C0603C105K4PAC10	Kemet		
C18, C19	4	4 7.5	CAR CERM 4.7E 10.1// 10% YER 0602	0603	06027D475KAT2A			
C17	1	4.7uF	CAP, CERM, 4.7 μF, 10 V, +/- 10%, X5R, 0603 CAP, CERM, 2.2 μF, 25 V, +/- 10%, X5R, 1206	0603	0603ZD475KAT2A GRM316R61E225KA12	AVX MuData		
C20	1	2.2uF	CAP, CERM, 2.2 µF, 25 V, +/- 10%, X5R, 1206	1206	GRM316R61E225KA12	MuRata		
C21	1	0.1	CAD CEDM 0.4. E 501/ 1/ 402/ 1/20 0000	0602				
	1	0.1uF	CAP, CERM, 0.1uF, 50V, +/-10%, X7R, 0603	0603	06035C104KAT2A	AVX MuRoto		
C101	1	4700pF	CAP, CERM, 4700 pF, 1000 V, +/- 10%, X7R, 1206	1206	GRM31BR73A472KW01	MuRata		
D1 D2	2	70\/		SMC		Fairshild Comission durates		
D1, D3		78V	TVS DIODE 78VWM 126VC SMC	SMC	SMCJ78A	Fairchild Semiconductor		
D2	1	800V	Diode, Switching-Bridge, 800V, 4A, TH	GBU	GBU4K-E3/45	Vishay-Semiconductor		
D4	1	1.7V	Diode, Ultrafast, 1000V, 1A, SMA	SMA	US1M-13-F	Diodes Inc.		
D5	1	200V	Diode, Ultrafast, 200V, 1A, SMA DIODE SCHOTTKY 40V 1A DO214AC	SMA	ES1D-13-F	Diodes Inc.		
D6		45V		SMA	CDBA140-G	Comchip		
D7	1	30V	Diode, Schottky, 30V, 0.2A, SOD-323	SOD-323	BAT54HT1G	ON Semiconductor		
F1	1		FUSE FAST 250VAC 2A RADIAL	TR5 fuse 8.5mm DIA	37012000410	Littelfuse		
HS1	1		Heat Sink, TO-220, TH	TO-220 Heat Sink	576012B00000G	Aavid		
J1	1	2x1	Conn Term Block, 2POS, 5.08mm, TH	PhoenixContact_1715	1715721	Phoenix Contact		
1.5				721				
J2	1		HEADER, .312 VERT 3POS	19.7x10.7 x8.5 mm	1-1318301-3	TE Connectivity		
L1	1	100uH	INDUCTOR 100UH .9A 8095 RAD	Dia 8x10mm	744772101	Wurth Elektronik eiSos		
L2	1	1.1uH	Inductor, Shielded Drum Core, Superflux, 1.1uH, 13A,	WE-HC3	744314110	Wurth Elektronik eiSos		
			0.0032 ohm, SMD					
L3	1	10mH	Coupled inductor, 10mH, 1A, TH	17.5x22x13 mm	744822110	Wurth Elektronik eiSos		
Q1	1	40V	MOSFET, N-CH, 40V, 22A, SON 5x6mm	SON 5x6mm	CSD18501Q5A	Texas Instruments		None
Q2	1	650V	MOSFET N-CH 650V 10.6A TO220	TO-220AB	IPP65R380E6	Infineon Technologies		None
Q3	1	1.6V	Transistor, PNP, 60V, 0.8A, SOT-23	SOT-23	MMBT2907A	Fairchild Semiconductor		
R1	1	100k	RES, 100 k, 5%, 0.1 W, 0603	0603	CRCW0603100KJNEA	Vishay-Dale		
R2	1	1.0k	RES, 1.0 k, 5%, 0.1 W, 0603	0603	CRCW06031K00JNEA	Vishay-Dale		
R4	1	20.0	RES, 20.0, 1%, 0.25 W, 1206	1206	CRCW120620R0FKEA	Vishay-Dale		
R5, R6	2	100	RES, 100 ohm, 1%, 0.063W, 0402	0402	CRCW0402100RFKED	Vishay-Dale		
R7	1	49.9k	RES, 49.9 k, 1%, 0.1 W, 0603	0603	CRCW060349K9FKEA	Vishay-Dale		
R8	1	221k	RES, 221k ohm, 1%, 0.1W, 0603	0603	CRCW0603221KFKEA	Vishay-Dale		
R9	1	100	RES, 100, 5%, 0.25 W, 1206	1206	CRCW1206100RJNEA	Vishay-Dale		
R10	1	107k	RES, 107 k, 1%, 0.1 W, 0603	0603	CRCW0603107KFKEA	Vishay-Dale		
R11	1	1.0	RES, 1.0, 5%, 0.25 W, 1206	1206	CRCW12061R00JNEA	Vishay-Dale		
R12	1	10	RES, 10 ohm, 5%, 0.1W, 0603	0603	CRCW060310R0JNEA	Vishay-Dale		
R13	1	100k	RES, 100k ohm, 5%, 0.125W, 0805	0805	CRCW0805100KJNEA	Vishay-Dale		
R14	1	590	RES, 590, 1%, 0.1 W, 0603	0603	CRCW0603590RFKEA	Vishay-Dale		
R15, R101	2	0.47	RES 0.47 OHM 1/2W 5% 2010 SMD	2010	ERJ-12ZQJR47U	Panasonic		
R16, R17	2	47.5k	RES, 47.5 k, 1%, 0.1 W, 0603	0603	CRCW060347K5FKEA	Vishay-Dale		
R21	1	0	RES, 0, 5%, 0.1 W, 0603	0603	CRCW06030000Z0EA	Vishay-Dale		
T1	1	220 uH	Transformer, 220 uH, TH	TH, 24-Leads, Body	RLTI-1123	Renco Electronics		
				1250x1100mil				
U1	1		Voltage Droop Monitor with Wake-Up Output,	DBV0005A	UCC24650DBV	Texas Instruments		None
			DBV0005A					
U2	1		GREEN Rectifier Controller Device, D0008A	D0008A	UCC24610D	Texas Instruments		None
U3	1		50 mA, 24 V, 3.2-mA Supply Current Low-Dropout	DCK0005A	TPS71550DCK	Texas Instruments		None
			Linear Regulator, DCK0005A					
U4	1		Constant-Voltage Constant-Current Flyback Controller	D0007A	UCC28730D	Texas Instruments		None
1			With PSR and Wake-Up Monitoring, D0007A			1		
			-					
C10	0	100pF	CAP, CERM, 100pF, 100V, +/-5%, C0G/NP0, 0603	0603	C1608C0G2A101J	TDK		
C16	0	47pF	CAP, CERM, 47pF, 25V, +/-5%, C0G/NP0, 0402	0402	GRM1555C1E470JA01	MuRata		
					D	I		
R3	0	DNP	RES, 0 ohm, 5%, 0.125W, 0805	0805	CRCW08050000Z0EA	Vishay-Dale		
R18	0	36.5k	RES, 36.5 k, 1%, 0.1 W, 0603	0603	CRCW060336K5FKEA	Vishay-Dale		
R19	0	3.16Meg	RES, 3.16 M, 1%, 0.1 W, 0603	0603	CRCW06033M16FKEA	Vishay-Dale		
R20	0	1.0Meg	RES, 1.0 M, 5%, 0.1 W, 0603	0603	CRCW06031M00JNEA	Vishay-Dale		
RT1	0	10 ohm		Disc 11.5mmx6mm		EPCOS Inc		

Notes:

Unless otherwise noted in the Alternate PartNumber and/or Alternate Manufacturer columns, all parts may be substituted with equivalents.

\$

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2015, Texas Instruments Incorporated