

Filename: PMP2735\_REVB\_SCH\_bom.xls

Date: 12/19/2008

**PMP2735\_REVB\_SCH BOM Vout=3.3V@3A**

COUNT	RefDes	Value	Description	Size	Part Number	MFR	AREA
4	C1	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	0603	Std	Std	
	C2	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	0603	Std	Std	
	C3	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	0603	Std	Std	
	C4	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	0603	Std	Std	
1	C5	1000pF	Capacitor, Ceramic, 2kV, X7R 10%	1808	C4520X7R3D102K	TDK	
1	C6	2200pF	Capacitor, Ceramic, 2kV, X7R, 20%	1812	C4532X7R3D222K	TDK	
1	C7	2200pF	Capacitor, Ceramic, 100V, X7R, 10%	0805	Std	Std	
1	C8	22uF	Capacitor, Aluminum, 100V, 20%	8x10.2mm	EEVFK2A220P	Panasonic	
2	C9	1uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	Std	Std	
	C10	1uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	Std	Std	
1	C11	0.01uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	Std	Std	
1	C14	330uF	Capacitor, Aluminum, 6.3V, ±20%	0.260 x 0.276 inch	EEVFK0J331XP	Panasonic	
1	C15	0.22uF	Capacitor, Ceramic, 25V, X7R, 10%	0805	Std	Std	
1	C16	10uF	Capacitor, Aluminum, 25V, ±20%	0.200 x 0.210 inch	EEVFK1E100R	Panasonic	
1	C17	220pF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
1	C18	560pF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
1	C19	2.2nF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
2	C20	0.1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
1	C21	47nF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
	C22	0.1uF	Capacitor, Ceramic, 16V, X7R, 10%	0603	Std	Std	
1	C23	0.1uF	Capacitor, Ceramic, 100V, X7R, 10%	1210	Std	Std	
1	C24	1nF	Capacitor, Ceramic, 100V, X7R, 10%	0805	Std	Std	
1	C25	330pF	Capacitor, Ceramic, 200V, X7R, 10%	0805	Std	Std	
1	C26	1nF	Capacitor, Ceramic, 100V, X7R, 10%	0805	Std	Std	
1	CL1	NA	Current Loop, 0.025 holes	0.120 X 0.075 inch	NA	NA	
1	D1	1SMA10CAT3	Diode, TVS, 58-V, 400W	SMA	1SMA10CAT3 Series	On Semi	
2	D2	HD01-T	Bridge Rectifier, 100V, 0.8A, Glass Passivated, §MINI DIP4		HD01-T	Diodes, Inc	
	D3	HD01-T	Bridge Rectifier, 100V, 0.8A, Glass Passivated, §MINI DIP4		HD01-T	Diodes, Inc	
1	D5	MURA120	Diode, Rectifier, 1A, 200V	SMA	MURA120	On Semi	
2	D6	BZT52C15S	Diode, Zener, 200mW, 15V	SOD-323	MM3Z2V4ST1	On Semi	
	D7	BZT52C15S	Diode, Zener, 200mW, 15V	SOD-323	MM3Z2V4ST1	On Semi	
	D8	MURA120	Diode, Rectifier, 1A, 200V	SMA	MURA120	On Semi	
1	D9	RED	Diode, LED, RED, 2.0-V, 850-mcd,SM	1210	LTST-C930KRKT	LITE-ON INC	
1	D10	BAS16	Diode, Switching, 200mA, 75V, 225mW	SOT-23	BAS16LT1	On Semi	
1	D12	BAV99	Diode, Dual Ultra Fast, Series, 200-mA, 70-V	SOT23	BAV99	Fairchild	
	D13	MURA120	Diode, Rectifier, 1A, 200V	SMA	MURA120	On Semi	

	D14	MURA120	Diode, Rectifier, 1A, 200V	SMA	MURA120	On Semi
2	FB1	15-Ohms	Bead, Ferrite, SMT, 15-Ohms, 1500mA	0805	MMZ2012R150A	Steward
	FB2	15-Ohms	Bead, Ferrite, SMT, 15-Ohms, 1500mA	0805	MMZ2012R150A	Steward
2	J1	5520252-4	Connector, Jack, Modular, 8 POS	0.705 x 0.820	5520252-4	AMP
	J2	5520252-4	Connector, Jack, Modular, 8 POS	0.705 x 0.820	5520252-4	AMP
1	J3	ED1514	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	OST
2	J4	ED1514	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	
	J6	ED1514	Terminal Block, 2-pin, 6-A, 3.5mm	0.27 x 0.25	ED1514	
1	L1	10uH	Inductor, SMT, 1.1A, 120milliohm	4.45x6.6mm	SRR0603-100ML	Bourns
1	L2	1.0uH	Inductor, SMT, 1.0-uH, 7.5-A, 7-milliohm	0.51x0.37	SDR1005-1R0ML	Bourns
1	Q1	IRF8113	MOSFET, N-ch, 30-V, 17.2-A, 5.6-milliOhms	SO8	IRF8113	IR
1	Q2	SI4848DY	MOSFET, N-ch, 150-V, 3.7-A, 85-milliOhms	SO8	SI4848DY	VISHAY SILICONIX
4	R1	75	Resistor, Chip, 1/16W, 5%	0603	Std	Std
	R2	75	Resistor, Chip, 1/16W, 5%	0603	Std	Std
	R3	75	Resistor, Chip, 1/16W, 5%	0603	Std	Std
	R4	75	Resistor, Chip, 1/16W, 5%	0603	Std	Std
1	R5	10	Resistor, Chip, 1/2W, 5%	2010	Std	Std
1	R6	160K	Resistor, Chip, 1/10W, 5%	0805	Std	Std
1	R7	24.9K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R8	1K	Resistor, Chip, 1/10-W, 5%	0805	Std	Std
1	R9	49.9	Resistor, Chip, 1/8W, 1%	0805	Std	Std
1	R10	118K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R11	162K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R12	1.27K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R13	24.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std
2	R14	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R15	4.7	Resistor, Chip, 1/16W, 5%	0603	Std	Std
1	R16	10K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R17	49.9	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R18	0.39	Resistor, Chip, 1/2W, 1%	2010	Std	Std
1	R19	41.2K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
	R20	0	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R21	20K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R22	422	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R23	2K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R24	24.3K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R25	79	Resistor, Chip, 1/2W, 5%	2010	Std	Std
1	R26	392K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R27	39.2K	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	R28	348	Resistor, Chip, 1/16W, 1%	0603	Std	Std
1	T1	H2019	Xfmr, Center-tapped, Voice Over IP	0.500 x 0.370	H2019	Pulse
1	T2	HA3801-AL	Transformer, PoE 13W, Triple Secondary, 165uH	0.875 x 0.675	HA3801-AL	Coilcraft

9	TP1	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
4	TP2	5013	Test Point, Orange, Thru Hole	0.125 x 0.125 inch	5013	Keystone
	TP3	5013	Test Point, Orange, Thru Hole	0.125 x 0.125 inch	5013	Keystone
	TP4	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP5	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
8	TP6	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
9	TP7	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP8	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP9	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP10	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP11	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP12	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP13	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP14	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP15	5013	Test Point, Orange, Thru Hole	0.125 x 0.125 inch	5013	Keystone
	TP17	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP19	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP20	5013	Test Point, Orange, Thru Hole	0.125 x 0.125 inch	5013	Keystone
	TP21	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP23	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP24	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP25	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP26	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP27	5010	Test Point, Red, Thru Hole	0.125 x 0.125 inch	5010	Keystone
	TP28	5012	Test Point, White, Thru Hole	0.125 x 0.125 inch	5012	Keystone
	TP29	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP30	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP31	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP32	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
	TP33	5011	Test Point, Black, Thru Hole	0.125 x 0.125 inch	5011	Keystone
1	U1	TPS23753PW	IC, IEEE 802.3af Integrated Primary Side Contro	TSSOP14	TPS23753PW	TI
1	U2	TCMT1107	IC, Photocoupler, 3750VRMS, 80-160% CTR	MF4	TCMT1107	Vishay
1	U3	TLV431ACDBVR	IC, Shunt Regulator, 1.24-V ref, 6-V, 10-mA, 1%	SOT23-5	TLV431ACDBVR	TI

- Notes:
1. These assemblies are ESD sensitive, ESD precautions shall be observed.
  2. These assemblies must be clean and free from flux and all contaminants.  
Use of no clean flux is not acceptable.
  3. These assemblies must comply with workmanship standards IPC-A-610 Class 2.
  4. Ref designators marked with an asterisk (\*\*\*) cannot be substituted.  
All other components can be substituted with equivalent MFG's components.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
OMAP Mobile Processors	<a href="http://www.ti.com/omap">www.ti.com/omap</a>
Wireless Connectivity	<a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>

TI E2E Community Home Page

[e2e.ti.com](http://e2e.ti.com)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated